


NOTES: UNLESS OTHERWISE SPECIFIED


1. FOR USE WITH BELDEN 9529, 1505A & 1805F CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CABLE TRIMMING USE KTJ-57 & KTD-26.
4. FOR CRIMPING USE DIE KTH-2261.
5. INTERFACE PER MIL-STD-348 SERIES TNC, SOCKET CONTACT, 75 OHM.
6. MATERIAL SPECIFICATION:
INSULATOR: TEFLON, ASTM-D-4894 OR ASTM D1710
GASKET: SILICONE RUBBER, A-A-59588
SPRING WASHER, OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196
ALL OTHER METAL PARTS: BRASS PER ASTM B16
7. FINISH SPECIFICATIONS:
CENTER CONTACT: .000050 MIN GOLD PER ASTM B488 OVER .000050 MIN NICKEL PER AMS-QQ-N-290(RoHS)
SPRING WASHER: .000200 MIN SILVER PER ASTM B700 OVER .000020 MIN COPPER PER ASTM B734 RoHS
ALL OTHER METAL PARTS, .000050 MIN NICKEL PER AMS-QQ-N-290 OVER .000050 MIN COPPER PER ASTM B734(RoHS)
8. ELECTRICAL SPECIFICATIONS:
NOMINAL IMPEDANCE- 75 OHMS
WORKING VOLTAGE- 500 VOLTS RMS
FREQUENCY RANGE- DC TO 6 GHz
RETURN LOSS: UP TO 1.5GHz, <-30dB
UP TO 3.0GHz, <-22dB
UP TO 6.0GHz, <-18dB
9. COMPLIANT TO SMPTE 424M (3G-SDI) SPECIFICATION.

REV	DESCRIPTION	BY DATE	APPD
N	ER045518	KPS 01/21/13	DCAM



MARK: KINGS 2065-2-2-9 (DATE CODE)

CATALOG P/N: 2065-2-9



PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES (MM) TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.25] XXX [XXX] ± .004 [0.10] XXXX [XXXX] ± .0005 ANGLES: ± 2° SCALE: X:1				KINGS by WINCHESTER Winchester Electronics Corporation 159 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				THIRD ANGLE PLUG, 75 BNC			
DRAWN	DATE	APPROVED	DATE	A			
TML	01/11/99	DCI	01/11/99				
APPROVED	DATE	APPROVED	DATE				
XXX	XX/XX/XX	XXX	XX/XX/XX	SD2065-2-9			
				SHT OF		REV	
				1 1		N	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[2065-2-9](#)