

NO OF POSITIONS
-020, -040, -060,
* -080, * -100
(PER ROW)
* (SEE NOTE 11)

LEAD STYLE

-01: .1680 [4.267]
-02: .2861 [7.267]
-03: .4042 [10.267]
-04: .6010 [15.265]
-05: .7190 [18.263]
-06: .8370 [21.260]
-07: .9540 [24.231]
-08: 1.1510 [29.260]
-09: .5220 [13.258]
-10: .5606 [14.239]

PLATING SPECIFICATION

-F: FLASH GOLD WITH MATTE TIN TAILS
(USE T-1SXX-XX-F, T-1G1-XX-F)
(SEE NOTE 07)
-L: LIGHT GOLD WITH MATTE TIN TAILS
(USE T-1SXX-XX-L, T-1G1-XX-L)
-H: HEAVY GOLD WITH FLASH GOLD TAILS
(USE T-1SXX-XX-H, T-1G1-XX-G)
-C: ELECTRO-POLISHED SELECTIVE
(USE T-1SXX-XX-C, T-1G1-XX-L)
-STL: SELECTIVE TIN LEAD
(USE T-1SXX-XX-STL, T-1G1-XX-STL)
-FTL: SELECTIVE TIN LEAD
(USE T-1SXX-XX-FTL, T-1G1-XX-FTL)

ROW SPECIFICATION

-D: DOUBLE (USE QTE-20-XX-D-XX
& QTEH-20-XX-D-XX)

NO OF BANKS

OPTION

-A: ALIGNMENT PINS
-LC: LOCKING CLIPS (SEE NOTE 12)
(USE LC-08-TM-01)
-K: POLYIMIDE FILM
(USE K-DOT-.276-.375-.005, SEE FIG. 2)
(N/A ON STYLE -07 & -08)
-TR: TAPE & REEL (60 POS. MAX)
(40 FOR -GP OPTION)
(N/A ON STYLE -05, -06, -07, & -08)
-GP: GUIDE POSTS (SEE FIG. 3, SHT. 2)
(AVAILABLE ON -01 ONLY)
(USE QTE-20-01-D-XX-GP)
(T & R PACK: 40 POS. MAX.)
-SD: SCREW DOWN (SEE FIGURE 4, SHEET 2)
(AVAILABLE ON -01 ONLY)
(USE QTE-20-01-D-XX-SD)
-FL: FRICTION LOCKS (SEE FIG. 8, SHEET 4)
(ONLY AVAILABLE ON -01 & -02)
(NOT AVAILABLE WITH -GP, -SD)
-RT1: RETENTION OPTION (SEE FIG. 9, SHEET 5)
(ONLY AVAILABLE ON -01 LEAD STYLE)
(MUST USE -A OPTION)
(USE QTE-20-01-D-XX-A-RT1 & T-1R36-01-F)
(NOT AVAILABLE WITH -LC, -GP, -SD, OR -FL)
(N/A ON STYLE -100 POS)
-L: LATCHING OPTION (40 POS. MAX.)
(SEE FIG. 11, SHEET 6) (MUST USE -A OPTION)
(AVAILABLE ON -01 ONLY)
(NOT AVAILABLE WITH -LC, -GP, -SD, -FL,
OR -RT1)

T-1SXX-XX-XXX
(SEE TABLE 1)

C3-B-CP
SEE TABLE 2

"A" +.003
-.001
(SEE NOTE 9)
C2-B-DC

.0370 [0.940] REF
.0150 [0.381] REF
.280 [7.11] REF
.0375 [0.953] REF

SECTION "A"- "A"

NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM TERMINAL RETENTION: 8 OZ.
3. MINIMUM GROUND PLANE RETENTION: 1 LB.
4. PARTS TO BE MOLDED TO POSITION.
5. MAXIMUM VARIANCE OF .002 [.05].
6. DIMENSION APPLIES TO TERMINALS AND GROUND PLANE.
7. T-1SXX-XX-L CAN BE SUBSTITUTED FOR T-1SXX-XX-F.
8. NOTE DELETED.
9. GROUND PLANE PRESS HEIGHT MUST BE .003 [.08] LESS THAN THE MAX HEIGHT OR .001 [.03] GREATER THAN THE MINIMUM HEIGHT OF THE TERMINALS.
10. T-1R36 RETENTION TO BODY TO BE 1.0 LBF.
11. FOR NEW APPLICATIONS REQUIRING THESE POSITIONS, PLEASE CONTACT SAMTEC INTERCONNECT PROCESSING GROUP.
12. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION."
13. ROW TO ROW MIN IS .152, PIN CAN EXTEND PAST WALL .003 MAX.

BY

C12-A-1MV






FIG 1
QTE-060-01-XXX-D-LC SHOWN



-LC: LOCKING CLIP OPTION SHOWN



-A: ALIGNMENT PIN OPTION SHOWN
(STYLES -01, -02 & -03)

TABLE 2	
NO OF POSITIONS	COPLANARITY INCLUDING GP
-020 THRU -060	.004 [.10]
-080 THRU -100	.006 [.15]

(SEE NOTE 11)

TABLE 1					
STYLE	"A"	"B"	BODY	GROUND PLANE	TERMINAL
-01	.1680 [4.267]	.1600 [4.064]	QTE-20-01-D-XX	T-1G1-01-XXX	T-1S39-01-XXX
-02	.2861 [7.267]	.2781 [7.064]	QTE-20-02-D-XX	T-1G1-02-XXX	T-1S39-02-XXX
-03	.4042 [10.267]	.3962 [10.063]	QTE-20-03-D-XX	T-1G1-03-XXX	T-1S39-03-XXX

MATED HEIGHT WITH QSE-01
.197 [5.00] REF
.315 [8.00] REF
.433 [11.00] REF

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
DECIMALS .XX: ±.01 [.3]
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

ANGLES 2°

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:

DO NOT SCALE DRAWING
INSULATOR: LCP, COLOR: BLACK
TERMINAL: PHOS BRONZE
GROUND PLANE: PHOS BRONZE

SHEET SCALE: 1:0.8

DESCRIPTION:

.8mm DOUBLE ROW HS TERMINAL ASSEMBLY

DWG. NO.

QTE-XXX-XX-XXX-D-XXX

BY: DEAN P

09-14-2010

SHEET 1 OF 6

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

FIG 2
-K: POLYIMIDE FILM PAD
[USE K-DOT-.276-.375-.005]

TABLE 3	
STYLE	"R"
-01	.173[4.39]
-02	.291[7.39]
-03	.409[10.39]
-04	.605[15.37]
-05	.721[18.31]
-06	.840[21.33]
-09	.528 [13.41]
-10	.567[14.37]





FIG 3
-GP: GUIDE POST OPTION
(-01 LEAD STYLE ONLY)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)





FIG 4
-SD: SCREW DOWN OPTION
(-01 LEAD STYLE ONLY)
(SAME AS FIG 3, UNLESS OTHERWISE STATED)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.8mm DOUBLE ROW HS TERMINAL ASSEMBLY

DWG. NO. QTE-XXX-XX-XXX-D-XXX

BY: DEAN P 09-14-2010 SHEET 2 OF 6

FIG 5
QTE-060-04-X-D-LC SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1]
(STYLES -04, -05 & -06)





FIG 6
QTE-060-07-X-D-A SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 5]
(STYLES -07 & -08)

TABLE 4						MATED HEIGHT WITH QSE-01
STYLE	"A"	GROUND PLANE	TERMINAL	BOTTOM SPACER BODY	TOP BODY	
-04	6010 [15 265]	T-1G1-04-XXX	T-1S41-04-XXX	QTEH-20-01-D-XXX	QTE-20-03-D-XXX	630 [16.00] REF
-05	7190 [18 263]	T-1G1-05-XXX	T-1S41-05-XXX	QTEH-20-01-D-XXX	QTE-20-03-D-XXX	748 [19.00] REF
-06	8370 [21 260]	T-1G1-06-XXX	T-1S41-06-XXX	QTEH-20-02-D-XXX	QTE-20-03-D-XXX	866 [22.00] REF
-07	9540 [24 232]	T-1G17-01-XXX	T-1S61-21-XXX	QTEH-20-04-D-XXX	QTE-20-02-D-XXX	984 [25.00] REF
-08	1 1510 [29 235]	T-1G17-02-XXX	T-1S61-22-XXX	QTEH-20-04-D-XXX	QTE-20-02-D-XXX	1 181 [30.00] REF
-09	5220 [13 259]	T-1G1-09-XXX	T-1S60-09-XXX	QTEH-20-01-D-XXX	QTE-20-02-D-XXX	551 [14.00] REF
-10	5606 [14 239]	T-1G1-10-XXX	T-1S60-10-XXX	QTEH-20-01-D-XXX	QTE-20-02-D-XXX	591 [15.00] REF







FIG 7
QTE-060-09-X-D-A SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 5]
(STYLES -09 & -10)


F:\DWG\MISC\MKTG\QTE-XXX-XX-X-D-XXX-MKT.SLDDRW

DO NOT SCALE DRAWING SHEET SCALE: 1:0.666667	PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.	
	DESCRIPTION: .8mm DOUBLE ROW HS TERMINAL ASSEMBLY	
	DWG. NO. QTE-XXX-XX-XXX-D-XXX	
	BY: DEAN P	09-14-2010 SHEET 3 OF 6


FIG 8
-FL: FRICTION LOCKS
(ONLY AVAILABLE ON -01 & -02 LEAD STYLES)
(NOT AVAILABLE WITH -GP, -SD OPTIONS)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



DETAIL 'E'
SCALE T2: 1



DETAIL 'F'
SCALE T2: 1



-A: ALIGNMENT PIN OPTION
(STYLES -04, -05, -06, -07, -08, -09 & -10)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322


DESCRIPTION:
.8mm DOUBLE ROW HS TERMINAL ASSEMBLY
DWG. NO.
QTE-XXX-XX-XXX-D-XXX

BY: DEAN P 09-14-2010 SHEET 4 OF 6

FIG 9
-RT1: RETENTION OPTION
(ONLY AVAILABLE ON -01 LEAD STYLE)(MUST USE -A OPTION)
(NOT AVAILABLE WITH -LC, -GP, -SD, OR -FL OPTIONS)
(NOT AVAILABLE ON -100 POSITION)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



SECTION "G"-"G"



DETAIL 'H'
SCALE 5:1

<p>PROPRIETARY NOTE</p> <p>THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.</p> <p>DO NOT SCALE DRAWING</p> <p>SHEET SCALE: 1:0.4</p>	
	<p>520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322</p>
	<p>DESCRIPTION: .8mm DOUBLE ROW HS TERMINAL ASSEMBLY</p>
	<p>DWG. NO. QTE-XXX-XX-XXX-D-XXX</p>
<p>BY: DEAN P 09-14-2010 SHEET 5 OF 6</p>	

REVISION BY

FIG 10
-TR: PACKAGING OPTION
(NOT AVAILABLE ON LEAD SYTLES -05, -06, -07 & -08)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)





FIG 11
-L: LATCHING OPTION
(40 POS. MAX.)
(MUST USE -A OPTION)
(AVAILABLE ON -01 LEAD SYTLE ONLY)
(NOT AVAILABLE WITH -LC, -GP, -SD, -FL, OR -RT1)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



BY

CRITICAL DIMENSION INSPECTION INSTRUCTION TABLE	
ASSEMBLY OPERATION	IN PROCESS INSPECTION
FILL T-1SXX	C1, C2, C3, C4, C5, C12
ADD -RT1 OPTION	C6, C8
ADD -L OPTION	C9, C10, C11

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:0.8

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.8mm DOUBLE ROW HS TERMINAL ASSEMBLY

DWG. NO.
QTE-XXX-XX-XXX-D-XXX

BY: DEAN P 09-14-2010 SHEET 6 OF 6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[QTE-040-09-F-D](#) [QTE-040-09-L-D](#) [QTE-040-10-L-D](#) [QTE-020-06-L-D](#)