

FLEXIBLE .025" SQ BOARD STACKERS

Mates with:

SSW, SSQ, ESW, ESQ,
CES, SLW, BSW, BCS,
SSM, IDSS, IDSD, HLE,
PHF, SMSD, SMSS

SPECIFICATIONS

For complete specifications
see www.samtec.com?DW,
www.samtec.com?EW or
www.samtec.com?ZW

DW, EW, ZW

Insulator Material:

Black Glass
Filled Polyester

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over
50µ" (1,27µm) Ni

Current Rating:

3A @ 80°C ambient

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave Only



SPECIFICATIONS

For complete specifications
see www.samtec.com?HW

HW

Same as ZW except:

Insulator Material:

Natural Liquid


Crystal Polymer

RoHS Compliant:

Yes


Lead-Free Solderable:

Yes




TYPE STRIP


DW
= (2,79mm)
.110" Tail




EW
= (8,38mm)
.330" Tail



ZW
= Custom Tail



HW
= High Temp
Custom Tail



NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

STACKER HEIGHT

OTHER OPTIONS

Specify LEAD STYLE from chart

LEAD STYLE	OAL
-07	(10,92) .430
-08	(13,46) .530
-09	(18,54) .730
-10	(21,08) .830
-11	(23,62) .930
-12	(26,16) 1.030
-13	(31,24) 1.230
-14	(36,32) 1.430
-15	(16,00) .630
-16	(11,30) .445
-17	(12,19) .480
-19	(33,78) 1.330
-20	(28,70) 1.130

01 thru 50

50	(2,54) .100 x No. of Positions	01	(2,54) .100	-S
02	(5,08) .200	100	(2,54) .100	-D
03	(7,52) .296	150	(5,08) .200	-T or -Q*
01		148	(2,54) .100	-Q*
			(2,54) .100	
			(0,64) .025 SQ TYP	


-S
= Single
Row

-D
= Double
Row


-T
= Triple
Row

-Q
= Double
Row .200"
(5,08mm)
row space

-“XXX”
= Stacker
Height



-“XXX”
= ZW or HW
Tail Length



-LL
= Locking
Lead
(Shortest
dimension
between the
tail and the
post is the
end that will
be crimped.
Available
on tails from
(2,29) .090" to
(7,87) .310"
only.)
Single row, 01
& 02 positions
& -Q row not
available

-“XXX”
= Polarized

Specify omitted
pin position

-F
= Gold flash on contact,
Matte Tin on tail

-L
= 10µ" (0,25µm) Gold on contact
area of longer tail,
Matte Tin on tail

-G
= 10µ" (0,25µm) Gold on contact
area of longer tail,
Gold flash on balance

-T
= Matte Tin

Note: Other Gold plating options available.
Contact Samtec.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[DW-50-10-G-D-485](#) [DW-50-20-G-D-485](#) [DW-02-12-G-D-650](#) [DW-03-10-L-S-448](#) [DW-05-13-G-S-650](#) [DW-05-14-T-D-1090](#) [DW-05-20-G-S-544](#) [DW-06-14-L-D-800](#) [DW-07-13-G-S-650](#) [DW-07-20-G-S-544](#) [DW-08-13-G-D-886](#) [DW-10-14-T-D-1090](#) [DW-10-15-G-D-245](#) [DW-13-10-L-D-415](#) [DW-15-11-T-D-433](#) [DW-15-12-T-D-250](#) [DW-16-09-T-D-415](#) [DW-20-15-L-S-215](#) [DW-16-09-G-D-465](#) [DW-16-10-G-S-400](#) [DW-08-10-G-D-410](#) [DW-03-08-L-D-216](#) [DW-07-11-T-S-625](#) [DW-07-09-L-D-350](#) [DW-10-15-G-S-394](#) [DW-05-13-T-S-600](#) [DW-08-08-F-S-250](#) [DW-04-15-F-D-280](#) [DW-02-13-F-D-915](#) [DW-15-12-G-D-730](#) [DW-10-08-L-S-255](#)