



NOTES:

1. FOR USE WITH BOEING BMS13-65 OE & ADAMS RUSSELL FC11Z CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-546-1.
3. FOR CRIMPING USE DIE KTH-2214.
4. INTERFACE PER MIL-STD-348, FIG. 310-1.
5. CENTER CONTACT (1-1027-4MA9) SUPPLIED UNASSEMBLED.
6. MARK PACKAGE: KINGS 875-92-3 (DATE CODE)
7. MATERIALS:
INSULATOR-TEFLON, ASTM D1710
GASKET-SILICONE RUBBER, A-A-59588
K-GRIP SLEEVE-COMMERCIAL BRONZE, ASTM B135
C-RING-BER. COP., ASTM B196
BODY & COUPLING NUT-STAINLESS STEEL, 303
ALL OTHER METAL PARTS-BRASS, ASTM B16
8. FINISHES:
CENTER CONTACT: .000050 MIN GOLD PLATE, PER ASTM B488 OVER
.000050 MIN. NICKEL PER AMS-QQ-N-290 (RoHS)
K-GRIP SLEEVE: .000050 MIN NICKEL PLATE PER AMS-QQ-N-290 OVER
.000050 MIN COPPER PER ASTM B734 (RoHS)
ALL OTHER METAL PARTS-PASSIVATED PER QQ-P-35
9. ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE-50 OHMS
FREQUENCY RANGE-DC TO 12.4 GHZ
WORKING VOLTAGE-500 VRMS
10. WEIGHT: 4.3 GRAMS

875-92-3

REVISIONS	
ISSUE	CHANGES
0	ER 34133 KH 10/07/92
B	REVISED PER DMF304 & ER35768 KPL 11/10/11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[875-92-3](#)