

Features

- Concave terminals
- RoHS compliant*
- 8 bit multiple applications
- Smallest bussed chip array
- E 24 Series from 10 ohms to 1 megohm

CAT25 - Thick Film Chip Resistor Arrays

Electrical Characteristics

Parameters	CAT25	Test Method
Number of Resistors	8	
Resistance Range E24	10 ohms to 1 megohm	
Resistance Tolerance	5 %	JIS-C-5202.5.1
Power Rating/Resistor	62.5 mW	
Rating Temperature	+70 °C	
T.C.R.	±200 ppm/°C	JIS-C-5202.5.2
Maximum Operating Voltage	25 V	
Operating Temperature	-55 °C to +125 °C	

Environmental Characteristics


Specification	Characteristics	Test Method
Short Time Overload	±(3 % +0.1 ohm)	JIS-C-5202.5.5
Load Life	±(5 % +0.1 ohm)	JIS-C-5202.7.10
Humidity Load Life	±(3 % +0.1 ohm)	JIS-C-5202.7.9
Resistance to Soldering Heat	±(1 % +0.1 ohm)	JIS-C-5202.6.4
Terminal Strength	±(1 % +0.1 ohm)	JIS-C-5202.6.
Temperature Cycle	±(2 % +0.1 ohm)	JIS-C-5202.7.4
Vibration	±(1 % +0.1 ohm)	JIS-C-5202.6.3
Insulation Resistance	1000 megohms minimum	JIS-C-5202.5.6
Dielectric Withstanding Voltage	50 VRMS	JIS-C-5202.5.7
Lead Solderability	>95 %	JIS-C-5202.6.5

How To Order


CA T 25 - 103	J A LF
Product CA = Chip Array	
Pin Style T = Concave	
Model	
Resistance Value 103 = 10K ohms	
ToleranceJ = 5 %	
Electrical Circuit — A = 8 Resistors, Bussed Type	
Terminations —	

LF = Tin-plated (RoHS compliant)


For Standard Values Used in Capacitors, Inductors, and Resistors, click here.



Land Pattern



Electrical Circuit



*RoHS Directive 2015/863, Mar 31, 2015 and Annex. Specifications are subject to change without notice. Users should verify actual device performance in their specific applications.


0.40 ± 0.20 $(.016 \pm .008)$

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

MM

CAT25 - Thick Film Chip Resistor Arrays

BOURNS



Soldering Profile for RoHS Compliant Chip Resistors and Arrays


Packaging

12 (.472) embossed tape 4,000 pcs. per reel

Material

Substrate	Alumina 96	
Element	Ruthenium Oxide	
Coating	Glass	
Terminal	Plated Ni+Sn	

Derating Curve



Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.

Legal Disclaimer Notice

This legal disclaimer applies to purchasers and users of Bourns[®] products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns[®] products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns[®] products.

The characteristics and parameters of a Bourns[®] product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns[®] product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns[®] product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns[®] product with other components of a Bourns[®] product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns[®] product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns[®] product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns[®] product to meet the requirements of such industry standard or particular qualification. Users of Bourns[®] products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns[®] products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns[®] products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns[®] standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns[®] standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns[®] standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns[®] standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns[®] standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns[®] custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns[®] custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns[®] standard products shall also apply to such Bourns[®] custom products.

Users shall not sell, transfer, export or re-export any Bourns[®] products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns[®] products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns[®] products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns[®] products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <u>http://www.bourns.com/legal/disclaimers-terms-and-policies</u> PDF: <u>http://www.bourns.com/docs/Legal/disclaimer.pdf</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

CAT25-822JALF CAT25-390JALF CAT25-184JALF CAT25-684JALF CAT25-472JA CAT25-331JALF CAT25-131JALF CAT25-125JALF CAT25-225JALF CAT25-431JALF CAT25-683JA CAT25-63JA CAT25-511JA CAT25-153JALF CAT25-122JALF CAT25-222JALF CAT25-822JA CAT25-510JALF CAT25-430JA CAT25-152JALF CAT25-820JALF CAT25-335JA CAT25-301JA CAT25-822JA CAT25-510JALF CAT25-430JA CAT25-152JALF CAT25-820JALF CAT25-335JA CAT25-301JA CAT25-475JALF CAT25-275JALF CAT25-393JA CAT25-431JA CAT25-154JA CAT25-824JA CAT25-823JA CAT25-224JA CAT25-512JALF CAT25-510JA CAT25-122JA CAT25-274JALF CAT25-474JALF CAT25-750JALF CAT25-150JALF CAT25-560JA CAT25-684JA CAT25-562JA CAT25-562JALF CAT25-103JA CAT25-121JALF CAT25-221JALF CAT25-260JA CAT25-182JA CAT25-562JA CAT25-513JALF CAT25-185JALF CAT25-155JALF CAT25-685JALF CAT25-274JA CAT25-153JA CAT25-394JALF CAT25-331JA CAT25-100JA CAT25-222JA CAT25-825JA CAT25-153JA CAT25-390JA CAT25-102JALF CAT25-100JA CAT25-222JA CAT25-184JA CAT25-560JALF CAT25-202JA CAT25-561JA CAT25-565JA CAT25-513JA CAT25-300JALF CAT25-100JALF CAT25-100JALF CAT25-202JA CAT25-561JA CAT25-565JA CAT25-513JA CAT25-500JALF CAT25-100JALF CAT25-100JALF CAT25-202JA CAT25-561JA CAT25-565JA CAT25-513JA CAT25-500JALF CAT25-100JALF CAT25-272JA CAT25-202JA CAT25-394JA CAT25-565JA CAT25-513JA CAT25-823JALF CAT25-100JALF CAT25-270JA CAT25-105JALF CAT25-394JA CAT25-124JALF CAT25-154JALF CAT25-823JALF CAT25-270JA CAT25-105JALF CAT25-334JA CAT25-300JA CAT25-330JALF CAT25-103JALF CAT25-392JALF CAT25-270JA CAT25-105JALF CAT25-334JA CAT25-302JA CAT25-330JALF CAT25-103JALF CAT25-330JALF CAT25-330JALF CAT25-334JA CAT25-330JA CAT25-330JA CAT25-103JALF CAT25-332JALF CAT25-330JA CAT25-105JALF CAT25-324JALF CAT25-271JA CAT25-821JALF CAT25-470JA CAT25-332JALF