




HIGH-DENSITY OPEN-PIN-FIELD ARRAYS

(1.27 mm) .050" PITCH




FEATURES & BENEFITS

- Maximum grounding & routing flexibility
- Up to 560 Edge Rate® contacts optimized for signal integrity performance.
- 7 mm to 40 mm stack heights
- Variety of designs and options: Right-Angle, Guide Posts, 85 Ω Elevated Risers, 85 Ω Tuned, Press-Fit and Press-Fit Right-Angle, Guide Post Field Termination Kits
- Cable mates (SEAC Series) and Jack Screw Standoffs (JSO Series) also available
- Standards: VITA 47, VITA 57.1 FMC, VITA 57.4 FMC+, VITA 74 VNX, PISMO™ 2
- Supports high-speed protocols such as Ethernet, PCI Express®, Fibre Channel & InfiniBand™
- Severe Environment Testing qualified (SEAM/SEAF); aligns with MIL-DTL-55302. Visit samtec.com/set



Solder Charges



(1.12 mm) .044"
Nominal Wipe


**EDGE
RATE**
CONTACT

PAM 4

56
G b p s



MAXIMUM GROUNDING & ROUTING FLEXIBILITY



Differential Pair



Single-Ended



Power


SERIES	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
SEAM/SEAF	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC	Yes
SEAM-RA/SEAF-RA	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	1.9 A (10 pins powered)	260 VAC	Yes
SEAM-GP	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC	Yes
SEAMP/SEAFP	Natural High Temp Nylon	Copper Alloy (SEAMP) BeCu Alloy (SEAFP)	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	1.9 A (6 pins powered)	225 VAC	Not Available
SEAR	Black LCP	Hard Gold Plated	Au over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	Contact Samtec	240 VAC	Not Available
SEAMI	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	Not Available	Not Available	Yes



Note: Some lengths, styles and options are non-standard, non-returnable

(1.27 mm) .050" PITCH • PRESS-FIT & 85 Ω OPEN-PIN-FIELD ARRAYS

SERIES	POSITIONS PER ROW	LEAD STYLE	PLATING OPTION	NO. OF ROWS	OPTION	PACKAGING										
SEAMP Terminal	-10, -20, -30, -40, -50	-02.0 (SEAMP only)	-L = 10 μ" (0.25 μm) Gold on contact area, Matte Tin on tail	-04, -06, -08, -10	-GP Guide Post (SEAMP only)	-TR = Tape & Reel										
SEAFP Socket		-05.0 (SEAFP only)	-S = 30 μ" (0.76 μm) Gold on contact area, Matte Tin on tail	SEAFP: -04 & -06 Rows only		-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)										
SEAMP Board Mates: SEAF, SEAF-RA-GP, SEAFP				<table><tr><th>NO. OF ROWS</th><th>A</th></tr><tr><td>-04</td><td>(7.06) .278</td></tr><tr><td>-06</td><td>(9.60) .378</td></tr><tr><td>-08</td><td>(12.14) .478</td></tr><tr><td>-10</td><td>(14.68) .578</td></tr></table>			NO. OF ROWS	A	-04	(7.06) .278	-06	(9.60) .378	-08	(12.14) .478	-10	(14.68) .578
NO. OF ROWS	A															
-04	(7.06) .278															
-06	(9.60) .378															
-08	(12.14) .478															
-10	(14.68) .578															
																

SEAFP Board Mates: SEAM, SEAM-RA, SEAMP			<table><tr><th>NO. OF ROWS</th><th>A</th></tr><tr><td>-04</td><td>(5.61) .221</td></tr><tr><td>-06</td><td>(8.15) .321</td></tr></table>	NO. OF ROWS	A	-04	(5.61) .221	-06	(8.15) .321
NO. OF ROWS	A								
-04	(5.61) .221								
-06	(8.15) .321								
View complete specifications at: samtec.com?SEAMP & samtec.com?SEAFP . Visit samtec.com?SEAFP-RA for right-angle socket.									

SERIES	POSITIONS PER ROW	LEAD STYLE	NO. OF ROWS	085								
SEAR 85 Ω Tuned Riser	-40, -50	-10.0 = 20 mm Mated Height -20.0 = 30 mm Mated Height -30.0 = 40 mm Mated Height	-06, -08, -10									
SEAR Board Mates: SEAFC		<table><tr><th>POSITIONS PER ROW</th><th>A</th></tr><tr><td>-40</td><td>(71.42) 2.812</td></tr><tr><td>-50</td><td>(84.12) 3.312</td></tr></table>			POSITIONS PER ROW	A	-40	(71.42) 2.812	-50	(84.12) 3.312		
POSITIONS PER ROW	A											
-40	(71.42) 2.812											
-50	(84.12) 3.312											
		<table><tr><th>NO. OF ROWS</th><th>B</th></tr><tr><td>-06</td><td>(11.43) .450</td></tr><tr><td>-08</td><td>(13.97) .550</td></tr><tr><td>-10</td><td>(16.51) .650</td></tr></table>			NO. OF ROWS	B	-06	(11.43) .450	-08	(13.97) .550	-10	(16.51) .650
NO. OF ROWS	B											
-06	(11.43) .450											
-08	(13.97) .550											
-10	(16.51) .650											
												

SERIES	POSITIONS PER ROW	11.0	PLATING OPTION	NO. OF ROWS	SOLDER TYPE	A	K	"X"R						
SEAMI 85 Ω Tuned Terminal	-40	-L = 10 μ" (0.25 μm) Gold on contact area, Matte Tin on solder tail	-08	-1 = Tin/Lead Alloy Solder Charge	-TR = Tape & Reel	-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)								
	-50													
SEAMI Board Mates: SEAF		-S = 30 μ" (0.76 μm) Gold on contact area, Matte Tin on solder tail		-2 = Lead-Free Solder Charge										
														
Note: Some lengths, styles and options are non-standard, non-returnable		View complete specifications at: samtec.com?SEAR & samtec.com?SEAMI .												
		<table><tr><th>NO. OF ROWS</th><th>A</th></tr><tr><td>-08</td><td>(13.41) .528</td></tr><tr><td>-10</td><td>(15.95) .628</td></tr></table>							NO. OF ROWS	A	-08	(13.41) .528	-10	(15.95) .628
NO. OF ROWS	A													
-08	(13.41) .528													
-10	(15.95) .628													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SEAFP-30-05.0-S-04](#) [SEAFP-40-05.0-L-04](#) [SEAFP-20-05.0-L-06](#) [SEAFP-50-05.0-S-06](#) [SEAFP-10-05.0-S-04](#)
[SEAFP-20-05.0-S-04-TR](#) [SEAFP-40-05.0-S-04](#) [SEAFP-20-05.0-S-04](#) [SEAFP-50-05.0-S-04](#) [SEAFP-10-05.0-S-04-TR](#)
[SEAFP-10-05.0-S-06-TR](#) [SEAFP-40-05.0-S-06-TR](#) [SEAFP-50-05.0-L-04](#) [SEAFP-10-05.0-L-06](#) [SEAFP-50-05.0-S-06-](#)
[TR](#) [SEAFP-30-05.0-L-06](#) [SEAFP-30-05.0-S-06](#) [SEAFP-20-05.0-S-06](#) [SEAFP-40-05.0-L-06-TR](#) [SEAFP-40-05.0-S-06](#)
[SEAFP-30-01-S-08-RA-WT-GP](#) [SEAFP-30-01-S-10-RA-WT](#) [SEAFP-10-05.0-L-04-TR](#) [SEAFP-30-05.0-L-04](#) [SEAFP-](#)
[40-05.0-L-06](#) [SEAFP-20-05.0-L-04](#) [SEAFP-20-05.0-L-04-TR](#) [SEAFP-50-05.0-L-06-TR](#) [SEAFP-50-05.0-L-06](#) [SEAFP-](#)
[40-01-S-08-RA-WT-GP](#) [SEAFP-30-01-S-08-RA-WT](#) [SEAFP-50-05.0-L-04-TR](#) [SEAFP-50-05.0-S-04-TR](#) [SEAFP-20-01-](#)
[L-10-RA-WT](#) [SEAFP-40-01-L-08-RA-WT-GP](#) [SEAFP-40-01-L-10-RA-WT-GP](#) [SEAFP-30-01-L-10-RA-WT-GP](#) [SEAFP-](#)
[10-05.0-L-04](#) [SEAFP-20-01-L-10-RA-WT-GP](#) [SEAFP-30-01-L-10-RA-WT](#) [SEAFP-50-01-L-10-RA-WT-GP](#) [SEAFP-20-](#)
[01-L-08-RA-WT](#) [SEAFP-40-01-L-10-RA-WT](#) [SEAFP-50-01-S-10-RA-WT](#) [SEAFP-50-01-L-10-RA-WT](#) [SEAFP-50-01-S-](#)
[08-RA-WT-GP](#) [SEAFP-10-05.0-S-06](#) [SEAFP-50-01-L-08-RA-WT-GP](#) [SEAFP-20-05.0-S-06-TR](#) [SEAFP-30-05.0-L-06-](#)
[TR](#) [SEAFP-30-01-L-08-RA-WT-GP](#) [SEAFP-30-01-L-08-RA-WT](#) [SEAFP-30-05.0-S-06-TR](#) [SEAFP-40-05.0-S-04-TR](#)
[SEAFP-20-01-S-10-RA-WT-GP](#) [SEAFP-40-01-L-08-RA-WT](#) [SEAFP-20-01-S-10-RA-WT](#) [SEAFP-50-01-L-08-RA-WT](#)
[SEAFP-40-05.0-L-06-FR](#) [SEAFP-30-05.0-L-04-TR](#) [SEAFP-30-05.0-S-04-TR](#) [SEAFP-40-01-S-08-RA-WT](#)