




HIGH-DENSITY OPEN-PIN-FIELD ARRAYS

(1.27 mm) .050" PITCH




FEATURES & BENEFITS


- Maximum grounding & routing flexibility
- Up to 560 Edge Rate® contacts optimized for signal integrity performance.
- 7 mm to 40 mm stack heights
- Variety of designs and options: Right-Angle, Guide Posts, 85 Ω Elevated Risers, 85 Ω Tuned, Press-Fit and Press-Fit Right-Angle, Guide Post Field Termination Kits
- Cable mates (SEAC Series) and Jack Screw Standoffs (JSO Series) also available
- Standards: VITA™ 47, VITA™ 57.1 FMC™, VITA™ 57.4 FMC™+, VITA™ 74 VNX™, PISMO™ 2
- Supports high-speed protocols such as Ethernet, PCI Express®, Fibre Channel & InfiniBand™
- Severe Environment Testing qualified (SEAM/SEAF); aligns with MIL-DTL-55302. Visit samtec.com/set

VITA/VNX/VNX+/FMC/FMC+/XMC/XMC+ are all respective trademarks of VITA PCI-SIG®.

The PCI Express® design marks are registered trademarks and/or service marks of PCI-SIG.



Solder Charges



(1.12 mm) .044"
Nominal Wipe


**EDGE
RATE®**
CONTACT

PAM 4

56
G b p s



MAXIMUM GROUNDING & ROUTING FLEXIBILITY



Differential Pair




Single-Ended

Power

SERIES	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
SEAM/SEAF	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC/339 VDC	Yes
SEAM-RA/SEAF-RA	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	1.9 A (10 pins powered)	240 VAC/339 VDC	Yes
SEAM-GP	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC/339 VDC	Yes
SEAMP/SEAFP	Natural High Temp Nylon	Copper Alloy (SEAMP) BeCu Alloy (SEAFP)	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	1.9 A (6 pins powered)	255 VAC/361 VDC	Not Available
SEAR	Black LCP	Hard Gold Plated	Au over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	1.4 A (20 pins powered)	240 VAC/339 VDC	Not Available
SEAMI	Black LCP	Copper Alloy	Au or Sn over 50 μ " (1.27 μ m) Ni	-55 °C to +125 °C	Not Available	Not Available	Yes



Note: Some lengths, styles and options are non-standard, non-returnable

(1.27 mm) .050" PITCH • PRESS-FIT & 85 Ω OPEN-PIN-FIELD ARRAYS

SERIES	POSITIONS PER ROW	LEAD STYLE	PLATING OPTION	NO. OF ROWS	OPTION	PACKAGING										
SEAMP Terminal	-10, -20, -30, -40, -50	-02.0 (SEAMP only)	-L = 10 μ" (0.25 μm) Gold on contact area, Matte Tin on tail	-04, -06, -08, -10	-GP Guide Post (SEAMP only)	-TR = Tape & Reel										
SEAFP Socket		-05.0 (SEAFP only)	-S = 30 μ" (0.76 μm) Gold on contact area, Matte Tin on tail	SEAFP: -04 & -06 Rows only		-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)										
SEAMP Board Mates: SEAF, SEAF-RA-GP, SEAFP				<table><tr><th>NO. OF ROWS</th><th>A</th></tr><tr><td>-04</td><td>(7.06) .278</td></tr><tr><td>-06</td><td>(9.60) .378</td></tr><tr><td>-08</td><td>(12.14) .478</td></tr><tr><td>-10</td><td>(14.68) .578</td></tr></table>			NO. OF ROWS	A	-04	(7.06) .278	-06	(9.60) .378	-08	(12.14) .478	-10	(14.68) .578
NO. OF ROWS	A															
-04	(7.06) .278															
-06	(9.60) .378															
-08	(12.14) .478															
-10	(14.68) .578															
																



SEAFP

Board Mates:
SEAM,
SEAM-RA,
SEAMP



NO. OF ROWS	A
-04	(5.61) .221
-06	(8.15) .321

View complete specifications at: samtec.com?SEAMP & samtec.com?SEAFP. Visit samtec.com?SEAFP-RA for right-angle socket.

SERIES	POSITIONS PER ROW	LEAD STYLE	NO. OF ROWS	085								
SEAR 85 Ω Tuned Riser	-40, -50	-10.0 = 20 mm Mated Height -20.0 = 30 mm Mated Height -30.0 = 40 mm Mated Height	-06, -08, -10									
SEAR Board Mates: SEAFC		<table><tr><th>POSITIONS PER ROW</th><th>A</th></tr><tr><td>-40</td><td>(71.42) 2.812</td></tr><tr><td>-50</td><td>(84.12) 3.312</td></tr></table>			POSITIONS PER ROW	A	-40	(71.42) 2.812	-50	(84.12) 3.312		
POSITIONS PER ROW	A											
-40	(71.42) 2.812											
-50	(84.12) 3.312											
		<table><tr><th>NO. OF ROWS</th><th>B</th></tr><tr><td>-06</td><td>(11.43) .450</td></tr><tr><td>-08</td><td>(13.97) .550</td></tr><tr><td>-10</td><td>(16.51) .650</td></tr></table>			NO. OF ROWS	B	-06	(11.43) .450	-08	(13.97) .550	-10	(16.51) .650
NO. OF ROWS	B											
-06	(11.43) .450											
-08	(13.97) .550											
-10	(16.51) .650											
												

SERIES	POSITIONS PER ROW	11.0	PLATING OPTION	NO. OF ROWS	SOLDER TYPE	A	K	"X"R						
SEAMI 85 Ω Tuned Terminal	-40 -50		-L = 10 μ" (0.25 μm) Gold on contact area, Matte Tin on solder tail -S = 30 μ" (0.76 μm) Gold on contact area, Matte Tin on solder tail	-08 -10	-1 = Tin/Lead Alloy Solder Charge -2 = Lead-Free Solder Charge			-TR = Tape & Reel -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)						
<div><div><div>SEAMI</div><div>Board Mates:</div><div>SEAF</div></div><div><div><div><div></div></div><div><div></div></div></div><div><div>No. of positions x (1.27) .050 + (4.98) .196</div><div>A</div><div>(14.66) .577</div></div></div></div> <table><tr><th>NO. OF ROWS</th><th>A</th></tr><tr><td>-08</td><td>(13.41) .528</td></tr><tr><td>-10</td><td>(15.95) .628</td></tr></table>									NO. OF ROWS	A	-08	(13.41) .528	-10	(15.95) .628
NO. OF ROWS	A													
-08	(13.41) .528													
-10	(15.95) .628													

Note: Some lengths,
styles and options
are non-standard,
non-returnable

View complete specifications at: samtec.com?SEAR & samtec.com?SEAMI.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SEAR-40-10.0-08-085](#) [SEAR-40-30.0-06-085](#) [SEAR-50-10.0-08-085](#) [SEAR-40-20.0-10-085](#) [SEAR-40-30.0-10-085](#)
[SEAR-50-10.0-10-085](#) [SEAR-50-30.0-08-085](#) [SEAR-40-20.0-08-085](#) [SEAR-50-30.0-10-085](#) [SEAR-40-10.0-06-085](#)
[SEAR-40-10.0-10-085](#) [SEAR-50-20.0-10-085](#) [SEAR-40-20.0-06-085](#) [SEAR-50-20.0-08-085](#) [SEAR-50-30.0-06-085](#)
[SEAR-20-31.0-10-085Q](#) [SEAR-20-10.0-10-085](#) [SEAR-40-31.0-08-085Q](#) [SEAR-40-20.0-10-100](#) [SEAR-20-30.0-10-085](#)
[SEAR-50-10.0-06-085](#) [SEAR-50-20.0-06-085](#) [SEAR-20-20.0-10-085](#)