

(2.54 mm) .100"

# THROUGH-HOLE .025" SQ POST SOCKET

## SPECIFICATIONS

For complete specifications see [www.samtec.com?SSW](http://www.samtec.com?SSW) or [www.samtec.com?SSQ](http://www.samtec.com?SSQ)

**Insulator Material:**  
Black Liquid Crystal Polymer (-S & -D) or Black High Temperature Thermoplastic (-T)  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Au or Sn over 50  $\mu$ " (1.27  $\mu$ m) Ni  
**Current Rating (SSW/TSW):**  
4.7 A per pin (2 pins powered)  
**Current Rating (SSQ/TSW):**  
6.3 A per pin (2 pins powered)  
**Operating Temp Range:**  
-55 °C to +125 °C with Gold  
-55 °C to +105 °C with Tin  
**Insertion Depth:**  
(3.68 mm) .145" to (6.35 mm) .250"  
**Normal Force:**  
Standard= 125 grams (4.4 N)  
**Max Cycles:**  
100 with 10  $\mu$ " (0.25  $\mu$ m) Au  
**Voltage Rating:**  
465 VAC / 655 VDC  
**RoHS Compliant:**  
Yes

## PROCESSING

**Lead-Free Solderable:**  
Yes:  
-S and -D row option  
No, Lead Wave only:  
-P, -T and -Q row option

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



**Note:**  
Some lengths, styles and options are non-standard, non-returnable.

Mates With:


TSW, MTSW, MTLW, DW, EW, ZW, TSS, ZSS, TSM, TSSH, HTSS

HIGH-SPEED CHANNEL PERFORMANCE

Rating based on Samtec reference channel. For full SI performance data visit [Samtec.com](http://Samtec.com) or contact [SIG@samtec.com](mailto:SIG@samtec.com)

8

Gbps



Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

All parts within this catalog are built to Samtec's specifications.  
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.


## TYPE STRIP

SSW = Solder Tail

SSQ = Square Tail

## PIN CENTERS

-1 = (2.54 mm) .100" Centers



## NO. PINS PER ROW

## LEAD STYLE

## PLATING OPTION

-F  
= Gold flash on contact, Matte Tin on tail

-L  
= 10  $\mu$ " (0.25  $\mu$ m) Gold on contact, Matte Tin on tail

-G  
= 20  $\mu$ " (0.51  $\mu$ m) Gold on contact, Gold flash on tail

-T  
= Matte Tin (-T N/A on LIF contacts)

## ROW OPTION

-S  
= Single Row

-P  
= Single Row (36 pins max)

-D  
= Double Row

-T  
= Triple Row

-Q  
= Double Row .200" (5.08 mm) row space (Outer rows filled only)

## TAIL OPTION

-RA  
= Right-angle (Leave blank for straight pin version)

ALSO AVAILABLE (MOQ Required)

- Other platings
- Notch option

## OTHER OPTION

-LL  
= Locking Lead


Two leads per strip crimped in opposite directions on or near centerline. Available on tails from (2.29 mm) .090" to (7.87 mm) .310" only. N/A with single row 1 or 2 positions.

-“XXX”  
= Polarized (Specify “XXX” as position number)

## Straight Pin Versions (Specify “LEAD STYLE” from chart)

LEAD STYLE		SINGLE DOUBLE OR TRIPLE A
Standard Insertion Force	Low Insertion Force*	
-01	-21	(2.64) .104
-02	-22	(4.93) .194
-03	-23	(10.00) .394
-04	-24	(14.83) .584
-06**	Not Available	(3.15) .124


\* LIF not available with Tin Plating  
\*\*Style -06 Not available with SSQ



## Right-Angle Versions (Specify “LEAD STYLE” from chart)

LEAD STYLE		SINGLE (-S)	DOUBLE (-D)	TRIPLE (-T & -Q)
Standard Insertion Force	Low Insertion Force*	A	A	A
-02	-22	(2.54) .100	(2.54) .100	(2.54) .100
-03	-23	(7.62) .300	(7.62) .300	Not Available
-04	-24	(12.45) .490	Not Available	Not Available

\*LIF not available with Tin Plating



Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

All parts within this catalog are built to Samtec's specifications.  
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SSQ-130-03-F-D](#)