




SM CONNECTOR

2.5 mm pitch/Disconnectable Crimp style wire-to-wire connectors



The SM series are 2.5 mm pitch, wire-to-wire connectors that perform reliably in high-density, small current applications.

- High contact pressure
- Highly reliable housing construction
- Mountable on a variety of panels
- Arm lock mechanism


Specifications

- Current rating: 3 A AC/DC max.
 - Voltage rating: 250 V AC/DC max.
 - Temperature range: -25°C to +85°C
(including temperature rise in applying electrical current)
 - Contact resistance: Initial value/ 10 mΩ max.
After environmental tests/ 20 mΩ max.
 - Insulation resistance: 500 MΩ min.
 - Withstanding voltage: 1,500 VAC/minute
 - Applicable wire: AWG #28 to #22
0.08 to 0.33 mm²
 - Applicable panel thickness: 0.5 to 2.0 mm
- * In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.


Standards

- Recognized E60389
- △ R50120150


Panel Layout and Assembly layout



<2 to 12 circuits>



<18 circuits>





No. of circuits	Model No. Plug housing	Panel thickness (mm)					
		0.5~0.9		1.0~1.5		1.5~2.0	
		Panel hole dimensions (mm)				General tolerance	
		A ^{+0.15 0}	B ^{±0.1}	A ^{+0.15 0}	B ^{±0.1}	A ^{+0.15 0}	B ^{±0.1}
2	SMP-02V-B(N)C	5.7	9.6	5.7	9.8	5.7	10.0
3	SMP-03V-B(N)C	8.2	12.1	8.2	12.3	8.2	12.5
4	SMP-04V-B(N)C	10.7	14.6	10.7	14.8	10.7	15.0
5	SMP-05V-B(N)C	13.2	17.1	13.2	17.3	13.2	17.5
6	SMP-06V-B(N)C	15.7	19.6	15.7	19.8	15.7	20.0
7	SMP-07V-B(N)C	18.2	22.1	18.2	22.3	18.2	22.5
8	SMP-08V-B(N)C	20.7	24.6	20.7	24.8	20.7	25.0
9	SMP-09V-B(N)C	23.2	27.1	23.2	27.3	23.2	27.5
10	SMP-10V-B(N)C	25.7	29.6	25.7	29.8	25.7	30.0
11	SMP-11V-B(N)C	28.2	32.1	28.2	32.3	28.2	32.5
12	SMP-12V-B(N)C	30.7	34.6	30.7	34.8	30.7	35.0
18	SMP-18V-B(N)C	23.2	27.2	23.2	27.4	23.2	27.6

- Note: 1. Punch holes in the panel according to the sketch and table shown above. Burrs must be removed.
 2. The strength of the panel must be considered when punching two or more holes.
 3. The connector must be inserted from the same side as the hole is punched.

SM CONNECTOR

Contact

Pin contact

Socket contact

Model No.		Applicable wire		Insulation O.D. (mm)	Q'ty/reel
Pin contact	Socket contact	mm ²	AWG #		
SYM-001T-P0.6	SHF-001T-0.8BS	0.08~0.33	28~22	1.2~1.8	Pin contact: 8,500 Socket contact: 5,000

Material and Finish					
Phosphor bronze, tin-plated (reflow treatment)					

RoHS2 compliance
Note: 1. Contact JST for special products.
2. Contact JST for brass products.

Contact	Crimping machine	Applicator		
		Crimp applicator	Dies	Crimp applicator with dies
SYM-001T-P0.6	AP-K2N	MKS-L	MK/SYM-001-06	APLMK SYM001-06


Note: Contact JST for fully automatic crimping applicator.

Contact	Crimping machine	Applicator		
		Crimp applicator	Dies	Crimp applicator with dies
SHF-001T-0.8BS	AP-K2N	MKS-L	MK/SHF-001-08S	APLMK SHF001-08S

Note: Contact JST for fully automatic crimping applicator.


Contact position location numbers

Contact position numbers are stamped




Receptacle housing Plug housing

Receptacle housing



1	10
2	11
3	12
4	13
5	14
6	15
7	16
8	17
9	18
10	
11	
12	

Plug housing



1	10
2	11
3	12
4	13
5	14
6	15
7	16
8	17
9	18
10	
11	
12	

Housing

Material: PA 6, UL94V-0











No. of circuits	Current rating	Receptacle housing (for pin contact)		Plug housing (for socket contact)	
2	3 A	SMR-02V-B, black SMR-02V-N, white (natural)	Q'ty/ bag	SMP-02V-BC, black SMP-02V-NC, white (natural)	Q'ty/ bag
			1,000		1,000
3	3 A	SMR-03V-B, black SMR-03V-N, white (natural)	Q'ty/ bag	SMP-03V-BC, black SMP-03V-NC, white (natural)	Q'ty/ bag
			1,000		1,000
4	3 A	SMR-04V-B, black SMR-04V-N, white (natural)	Q'ty/ bag	SMP-04V-BC, black SMP-04V-NC, white (natural)	Q'ty/ bag
			500		1,000
5	3 A	SMR-05V-B, black SMR-05V-N, white (natural)	Q'ty/ bag	SMP-05V-BC, black SMP-05V-NC, white (natural)	Q'ty/ bag
			500		1,000
6	3 A	SMR-06V-B, black SMR-06V-N, white (natural)	Q'ty/ bag	SMP-06V-BC, black SMP-06V-NC, white (natural)	Q'ty/ bag
			500		500

RoHS2 compliance

SM CONNECTOR

Housing





Material: PA 6, UL94V-0

No. of circuits	Current rating	Receptacle housing (for pin contact)		Plug housing (for socket contact)	
		SMR-07V-B, black SMR-07V-N, white (natural)	Q'ty/ bag	SMP-07V-BC, black SMP-07V-NC, white (natural)	Q'ty/ bag
7	3 A		500		500
8	3 A		500		500
9	3 A		500		500
10	3 A		200		500
11	3 A		200		500

RoHS2 compliance

Housing

Material: PA 6, UL94V-0

No. of circuits	Current rating	Receptacle housing (for pin contact)		Plug housing (for socket contact)	
12	3 A	SMR-12V-B, black SMR-12V-N, white (natural) 	Q'ty/ bag 500	SMP-12V-BC, black SMP-12V-NC, white (natural) 	Q'ty/ bag 500
18	2 A	SMR-18V-B, black SMR-18V-N, white (natural) 	Q'ty/ bag 200	SMP-18V-BC, black SMP-18V-NC, white (natural) 	Q'ty/ bag 200

RoHS2 compliance

Note: 1. SM connectors with any number of circuits can be used either panel mounted or free hanging.
 2. Contact JST for special products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[SMR-03V-B](#) [SMP-02V-BC](#) [SMR-04V-B](#) [SMP-03V-BC](#) [SMP-04V-NC](#) [SMR-05V-N](#) [SMR-02V-B](#) [SMP-04V-BC](#) [SHF-](#)
[001T-0.8BS](#) [SMP-12V-BC](#) [SMR-02V-N](#) [SMP-06V-NC](#) [SMP-05V-NC](#) [SMR-04V-N](#) [SYM-001T-0.6\(N\)](#) [SYM-001T-0.6](#)