

TFSDT-05-30-G-05.00-D-NUS

TSDF-10-D-S

T1M44-M-2830-01-G

(1.27 mm) .050"

TFSD, TFSDT, TSDF, T1M44-R, T1M44-M SERIES

# DISCRETE WIRE COMPONENTS & TOOLING

## Mates with:

SFM, SFC (-TR requires TFM-WT option),  
SFML (-XL end option required)

## SPECIFICATIONS

For complete specifications see [www.samtec.com?TFSD](http://www.samtec.com?TFSD) or [www.samtec.com?TFSDT](http://www.samtec.com?TFSDT)

**Insulator Material:** Black LCP  
**Contact Material:** BeCu

### Plating:

Au over 50  $\mu$ " (1.27  $\mu$ m) Ni

### Operating Temp Range:

-10 °C to +80 °C (PVC)

-40 °C to +125 °C (\*Teflon®)

**Wire:** 28 or 30 AWG

**RoHS Compliant:** Yes

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)





### Notes:

For wiring option and pin position location information, refer to drawings on web.

Teflon® cable is intended for crimp only. Contact Samtec for solderable cable applications.

Some lengths, styles and options are non-standard, non-returnable.

| TYPE STRIP                            | POSITIONS PER ROW                                                                | WIRE GAUGE                             | PLATING OPTION                                          | ASSEMBLED LENGTH                                                                                                                                   | END OPTION                                                                                                                                                                                                                                                                                | END 2 OPTION                                                                                                                                                                                  |
|---------------------------------------|----------------------------------------------------------------------------------|----------------------------------------|---------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>TFSD</b><br>= Double Row PVC Cable | -03, -04,<br>-05, -07,<br>-10, -15,<br>-20, -25,<br>-40, -50<br>(Standard sizes) | -30<br>= 30 AWG<br><br>-28<br>= 28 AWG | -G<br>= 10 $\mu$ "<br>(0.25 $\mu$ m)<br>Gold on contact | "XX.XX"<br>= Assembled Length in Inches (76.20 mm)<br>03.00" min. for -S end option<br>(82.60 mm)<br>03.25" min. for -D, -T, -TF, & -TR end option | -S<br>= Single Ended<br><br>-D<br>= Double Ended<br><br>-T<br>= Transfer End Terminal on End 1 Socket on End 2<br><br>-TF<br>= Transfer End with Friction Lock (-05 & -07 positions not available.)<br><br>-TR<br>= Transfer End with Retention Latch (TFM-WT option required for mating) | Requires -D, -TF or -TR (End 1 Notch Down).<br><br>-NUS<br>= Notch up, straight<br><br>-NDS<br>= Notch down, straight<br><br>-NUX<br>= Notch up, crossed<br><br>-NDX<br>= Notch down, crossed |

\*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

## SPECIFICATIONS

For complete specifications see [www.samtec.com?TSDF](http://www.samtec.com?TSDF), [www.samtec.com?T1M44-R](http://www.samtec.com?T1M44-R) or [www.samtec.com?T1M44-M](http://www.samtec.com?T1M44-M)

**Insulator Material:** Black LCP

**Contact Material:** BeCu



## TOOLING

- Hand Tool:  
CAT-HT-144-2830-12
- Mini Applicator  
CAT-MC-144-2830-XX-01
- Extraction Tool:  
CAT-EX-169-01

### Note:

Some sizes, styles and options are non-standard, non-returnable.

| TYPE                     | POSITIONS PER ROW                                                                | ROW OPTION         | S | TYPE                                                                                                                                  | WIRE GAUGE              | 01 | PLATING                                                 |
|--------------------------|----------------------------------------------------------------------------------|--------------------|---|---------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----|---------------------------------------------------------|
| <b>TSDF</b><br>= Housing | -03, -04,<br>-05, -07,<br>-10, -15,<br>-20, -25,<br>-40, -50<br>(Standard sizes) | -D<br>= Double Row |   | <b>T1M44-R</b><br>= Terminal, Full Reel (35,000 parts per Reel)<br><br><b>T1M44-M</b><br>= Terminal, Mini Reel (5,000 parts per Reel) | -2830<br>= 28 to 30 AWG |    | -G<br>= 10 $\mu$ "<br>(0.25 $\mu$ m)<br>Gold on contact |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[TFSDT-08-28-H-15.00-S](#) [TFSDT-04-28-G-18.00-S](#) [TFSDT-05-28-H-08.00-D-NDS](#) [TFSDT-10-28-H-20.00-SL](#)  
[TFSDT-15-28-G-08.00-T-NDS](#) [TFSDT-03-28-H-15.00-S](#) [TFSDT-05-28-H-08.00-D-NUX](#) [TFSDT-03-28-H-12.00-S](#)  
[TFSDT-06-28-F-12.00-S](#) [TFSDT-08-28-H-03.00-S](#) [TFSDT-13-28-G-08.00-DL-NUX](#) [TFSDT-25-28-G-10.00-S](#) [TFSDT-](#)  
[05-28-H-20.00-S](#) [TFSDT-07-28-F-12.00-S](#) [TFSDT-10-28-G-32.50-T-NDS](#) [TFSDT-05-28-F-12.00-S](#) [TFSDT-05-28-G-](#)  
[14.00-DL-NDS](#) [TFSDT-15-28-H-05.00-S](#) [TFSDT-15-28-G-03.25-T-NUS](#) [TFSDT-15-28-G-07.50-T-NUS](#) [TFSDT-15-28-](#)  
[G-12.00-T-NDX](#) [TFSDT-15-28-H-30.00-TF-NDS](#) [TFSDT-15-30-G-03.25-T-NDS](#) [TFSDT-15-30-G-03.25-T-NUX](#)  
[TFSDT-20-28-G-03.25-T-NUX](#) [TFSDT-20-28-G-03.54-T-NDS](#) [TFSDT-20-28-H-12.00-D-NUS](#) [TFSDT-20-28-H-12.00-D-](#)  
[NUX](#) [TFSDT-25-28-G-04.00-DL-NUX](#) [TFSDT-25-28-G-04.00-TR-NUX](#) [TFSDT-25-28-G-10.00-TR-NDX](#) [TFSDT-25-30-](#)  
[G-84.00-T-NUX](#) [TFSDT-40-28-G-10.00-T-NDS](#) [TFSDT-40-28-G-11.00-S](#) [TFSDT-50-28-H-18.00-T-NDS](#) [TFSDT-05-](#)  
[28-G-07.87-S](#) [TFSDT-05-28-G-48.00-SL](#) [TFSDT-10-28-F-12.00-T-NDS](#) [TFSDT-10-28-G-20.00-D-NUS](#) [TFSDT-15-28-](#)  
[G-10.00-T-NDS](#) [TFSDT-20-28-G-10.00-T-NUS](#) [TFSDT-05-28-G-10.00-S](#) [TFSDT-05-28-G-24.00-TR-NDS](#) [TFSDT-05-](#)  
[28-G-25.00-S](#) [TFSDT-05-28-G-36.00-S](#) [TFSDT-05-30-G-12.00-D-NUS](#) [TFSDT-07-28-G-03.00-S](#) [TFSDT-07-30-G-](#)  
[06.00-T-NDS](#) [TFSDT-08-28-G-06.00-S](#) [TFSDT-10-28-G-06.00-S](#) [TFSDT-10-28-G-08.00-T-NDS](#) [TFSDT-10-28-G-](#)  
[08.00-TR-NDS](#) [TFSDT-10-28-G-36.00-S](#) [TFSDT-15-28-G-06.00-S](#) [TFSDT-05-28-G-05.00-S](#) [TFSDT-05-28-H-15.00-T-](#)  
[NDS](#) [TFSDT-05-28-H-40.00-T-NDS](#) [TFSDT-07-28-G-20.00-SL](#) [TFSDT-07-28-H-36.00-S](#) [TFSDT-10-28-G-05.00-S](#)  
[TFSDT-10-28-G-06.00-D-NDX](#) [TFSDT-10-28-G-11.00-S](#) [TFSDT-10-28-G-12.00-T-NDS](#) [TFSDT-10-28-G-12.00-T-NUX](#)  
[TFSDT-10-28-H-04.00-S](#) [TFSDT-10-30-H-05.00-D-NUS](#) [TFSDT-15-28-G-04.00-T-NDS](#) [TFSDT-05-28-F-12.00-DL-](#)  
[NUS](#) [TFSDT-05-28-G-04.00-D-NUS](#) [TFSDT-05-28-G-20.00-D-NDX](#) [TFSDT-05-28-G-40.00-TF-NDS](#) [TFSDT-05-30-G-](#)  
[40.00-S](#) [TFSDT-07-28-G-08.00-S](#) [TFSDT-07-28-G-12.00-D-NUX](#) [TFSDT-07-30-F-05.00-S](#) [TFSDT-10-28-F-11.81-S](#)  
[TFSDT-10-28-G-04.00-TF-NDS](#) [TFSDT-05-28-G-10.00-D-NDS](#) [TFSDT-05-28-G-11.00-S](#) [TFSDT-05-28-G-48.00-D-](#)  
[NUS](#) [TFSDT-05-30-G-11.81-S](#) [TFSDT-07-30-F-15.00-TR-NDS](#) [TFSDT-09-28-G-12.00-S](#) [TFSDT-10-28-G-24.00-D-](#)  
[NUS](#) [TFSDT-10-28-G-30.00-T-NDS](#) [TFSDT-15-28-G-04.00-T-NUS](#) [TFSDT-15-28-G-15.00-SL](#) [TFSDT-15-28-G-15.00-](#)  
[T-NDS](#) [TFSDT-15-28-G-18.00-S](#) [TFSDT-20-28-G-03.00-S](#) [TFSDT-20-28-G-16.00-S](#) [TFSDT-25-28-G-08.00-D-NUS](#)  
[TFSDT-25-28-H-36.00-S](#) [TFSDT-25-30-H-40.00-SL](#) [TFSDT-05-28-G-06.00-D-NDS](#) [TFSDT-05-28-G-13.78-T-NDS](#)  
[TFSDT-05-28-G-24.00-T-NDS](#) [TFSDT-05-30-G-03.00-S](#) [TFSDT-07-28-G-06.00-S](#) [TFSDT-07-28-H-12.00-S](#)