



preci-dip

PCB CONNECTORS


SERIES 800

800-PP-NNN-65-001101

Single row

2.54 mm, Solderless compliant press-fit, Pin Ø 0.76 mm

Pin connectors, press-fit With compliant pin for solderless mount in PCB plated through holes.



TECHNICAL SPECS.:

Insulator	Black glass filled polyester PCT-GF30-FR
Flammability	UL 94V-O
Contact	Bronze CuSn4Pb4Zn4 (C54400)
Connecting pin Ø	0.76 mm
Mechanical life	Min. 500 cycles
Rated current	3 A
Dielectric strength	Min. 1000 V RMS
PCB hole Ø	1 mm +0.09/-0.06 mm finished (1.15 ±0.025 mm drill)

ORDERING INFORMATION:

PP Plating code	Termination	Connecting pin
10*	Gold 0.25 µm	Gold 0.25 µm
80*	Tin	Tin
V3	Tin	Gold 0.75 µm

* not for 800...-6B-002101NNN number of poles. Replace NNN with the requested number of poles, e.g. 800-10-NNN-65-001101 for a single row version with 8 pins becomes 800-10-008-65-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole $\varnothing$: $0.7 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole $\varnothing$: $1 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Preci-dip:](#)

[800-10-002-66-001101](#) [800-10-013-66-001101](#) [800-10-012-66-001101](#) [800-10-011-66-001101](#) [800-10-010-66-001101](#) [800-10-009-66-001101](#) [800-80-007-66-001101](#) [800-80-006-66-001101](#) [800-80-005-66-001101](#) [800-80-004-66-001101](#) [800-80-003-66-001101](#) [800-80-015-66-001101](#) [800-80-026-66-001101](#) [800-80-012-66-001101](#) [800-80-011-66-001101](#) [800-80-010-66-001101](#) [800-80-009-66-001101](#) [800-80-008-66-001101](#) [800-80-019-66-001101](#) [800-80-018-66-001101](#) [800-80-017-66-001101](#) [800-80-016-66-001101](#) [800-10-063-66-001101](#) [800-80-014-66-001101](#) [800-10-040-66-001101](#) [800-80-024-66-001101](#) [800-80-023-66-001101](#) [800-80-022-66-001101](#) [800-80-021-66-001101](#) [800-80-020-66-001101](#) [800-10-045-66-001101](#) [800-10-044-66-001101](#) [800-10-043-66-001101](#) [800-10-042-66-001101](#) [800-10-053-66-001101](#) [800-80-013-66-001101](#) [800-80-002-66-001101](#) [800-10-050-66-001101](#) [800-10-049-66-001101](#) [800-10-048-66-001101](#) [800-10-047-66-001101](#) [800-10-046-66-001101](#) [800-10-057-66-001101](#) [800-10-056-66-001101](#) [800-10-055-66-001101](#) [800-10-054-66-001101](#) [800-10-064-66-001101](#) [800-10-052-66-001101](#) [800-80-027-66-001101](#) [800-10-062-66-001101](#) [800-10-061-66-001101](#) [800-10-060-66-001101](#) [800-10-059-66-001101](#) [800-10-058-66-001101](#) [800-80-055-66-001101](#) [800-80-054-66-001101](#) [800-80-053-66-001101](#) [800-80-025-66-001101](#) [800-80-064-66-001101](#) [800-10-051-66-001101](#) [800-80-061-66-001101](#) [800-80-060-66-001101](#) [800-80-059-66-001101](#) [800-80-058-66-001101](#) [800-80-057-66-001101](#) [800-80-056-66-001101](#) [800-80-028-66-001101](#) [800-80-040-66-001101](#) [800-80-062-66-001101](#) [800-80-050-66-001101](#) [800-80-063-66-001101](#) [800-80-051-66-001101](#) [800-80-034-66-001101](#) [800-80-033-66-001101](#) [800-80-032-66-001101](#) [800-80-031-66-001101](#) [800-80-030-66-001101](#) [800-80-029-66-001101](#) [800-10-039-66-001101](#) [800-80-039-66-001101](#) [800-80-052-66-001101](#) [800-80-037-66-001101](#) [800-80-036-66-001101](#) [800-80-035-66-001101](#) [800-80-046-66-001101](#) [800-80-045-66-001101](#) [800-80-044-66-001101](#) [800-80-043-66-001101](#) [800-80-042-66-001101](#) [800-80-041-66-001101](#) [800-10-028-66-001101](#) [800-10-041-66-001101](#) [800-80-038-66-001101](#) [800-80-049-66-001101](#) [800-80-048-66-001101](#) [800-80-047-66-001101](#) [800-10-022-66-001101](#) [800-10-021-66-001101](#) [800-10-020-66-001101](#) [800-10-019-66-001101](#)