

samtec



(1,27 mm) .050"

TFSDT-05-30-G-05.00-D-NUS

TFSD-15-30-G-05.00-D-NUS

TFSS-07-30-G-05.00-D-NUS

TFSS, TFSST, TFSD, TFSDT SERIES

TIGER EYE™ DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?TFSS, www.samtec.com?TFSD, www.samtec.com?TFSDT, or www.samtec.com?TFSST

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Au over 50µ" (1,27 µm) Ni

Operating Temp Range:

-10°C to +80°C (PVC)

-40°C to +125°C (*Teflon®)

Wire:

28 or 30 AWG

RoHS Compliant:

Yes

Mates with:

SFM, SFC (-TR requires

TFM-WT option),

SFML (-XL end option required)

Single or
Double
Ended28 or 30
AWG(1,27 mm)
.050"
pitch

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE STRIP	POSITIONS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLED LENGTH	END OPTION	END 2 OPTION
TFSS = Single Row PVC Cable	-03, -04, -05, -07, -10, -15, -20, -25, -40, -50 (Standard sizes)	-30 = 30 AWG -28 = 28 AWG	-G = 10µ" (0,25 µm) Gold on contact	"XX.XX" = Assembled Length in Inches (76,20 mm) 03.00" min. for -S end option (82,60 mm) 03.25" min. for -D end option	-S = Single Ended -D = Double Ended -T = Transfer End Terminal on End 1 Socket on End 2 (See chart for End 2 option) -TF* = Transfer End with Friction Lock -TR = Transfer End with Retention Latch (TFM -WT option required for mating) *-05 & -07 positions not available. TFSD, TFSDT only	Requires -D, -TF or -TR (End 1 Notch Down). -NUS = Notch up, straight (Pin 1 to Pin 2) -NDS = Notch down, straight (Pin 1 to Pin N-1) -NUS = Notch up, crossed (Pin 1 to Pin 1) (TFSD/TFSDT only) -NDX = Notch down, crossed (Pin 1 to Pin N) (TFSD/TFSDT only)
TFSST = Single Row *Teflon® Cable						
TFSD = Double Row PVC Cable						
TFSDT = Double Row *Teflon® Cable						

END 2	END OPTION
T-NUS	Pin 1 to Pin N
T-NDS	Pin 1 to Pin 1
T-NUS	Pin 1 and Pin N-1
T-NDX	Pin 1 to Pin 2

ALSO AVAILABLE (MOQ Required)

- Color coded cable (*Teflon® N/A)
 - Other plating options
- Contact Samtec.

*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Note: For wiring option and pin position location information, refer to drawings on web.

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TFSST-10-28-G-03.25-D-NUS](#) [TFSST-07-28-G-10.00-T-NUS](#) [TFSST-25-28-G-03.25-D-NUS](#) [TFSST-50-28-G-03.25-D-NDS](#) [TFSST-15-28-G-16.00-S](#) [TFSST-25-28-G-10.00-T-NUS](#) [TFSST-05-28-G-24.00-S](#) [TFSST-10-28-G-24.00-S](#) [TFSST-15-28-G-06.00-S](#) [TFSST-20-28-G-11.00-S](#) [TFSST-10-30-G-12.00-T-NUS](#) [TFSST-05-28-G-15.00-S](#) [TFSST-05-28-G-60.00-D-NUS](#) [TFSST-07-28-G-06.00-S](#) [TFSST-50-28-G-03.25-D-NUS](#) [TFSST-05-28-G-12.00-S](#) [TFSST-07-28-G-03.00-S](#) [TFSST-05-28-G-06.00-T-NUS](#) [TFSST-15-28-G-05.00-S](#) [TFSST-15-28-G-10.00-T-NUS](#) [TFSST-08-30-H-12.00-S](#) [TFSST-05-28-G-03.00-S](#) [TFSST-05-28-G-12.00-D-NUS](#) [TFSST-10-28-G-06.00-S](#) [TFSST-10-28-G-11.00-S](#) [TFSST-02-30-G-04.00-T-NUS](#) [TFSST-07-28-G-50.00-S](#) [TFSST-07-28-G-12.00-S](#) [TFSST-25-28-G-03.25-D-NDS](#) [TFSST-07-28-G-10.00-S](#) [TFSST-20-28-G-10.00-T-NUS](#) [TFSST-06-28-G-20.00-D-NUS](#) [TFSST-03-28-H-12.00-S](#) [TFSST-06-28-H-03.00-S](#) [TFSST-06-28-H-06.00-S](#) [TFSST-09-28-H-18.00-T-NUS](#) [TFSST-40-28-H-24.00-T-NUS](#) [TFSST-15-28-H-18.00-T-NUS](#) [TFSST-09-28-H-24.00-T-NUS](#) [TFSST-07-28-H-03.00-S](#) [TFSST-20-28-H-12.00-D-NDS](#) [TFSST-20-28-H-24.00-T-NUS](#) [TFSST-04-28-G-06.00-S](#) [TFSST-10-28-G-15.00-T-NUS](#) [TFSST-07-28-H-03.25-T-NUS](#) [TFSST-17-28-H-18.00-T-NUS](#) [TFSST-25-28-H-18.00-T-NUS](#) [TFSST-40-28-H-18.00-T-NUS](#) [TFSST-17-28-H-24.00-T-NUS](#) [TFSST-28-28-H-24.00-T-NUS](#) [TFSST-10-28-G-15.00-TR-NUS](#) [TFSST-10-28-H-18.00-T-NUS](#) [TFSST-14-28-H-18.00-T-NUS](#) [TFSST-14-28-H-24.00-T-NUS](#) [TFSST-22-28-H-18.00-T-NUS](#) [TFSST-22-28-H-24.00-T-NUS](#) [TFSST-07-28-H-24.00-T-NUS](#) [TFSST-25-28-H-24.00-T-NUS](#) [TFSST-10-28-H-24.00-T-NUS](#) [TFSST-28-28-H-18.00-T-NUS](#) [TFSST-20-28-H-18.00-T-NUS](#) [TFSST-10-28-G-10.00-S](#) [TFSST-15-28-H-24.00-T-NUS](#) [TFSST-20-28-G-06.00-S](#) [TFSST-07-28-H-18.00-T-NUS](#) [TFSST-02-28-H-03.00-S](#) [TFSST-10-28-G-36.00-S](#) [TFSST-15-28-H-03.00-S](#) [TFSST-15-28-G-10.00-S](#) [TFSST-02-28-G-04.00-S](#) [TFSST-04-30-F-06.00-S](#) [TFSST-10-28-G-06.00-D-NDS](#) [TFSST-15-28-H-12.00-S](#) [TFSST-02-30-F-06.00-S](#) [TFSST-15-28-G-36.00-S](#) [TFSST-08-30-F-06.00-S](#) [TFSST-10-28-H-06.00-D-NUS](#) [TFSST-04-28-H-03.00-S](#) [TFSST-21-30-H-12.00-D-NUS](#) [TFSST-25-28-H-12.00-S](#) [TFSST-25-28-G-36.00-S](#) [TFSST-02-28-H-08.00-S](#) [TFSST-10-28-H-12.00-S](#)