

**CLI C 02-3 GE/SW W MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                        |
|------------|------------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow |
| Order No.  | <a href="#">0252111683</a>                                             |
| Type       | CLI C 02-3 GE/SW W MP                                                  |
| GTIN (EAN) | 4008190098261                                                          |
| Qty.       | 200 pc(s).                                                             |

## CLI C 02-3 GE/SW W MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 3.5 mm | Depth (inches)  | 0.138 inch |
| Height     | 3 mm   | Height (inches) | 0.118 inch |
| Width      | 3.4 mm | Width (inches)  | 0.134 inch |
| Net weight | 0.03 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                              |                    |                                   |                                                |
|----------------------------------------------|--------------------|-----------------------------------|------------------------------------------------|
| Colour                                       | yellow             | Colour of printing                | black                                          |
| Halogen                                      | Yes                | Material                          | PVC, soft, without Cadmium                     |
| Material colour according to resistance code | 4                  | Number of markers per combination | 1 Component part = Conductor and cable markers |
| Operating temperature range                  | -30...80 °C        | Operating temperature range, max. | 80 °C                                          |
| Operating temperature range, min.            | -30 °C             | Orientation of print              | horizontal                                     |
| Printed characters                           | Upper-case letters | Printing                          | W                                              |
| Printing method                              | hot-embossing      | Recommended industries            | Process, Machinery                             |
| Type of printing                             | Standard           | UL 94 flammability rating         | V-0                                            |
| Version                                      | MultiPack          | Width                             | 3.4 mm                                         |

## Conductor and cable markers

|                               |                     |                                  |                           |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D.                | 1.3 - 3 mm          | Conductor O.D., max.             | 3 mm                      |
| Conductor O.D., min.          | 1.3 mm              | Conductor cross-section, max.    | 1.5 mm <sup>2</sup>       |
| Conductor cross-section, min. | 0.2 mm <sup>2</sup> | Cross-section for connected wire | 0.2 - 1.5 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI C 02-3 GE/SW W MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0252111683](#)