


SURFACE MOUNT .025" SQ POST HEADER

(2.54 mm) .100" PITCH • TSM SERIES

8
G b p s



TSM

Board Mates:

SSW, SSQ, SSM, BSW, ESW,
ESQ, BCS, SLW, CES, HLE

Cable Mates:

IDSS, IDSD

TSM

1

NO. PINS PER ROW

LEAD STYLE

02 thru 36

Specify
LEAD STYLE
from chart

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:


Au or Sn over
50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

Voltage Rating:

495 VAC/700 VDC -SV/-DV
mated with the BCS
405 VAC/573 VDC -SV/-DV
mated with the SSM



-SV Row Option

LEAD STYLE	POST HEIGHT	MATES WITH
-01	(5.84) .230	SSW, BCS, SSM, IDSS, IDSD
-02	(8.13) .320	SSM -DH
-03	(10.67) .420	Bottom Mount & Pass Through
-04	(3.05) .120	SLW, CES, HLE

PROCESSING

Lead-Free Solderable:

Yes

-DH/-SH/-SV Lead Coplanarity:

(0.15 mm) .006" max (02-36)*



-DV Lead Coplanarity:

(0.10 mm) .004" max (02-05)

(0.13 mm) .005" max (06-10)*

(0.15 mm) .006" max (11-36)*


*(.004" stencil solution
may be available; contact
ipg@samtec.com)



-SH Row Option

MATES	CURRENT RATING (PER PIN)
TSM/SSW	4.7 A
TSM/SSM	5.6 A
TSM/HLE	4.1 A
TSM/BCS	5.0 A

2 POSITIONS POWERED




-DV Row Option

Notes:

Severe Environment
Testing qualified; aligns
with MIL-DTL-55302.
Visit samtec.com/set

Some sizes, styles and
options are non-standard,
non-returnable.



PLATING OPTION

-F
= Gold flash on post, Matte Tin on tail

-L
= 10 μ " (0.25 μ m) Gold on post,
Matte Tin on tail

-S
= 30 μ " (0.76 μ m) Gold on post,
Matte Tin on tail

-T
= Matte Tin

ROW OPTION

-SV
= Single Row Vertical Pin

-DV
= Double Row Vertical Pin

-SH
= Single Row Horizontal Pin

-DH
= Double Row Horizontal Pin

-TM
= Triple Row Vertical Mixed Technology
(Style -01 only)
(02 thru 30 positions only)

-MT
= Mixed Technology Pin
(Style -01, -02 or -03 only)

OTHER OPTIONS

-"XXX"
= Polarized Position

-A
= Alignment Pin
metal or plastic at Samtec discretion
(Not available with -TM or -MT)
(02 positions minimum)
(Not available with -LC)




-LC
= Locking Clip
(Not available with -TM)
(3 positions minimum)
(Not available with -A)
(Manual placement required)

-K
= (6.50 mm) .256" DIA
Polyimide Film Pick & Place Pad
(-SH: 4 positions minimum without -TR;
2 & 3 positions available with -TR)
(-DH: 4 positions minimum without -TR)

-P
= Plastic Pick & Place Pad
(-DV: 4 positions minimum without -TR;
2 & 3 positions available with -TR)
(-SH: 4 positions minimum without -TR;
2 & 3 positions available with -TR)
(-DH: 5 positions minimum without -TR)
(-SV: 4 positions minimum without -TR;
2 & 3 positions available with -TR)

-TR
= Tape & Reel
-SV: 02-22 positions, -DV: 02-28 positions,
-SH: 02-30 positions, -DH: 02-29 positions
(Not available with -MT or -TM)

-FR
= Full Reel Tape & Reel
(must order maximum quantity per reel;
contact Samtec for quantity breaks)
-SV: 02-22 positions, -DV: 02-28 positions,
-SH: 02-30 positions, -DH: 02-29 positions
(Not available with -MT or -TM)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TSM-142-02-L-DH-A](#) [TSM-149-01-S-DH-A](#) [TSM-142-02-T-DH-A](#) [TSM-145-02-S-DH-A](#) [TSM-146-02-S-DH-A](#) [TSM-149-02-S-DH-A](#) [TSM-139-02-L-DH-A](#) [TSM-141-01-S-DH-A](#) [TSM-141-01-T-DH-A](#) [TSM-142-01-F-DH-A](#) [TSM-144-01-F-DH-A](#) [TSM-145-02-T-DH-A](#) [TSM-147-01-S-DH-A](#) [TSM-143-01-T-DH-A](#) [TSM-147-01-T-DH-A](#) [TSM-148-01-F-DH-A](#) [TSM-141-01-L-DH-A](#) [TSM-143-02-S-DH-A](#) [TSM-144-02-S-DH-A](#) [TSM-144-02-T-DH-A](#) [TSM-145-01-L-DH-A](#) [TSM-146-01-S-DH-A](#) [TSM-147-02-F-DH-A](#) [TSM-147-02-L-DH-A](#) [TSM-148-02-T-DH-A](#) [TSM-138-01-F-DH-A](#) [TSM-138-02-S-DH-A](#) [TSM-142-01-S-DH-A](#) [TSM-143-02-L-DH-A](#) [TSM-145-01-F-DH-A](#) [TSM-149-01-F-DH-A](#) [TSM-140-01-T-DH-A](#) [TSM-142-01-L-DH-A](#) [TSM-143-02-T-DH-A](#) [TSM-144-01-L-DH-A](#) [TSM-146-01-F-DH-A](#) [TSM-149-02-F-DH-A](#) [TSM-140-01-F-DH-A](#) [TSM-141-02-S-DH-A](#) [TSM-146-02-T-DH-A](#) [TSM-148-01-T-DH-A](#) [TSM-137-02-F-DH-A](#) [TSM-138-01-L-DH-A](#) [TSM-138-02-T-DH-A](#) [TSM-142-02-F-DH-A](#) [TSM-138-01-S-DH-A](#) [TSM-138-01-T-DH-A](#) [TSM-139-01-L-DH-A](#) [TSM-140-02-F-DH-A](#) [TSM-140-02-L-DH-A](#) [TSM-141-02-F-DH-A](#) [TSM-141-02-L-DH-A](#) [TSM-143-01-F-DH-A](#) [TSM-143-01-L-DH-A](#) [TSM-144-01-S-DH-A](#) [TSM-144-01-T-DH-A](#) [TSM-145-02-F-DH-A](#) [TSM-145-02-L-DH-A](#) [TSM-147-01-F-DH-A](#) [TSM-147-01-L-DH-A](#) [TSM-148-01-S-DH-A](#) [TSM-149-02-L-DH-A](#) [TSM-149-02-T-DH-A](#) [TSM-137-01-S-DH-A](#) [TSM-139-01-S-DH-A](#) [TSM-142-01-T-DH-A](#) [TSM-143-02-F-DH-A](#) [TSM-146-01-T-DH-A](#) [TSM-147-02-S-DH-A](#) [TSM-149-01-L-DH-A](#) [TSM-140-01-L-DH-A](#) [TSM-143-01-S-DH-A](#) [TSM-144-02-L-DH-A](#) [TSM-145-01-S-DH-A](#) [TSM-145-01-T-DH-A](#) [TSM-146-01-L-DH-A](#) [TSM-146-02-L-DH-A](#) [TSM-148-02-F-DH-A](#) [TSM-141-02-T-DH-A](#) [TSM-142-02-S-DH-A](#) [TSM-144-02-F-DH-A](#) [TSM-146-02-F-DH-A](#) [TSM-147-02-T-DH-A](#) [TSM-148-01-L-DH-A](#) [TSM-148-02-L-DH-A](#) [TSM-148-02-S-DH-A](#) [TSM-149-01-T-DH-A](#) [TSM-137-01-F-DH-A](#) [TSM-137-02-S-DH-A](#) [TSM-137-02-T-DH-A](#) [TSM-141-01-F-DH-A](#) [TSM-139-02-T-DH-A](#) [TSM-137-01-T-DH-A](#) [TSM-140-02-S-DH-A](#) [TSM-138-02-L-DH-A](#) [TSM-139-02-F-DH-A](#) [TSM-140-01-S-DH-A](#) [TSM-140-02-T-DH-A](#) [TSM-137-01-L-DH-A](#) [TSM-137-02-L-DH-A](#)