


**SAIL-M8WM8G-3-5.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

**General ordering data**

|            |   |
|------------|---|
| Version    | Sensor/actuator line, Connecting line, M8 / M8, Number of poles : 3, 5 m, pin, angled - bush straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">1073020500</a>  |
| Type       | SAIL-M8WM8G-3-5.0U  |
| GTIN (EAN) | 4032248831227   |
| Qty.       | 1 pc(s).  |

Creation date October 11, 2022 7:06:49 PM CEST

Catalogue status 07.10.2022 / We reserve the right to make technical changes.

**SAIL-M8WM8G-3-5.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 121 g

**Environmental Product Compliance**

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 1c533b66-fcff-4da5-b89f-fd55fbf5cb55 |
|------------|----------------|------|--------------------------------------|

**Technical specifications for cable**

|  |                                  |                                      |  |
|--|----------------------------------|--------------------------------------|--|
| Acceleration                                   | 5 m/s <sup>2</sup>               | Bending cycles                       | 12 Mio   |
| Bending cycles at torsion                      | > 5 Mio.                         | Bending radius, min., moving         | 10 x cable diameter  |
| Bending radius, min., stationary               | 5 x cable diameter               | Cable length                         | 5 m  |
| Colour coding                                  | brown, blue, black               | Configurable cable length            | No   |
| Core cross-section                             | 0.25 mm <sup>2</sup>             | Core in accordance with UL AWM style | 10493 (80 °C / 300 V)  |
| Halogen  | No                               | Hydrolysis and microbe resistant     | Yes  |
| Insulation                                     | PP                               | Irradiation crosslinked              | No   |
| Length of torsion                              | 1 m                              | Number of poles                      | 3  |
| Outer cladding in accordance with UL AWM style | 20549 (80 °C / 300 V)            | Outside diameter                     | 4.1 mm ± 0.2 mm  |
| Resistance to oils                             | in accordance with IEC 60811:404 | Resistance to spread of flame        | in accordance with IEC 60332-2-2, In accordance with UL1581 UL / CUL FT2 |
| Resistant to welding beads                     | No                               | Sheath material                      | PUR  |
| Sheathing colour                               | black                            | Shielded                             | No   |
| Speed  | 5 m/s                            | Suitable for cable carriers          | Yes  |
| Temperature range, moving                      | -25...80 °C                      | Temperature range, stationary        | -40...80 °C  |
| Torsion resistance                             | 360 °/m                          | Welding spark resistance             | No   |

**General technical data**

|                        |   |                              |                  |
|------------------------|---|------------------------------|------------------|
| Coding                 | A   | Connection thread            | M8 / M8          |
| Contact surface        | Gold-plated                                   | Housing main material        | PUR              |
| Insulation strength    | 10 <sup>8</sup> Ω                             | LED                          | No               |
| Plugging cycles        | ≥ 100   | Pollution severity           | 3                |
| Protection degree      | IP65, IP66, IP67, IP68, when screwed in, IP69 | Rated current                | 4 A              |
| Rated voltage          | 60 V  | Temperature range of housing | -40 ... +85 °C   |
| Threaded ring material | Brass, nickel-plated                          | Tightening torque            | M8: 0.5 - 0.6 Nm |
| Version                | pin, angled - bush straight                   | jumpered                     | No               |

**Electrical properties**

|                     |                   |               |      |
|---------------------|-------------------|---------------|------|
| Insulation strength | 10 <sup>8</sup> Ω | Rated voltage | 60 V |
|---------------------|-------------------|---------------|------|

**General standards**

|                         |         |                    |                 |
|-------------------------|---------|--------------------|-----------------|
| Certificate no. (cULus) | E307231 | Connector standard | IEC 61076-2-104 |
|-------------------------|---------|--------------------|-----------------|

**Standards**

|                    |                 |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-104 |
|--------------------|-----------------|

**SAIL-M8WM8G-3-5.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001855    | ETIM 7.0    | EC001855    |
| ETIM 8.0    | EC001855    | ECLASS 9.0  | 27-06-03-11 |
| ECLASS 9.1  | 27-06-03-11 | ECLASS 10.0 | 27-06-03-11 |
| ECLASS 11.0 | 27-06-03-11 | ECLASS 12.0 | 27-06-03-11 |

**Approvals**

Approvals



|                         |         |
|-------------------------|---------|
| ROHS                    | Conform |
| Certificate no. (cULus) | E307231 |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">EPLAN, WSCAD</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        | <a href="#">FL FIELDWIRING EN</a>        |

## SAIL-M8WM8G-3-5.0U

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



Male, angled

### Pole scheme



Male

### Wiring diagram



### Dimensioned drawing



Straight socket

### Pole scheme



Socket

### The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1073020500](#)