

KEBI QL 504022 S2B0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

For many years, the name Klippon® has stood for competence and quality in enclosures.

The Klippon® EBi industrial enclosure series protects your components reliably if they are used in moderate environmental conditions and is designed for everyday applications. With the ever-increasing need for individual application solutions, the Klippon® EBi with its high degree of protection and impact resistance is ideally suited to your needs.

Our standard product is the Klippon® EBi QL – with hinged door and double-bit key lock.

A variant with mounting screws is also available, but is only manufactured on request and is subject to a minimum order quantity. DNV GL and cULus approvals are also available on request.

General ordering data

Version	Klippon EBi QL (Essential Box industrial - Quarter Lock), Empty enclosure, stainless steel enclosure, Height: 500 mm, Width: 400 mm, Depth: 220 mm, Material: Stainless steel 1.4301 (304), Brushed, silver
Order No.	2470750000
Type	KEBI QL 504022 S2B0
GTIN (EAN)	4050118591224
Qty.	1 pc(s).

KEBI QL 504022 S2B0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	220 mm	Depth (inches)	8.661 inch
Height	500 mm	Height (inches)	19.685 inch
Width	400 mm	Width (inches)	15.748 inch
Diameter	9 mm	Mounting dimension - height	450 mm
Mounting dimension - width	350 mm	Wall thickness, min.	1.5 mm
Wall thickness, max.	1.5 mm	Net weight	10,279.3 g

Temperatures

Operating temperature	-40 °C...85 °C	Operating temperature range	-40 °C to 85 °C
-----------------------	----------------	-----------------------------	-----------------

Cable glands, left

M12	140	M16	85
M20	52	M25	33
M32	27	M40	14
M50	10	M63	4
M75	3		

Cable glands, right

M12	140	M16	85
M20	52	M25	33
M32	27	M40	14
M50	10	M63	4
M75	3		

Cable glands, top/bottom

M12	112	M16	65
M20	40	M25	24
M32	21	M40	10
M50	8	M63	3
M75	2		

Certificate numbers enclosure

Approval conditions	cULus	Certificate No. (DNVGL)	TAE00002RN
Certificate no. (cULus)	E243298	Declaration of Conformity No. (DoC LVD)	DE PS2650 180129 001ISS00

KEBI QL 504022 S2B0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General information

Access opening: height	443 mm	Access opening: width	343 mm
Areas of use	Harbour facilities, Machine construction, Transportation, Marine engineering, Packaging industry, Process industry	Enclosure attachment	Fixing lugs, Installation through the housing rear wall
Flange plate	No	Impact resistance	10.00 J
Integral fixing	Screwed	Lid	Yes
Lid attachment	Quarter-turn fastener with slotted insert	Material	Stainless steel 1.4301 (304)
Material thickness of cover	1.5 mm	Material thickness of enclosure	1.5 mm
Opening angle lid	125 °	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Protection class (UL)	Type 3, Type 4x, Type 5
Protection degree	IP66	Seal material	Polyurethane foamed
Seal material of cover	Polyurethane foamed	Standards	DIN EN 62208, IEC 60529
Surface finish	Brushed		

Housing earth

Earth, enclosure, cover	Welded-on M6 stainless- steel earth stud in enclosure body and lid.	Earth, enclosure, external	M6 earth tab rivet
Earth, enclosure, internal	Welded-on M6 stainless- steel earth stud in enclosure body and lid.		

horizontal assembly

WDU 10 / ZDU 10	6x28	WDU 16 / ZDU 16	6x23
WDU 2,5 / ZDU 2,5 / IDU 2,5	6x56	WDU 35 / ZDU 35	6x18
WDU 4 / ZDU 4	6x47	WDU 6 / ZDU 6	6x35

vertical assembly

WDU 10 / ZDU 10	4x38	WDU 16 / ZDU 16	4x32
WDU 2,5 / ZDU 2,5 / IDU 2,5	4x75	WDU 35 / ZDU 35	4x24
WDU 4 / ZDU 4	4x63	WDU 6 / ZDU 6	4x47

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E243298

Creation date September 17, 2022 11:02:18 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

KEBI QL 504022 S2B0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	TAE00002RN Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Mounting Instructions Empty enclosures Klippon
Catalogues	Catalogues in PDF-format


KEBI QL 504022 S2B0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2470750000](#)