

**H1,0/14S GE BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

|            |                                                 |
|------------|-------------------------------------------------|
| Version    | Wire-end ferrule, Standard, 10 mm, 8 mm, yellow |
| Order No.  | <a href="#">2528570000</a>                      |
| Type       | H1,0/14S GE BD GSP                              |
| GTIN (EAN) | 4050118539059                                   |
| Qty.       | 4,000 pc(s).                                    |

**H1,0/14S GE BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 0.105 g |
|------------|---------|

**Technical data**

|                        |                                   |         |          |
|------------------------|-----------------------------------|---------|----------|
| Description of article | Wire end ferrules on reel, yellow | Version | Standard |
|------------------------|-----------------------------------|---------|----------|

**Wire-end ferrules**

|                             |                   |                                         |            |
|-----------------------------|-------------------|-----------------------------------------|------------|
| Collar diameter (D2)        | 3.5 mm            | Colour code                             | Weidmüller |
| Conductor cross-section     | 1 mm <sup>2</sup> | Contact surface diameter (D1)           | 1.4 mm     |
| Contact surface length (L2) | 8 mm              | L1 in mm                                | 14 mm      |
| Metal sleeve thickness (S1) | 0.15 mm           | Plastic collar thickness (S2)           | 0.25 mm    |
| Stripping length            | 10 mm             | Wire connection cross section AWG, max. | AWG 18     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ECLASS 9.0  | 27-40-02-01 |
| ECLASS 9.1  | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

**Approvals**

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E354986    |

**Downloads**

|                    |                                                                                          |
|--------------------|------------------------------------------------------------------------------------------|
| Engineering Data   | <a href="#">EPLAN</a>                                                                    |
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                                 |

## H1,0/14S GE BD GSP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Drawing



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2528570000](#)