

RCMA-B22-D70-1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Rogowski coil**

A Rogowski coil is a closed air coil without a ferromagnetic core used for floating potential measurement of AC and pulse currents. Measurement with the Rogowski coil is used widely in technology, as it can be retroactively integrated without separating the primary electric circuit in existing systems. Because this method shows no saturation effect, even the smallest currents and high-frequency harmonics can be measured without loss of accuracy.

General ordering data

Version	Rogowski coil, Diameter: 70 mm, Cable length: 1.5 m
Order No.	2593370000
Type	RCMA-B22-D70-1.5
GTIN (EAN)	4050118647815
Qty.	1 pc(s).

RCMA-B22-D70-1.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Diameter	70 mm	Net weight	120 g
----------	-------	------------	-------

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Humidity at operating temperature	5 - 90 %, no condensation		

Electrical attributes

Frequency band	50...60 Hz	Nominal turns ratio	44.44 kA/V
Phase shift	0.004 °	Primary conductor temperature	105 °C
Primary current	5,000 A	Secondary voltage	22,5 mV (@ 50Hz I _{primary} = 1 kA), 30 V (max)
Tolerance class	0,5		

Technical data

Protection degree	Standards	IEC 61010-1: 2010, UL 61010-1, IEC 61869-1: 2007, IEC 61869-2: 2012, IEC 61869-6: 2016, IEC 61869-10: 2017
IP57		

Technical properties

Cable diameter	6.1 mm	Cable length	1.5 m
Coil resistance	56 Ω	Protection degree	IP57

General data

Linearity	Standard	IEC 61010-1: 2010, IEC 61869-1: 2007, IEC 61869-2: 2012, IEC 61869-6: 2016, IEC 61869-10: 2017, UL 61010-1
no linearity error		

Insulation coordination

Clearance & creepage distances	>16 mm	Impulse withstand voltage	12.8 kV (1.2/50 ms)
Insulation voltage	7.4 kV _{RMS} (50 Hz, 1 min)	Partial discharge voltage	1.65 kV _{Effective} (q _m <10 pC, IEC 60664-1)
Standard	IEC 61010-1: 2010, IEC 61869-1: 2007, IEC 61869-2: 2012, IEC 61869-6: 2016, IEC 61869-10: 2017, UL 61010-1	Tolerance class	0,5
Tracking resistance (CTI)	600		

Classifications

ETIM 6.0	EC002475	ETIM 7.0	EC002475
ETIM 8.0	EC002475	ECLASS 9.0	27-21-01-23
ECLASS 9.1	27-21-01-23	ECLASS 10.0	27-21-01-23
ECLASS 11.0	27-21-01-23	ECLASS 12.0	27-21-01-23

RCMA-B22-D70-1.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Important note

Product information

The Rogowski coil **RCMA-B22-DXX** is intended for the electronic measurement of alternating current. The Rogowski coil must only be used in conjunction with a Weidmüller transducer RCMC-5000-XX.

Functional description

The primary circuit (power circuit) and the secondary circuit (measurement circuit) are galvanically isolated by the Rogowski coil.

As there is no saturation effect, currents can be measured over a wide primary current range without any losses in accuracy.

Features

- Conductor diameter of the measuring coil: 6.1 mm
- Housing tabs for attachment with cable ties
- Sealable bayonet fastening

Approvals

Approvals



ROHS	Conform
------	---------

UL File Number Search	UL Website
-----------------------	------------

Certificate No. (UL)	E469563
----------------------	---------

Certificate No. (cURus)	E469563
-------------------------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
---	---

User Documentation	Instruction sheet
--------------------	-----------------------------------

Catalogues	Catalogues in PDF-format
------------	--


RCMA-B22-D70-1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2593370000](#)