

WAS5 DC/ALARM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Limit value monitoring, Input : 0-20 mA, 0-10 V, Output : 2 x relays
Order No.	8543820000
Type	WAS5 DC/ALARM
GTIN (EAN)	4032248181230
Qty.	1 pc(s).

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	112.4 mm	Depth (inches)	4.425 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	92.4 mm	Length (inches)	3.638 inch
Net weight	110.1 g		

Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	0 °C...55 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Probability of failure

MTTF	369 Jahre
------	-----------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	c2a21576-d875-4548-ae68-5e7f85ddf0c7
------------	----------------	------	--------------------------------------

Input

Input current	0(4)...20 mA	Input resistance, current	≤ 110 Ω
Input resistance, voltage	≥ 100 kΩ	Input voltage	0...10 V
Number of inputs	1		

Output

Contact material	AgNi 90/10	Status indicator	LED green ON: OK, LED red ON: alarm (per channel)
Switching thresholds	1...90 % (independently for channel 1 and channel 2)		

Output (digital)

Alarm function	configurable, High or low alarm, Hysteresis 5% / 10%	Contact material	AgNi 90/10
Continuous current	3 A	Hysteresis	1...10 % (independent for channel 1 and channel 2)
Max. switching voltage, AC	250 V	Type	2 CO contacts, Open or closed-circuit principle

General data

Accuracy	Repeat accuracy: max. ± 0.3% of measuring range end value (10 V/ 20 mA)	Configuration	DIP switch, Potentiometer
Current-carrying capacity of cross-connect.	≤ 2 A	Galvanic isolation	3-way isolator
Input/Output	0...10 V, 0(4)...20 mA / 2 CO contact	Power consumption	Typ.: 1 W both relays picked up
Rail	TS 35	Temperature coefficient	≤ 500 ppm/K
Type of connection	Screw connection	Voltage supply	24 V DC ± 25 %

Creation date September 18, 2022 3:40:36 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

Clearance & creepage distances	≥ 3 mm	EMC standards	EN 61000-4-2, -3, -4, -5, -6
Galvanic isolation	3-way isolator	Impulse withstand voltage	4 kV
Insulation voltage	2 kV _{eff} / 5 s	Pollution severity	2
Rated voltage	300 V	Surge voltage category	III

Connection data

Type of connection	Screw connection	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-20	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20	ECLASS 12.0	27-21-01-20

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Limit-value monitoring component for DC-current/ voltage standard signals with relay output and 3-way electrical isolation.

Limit-value monitoring component in 22.5 mm width for recording 0(4)...20 mA / 0...10 V standard signals. Two relay contacts (COs), each with a switching capacity of 750 VA, are available on the output side for monitoring an upper and lower limit. The switching behaviour (high/low trip, fail-safe) can be selected using DIP switches. Switching thresholds and hystereses can be adjusted with the front-side potentiometer. The component has 4 kV of 3-way isolation and is supplied externally with 24 VDC.

Add-on housing for TS35 rail mounting
Dimensions: L/W/H
92.4/ 22.5/ 112.4 mm
Screw connection /
Nominal cross-section
2.5 mm²
Protection degree: IP
20
Input
0(4)...20 mA / 0...10 V
Output
2 x relay / CO

Open-circuit/closed-circuit principle
Switching current 3 A
Switching voltage 6...250 V AC / 6...60 V DC
Switching thresholds 1...90 % via potentiometer (independently for channels 1 and 2)
Hysteresis 1% ... 10 % via potentiometer (independently for channels 1 and 2)
Temperature coefficient < 500 ppm/K
Step response time < 60 ms

Auxiliary power 24 VDC ± 25 %

Ambient temperature -40...70 °C

Short specification

Limit-value monitoring component for DC-current/voltage standard signals with relay output and 3-way electrical isolation.

Limit-value monitoring component in 22.5 mm width for recording 0(4)...20 mA / 0...10 V standard signals. Two

WAS5 DC/ALARM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Important note**

Product information

This product will soon be replaced by a new product.

Please do not use with new systems. Please contact our technical support.

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	20220218 Technical change - WAVE series' signal conditioners WS WZ
User Documentation	instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	


WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings


Connection diagram



Example 1



Example 2



Switch position/setting options

function	SW 1			
	1	2	3	4
Channel A High Trip	■			
Channel A Low Trip	□			
Channel B High Trip		■		
Channel B Low Trip		□		
FAILSAFE, Channel 1 & 2			□	□
NON FAILSAFE, Chan. 1 & 2			■	■

■ = on
 □ = off

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8543820000](#)