

(2.00 mm) .0787"

YTS, YTQ SERIES

HIGH-DENSITY SOCKET STRIP

SPECIFICATIONS

For complete specifications see www.samtec.com?YTS or www.samtec.com?YTQ

Insulator Material:
Black Liquid Crystal Polymer

Contact Material:
Phosphor Bronze

Operating Temp Range:
-55 °C to +125 °C

Plating:

Sn or Au over 50 μ " (1.27 μ m) Ni

Insertion Depth:
(2.62 mm) .103" to (5.03 mm) .198"

Max Cycles:
100 with 10 μ " (0.25 μ m) Au

RoHS Compliant:
Yes

PROCESSING

YTS Lead-Free Solderable:
Wave Only




YTQ Lead-Free Solderable:
Wave or reflow with Matte Sn plating

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality





Mates with:
YTT, YTW, YTE, TMMS



LEAD STYLE	A
-01	(2.29) .090
-02	(15.24) .600
-03	(5.28) .208

TYPE SOCKET	B
YTS	(0.25) (0.51) .010 x .020
YTQ	(0.51) .020 SQ



Note:
Some lengths, styles and options are non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[YTS-103-01-F-5](#) [YTS-112-01-L-Q](#) [YTS-120-01-S-6](#) [YTS-121-01-F-Q](#) [YTS-132-01-L-5](#) [YTS-150-01-L-Q](#) [YTS-132-01-L-6-111](#) [YTS-150-01-S-6](#) [YTS-102-01-F-5](#) [YTS-116-01-F-5](#) [YTS-120-01-L-6](#) [YTS-122-01-S-Q](#) [YTS-140-01-F-Q](#) [YTS-150-01-G-5](#) [YTS-106-01-F-Q](#) [YTS-115-01-L-Q](#) [YTS-125-01-F-6](#) [YTS-126-01-L-6](#) [YTS-133-01-L-Q](#) [YTS-137-01-L-Q](#) [YTS-106-01-L-6](#) [YTS-108-01-L-Q](#) [YTS-110-01-L-Q](#) [YTS-120-01-F-5](#) [YTS-125-01-L-5](#) [YTS-125-01-L-6](#) [YTS-140-01-L-Q](#) [YTS-103-01-L-Q](#) [YTS-104-01-F-5](#) [YTS-104-01-L-5](#) [YTS-113-01-L-Q](#) [YTS-120-01-S-Q](#) [YTS-122-01-F-6](#) [YTS-130-01-L-Q](#) [YTS-132-01-F-Q](#) [YTS-112-01-L-Q-020](#) [YTS-112-01-L-Q-022](#) [YTS-122-01-L-Q](#) [YTS-107-01-L-Q](#) [YTS-108-01-F-5](#) [YTS-125-01-L-Q](#) [YTS-125-01-S-Q](#) [YTS-140-01-L-6](#) [YTS-116-01-L-6](#) [YTS-116-01-L-Q](#) [YTS-119-01-L-6](#) [YTS-140-01-L-Q-070](#) [YTS-144-01-F-5](#) [YTS-105-01-L-Q](#) [YTS-112-01-F-Q](#) [YTS-115-01-F-Q](#) [YTS-150-01-F-5](#) [YTS-150-01-L-5](#) [YTS-105-01-S-Q](#) [YTS-110-01-S-Q](#) [YTS-115-01-L-5](#) [YTS-124-01-L-Q](#) [YTS-130-01-F-6](#) [YTS-133-01-F-5](#) [YTS-144-01-L-6](#) [YTS-105-01-F-5](#) [YTS-112-01-F-6](#) [YTS-120-01-F-Q](#) [YTS-130-01-L-6](#) [YTS-135-01-L-6](#) [YTS-111-01-L-5](#) [YTS-120-01-L-5](#) [YTS-120-01-L-Q](#) [YTS-123-01-F-5](#) [YTS-130-01-F-Q](#) [YTS-136-01-F-5](#) [YTS-130-01-H-5](#) [YTS-120-01-G-5](#) [YTS-120-01-L-5-006](#) [YTS-118-01-F-6](#) [YTS-122-01-F-Q](#) [YTS-125-01-L-Q-006](#) [YTS-102-01-F-6](#) [YTS-117-01-L-6](#) [YTS-102-01-FM-5](#) [YTS-104-01-FM-5](#) [YTS-110-01-L-5](#) [YTS-117-01-L-5](#) [YTS-140-01-F-6](#) [YTS-114-01-L-Q](#) [YTS-112-01-FM-6](#) [YTS-130-01-F-Q-118](#) [YTS-103-01-S-Q](#)