

SHROUDED .025" SQ POST HEADERS

(2.54 mm) .100" PITCH • TSS/HTSS/ZSS SERIES



TSS/HTSS/ZSS

Mates:
SSW, SSQ, ESW, ESQ,
SSM, BCS

SPECIFICATIONS

Insulator Material:
TSS, ZSS=Black Glass Filled Polyester
HTSS=Natural PCT
Insulation Resistance:
5000 MΩ min
Terminal Material:
Phosphor Bronze
Plating: Au or Sn over 50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin
Withstanding Voltage:
1000 VRMS

PROCESSING

Lead-Free Solderable:
HTSS=Yes
TSS, ZSS=No, Lead Wave only
SMT Lead Coplanarity:
(0.15 mm) .006" max*
*(.004" stencil solution may be available; contact ipg@samtec.com)

SERIES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION
--------	---	------------------	------------	----------------	------------

TSS
= Connector Strip
HTSS
= High Temp Connector Strip

03
(TSS only)
05, 07, 08, 10, 12, 13, 15, 17, 20, 25, 32, 36
(Standard sizes)

Specify LEAD STYLE from chart

-F
= Gold flash on post, Matte Tin on tail
(Not available on -DV)

-L
= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail



-T
= Matte Tin

-D
= Double Row Through-hole (lead style -01, -02 & -03 only)


-DV
= Double Row Surface Mount (lead style -01 only) (HTSS only)

-D-RA
= Double Row Right-angle (lead style -04 & -05 only)

LEAD STYLE	T/H (A)
-01	(2.92) .115
-02	(4.19) .165
-03	(14.35) .565



-DV
(HTSS ONLY)



-D-RA

LEAD STYLE	RIGHT ANGLE (B)
-04	(3.30) .130
-05	(5.84) .230

ZSS	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	BODY HEIGHT
-----	---	------------------	------------	----------------	---	-------------

03, 05, 07, 08, 10, 12, 13, 15, 17, 20, 25, 32, 36
(Standard sizes)




Specify LEAD STYLE from chart

-F
= Gold flash on post, Matte Tin on tail

-L
= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

-T
= Matte Tin

"XXXX"
= Body Height



LEAD STYLE	C (OAL)	MAX BODY HEIGHT
-01	(16.00) .630	(13.72) .540
-02	(18.54) .730	(16.26) .640
-03	(21.08) .830	(18.80) .740
-04	(23.62) .930	(21.34) .840
-05	(26.16) 1.030	(23.88) .940
-06	(28.70) 1.130	(26.42) 1.040
-07	(31.24) 1.230	(28.96) 1.140
-08	(33.78) 1.330	(31.50) 1.240
-09	(36.32) 1.430	(34.04) 1.340

Note:
Some lengths, styles and options are non-standard, non-returnable. ZSS is non-standard, non-returnable.

Note:
For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[ZSS-117-02-L-D-630](#) [ZSS-120-03-G-D-710](#) [ZSS-122-08-H-D-1210](#) [ZSS-125-05-S-D-880](#) [ZSS-103-08-F-D-1093](#)
[ZSS-103-08-T-D-1165](#) [ZSS-106-08-F-D-1093](#) [ZSS-107-02-G-D-624](#) [ZSS-107-05-L-D-910](#) [ZSS-108-01-G-D-484](#) [ZSS-108-07-S-D-755](#) [ZSS-110-03-L-D-640](#) [ZSS-111-07-F-S-1040](#) [ZSS-112-01-L-D-500](#) [ZSS-112-03-S-D-670](#) [ZSS-113-04-L-D-760](#) [ZSS-115-04-T-D-780](#) [ZSS-120-04-G-D-800](#) [ZSS-120-08-G-D-1170](#) [ZSS-125-06-G-D-1023](#) [ZSS-105-07-G-D-1040](#) [ZSS-110-01-G-D-470](#) [ZSS-110-07-L-D-1140](#) [ZSS-110-08-L-D-1140](#) [ZSS-110-08-S-D-1110](#) [ZSS-112-04-L-D-840](#) [ZSS-112-05-S-D-940](#) [ZSS-116-01-F-D-466](#) [ZSS-125-04-L-D-785](#) [ZSS-132-04-T-D-781](#) [ZSS-112-03-S-D-615](#) [ZSS-112-08-L-D-1240](#) [ZSS-113-03-L-D-740](#) [ZSS-115-08-S-D-1194](#) [ZSS-117-04-S-D-790](#) [ZSS-118-07-S-D-1088](#) [ZSS-120-01-G-D-512](#) [ZSS-120-03-G-D-540](#) [ZSS-120-04-G-D-750-LL](#) [ZSS-120-08-S-D-1125](#) [ZSS-125-08-T-D-1240-LL](#) [ZSS-132-03-S-D-702](#) [ZSS-136-01-G-D-530](#) [ZSS-104-01-S-D-540](#) [ZSS-105-04-L-D-765](#) [ZSS-105-04-S-D-760](#) [ZSS-107-01-L-D-450](#) [ZSS-107-05-G-D-875](#) [ZSS-108-07-G-D-1140](#) [ZSS-110-02-L-D-623](#) [ZSS-110-04-S-D-830](#) [ZSS-115-05-S-D-892](#) [ZSS-117-05-S-D-855](#) [ZSS-120-01-G-D-530](#) [ZSS-120-02-L-D-470](#) [ZSS-120-09-T-D-1300](#) [ZSS-132-02-G-D-620](#) [ZSS-136-04-G-D-735](#) [ZSS-110-05-S-D-905-20](#) [ZSS-112-01-L-D-505](#) [ZSS-112-01-S-D-480](#) [ZSS-113-02-G-D-593](#) [ZSS-115-04-T-D-670](#) [ZSS-115-05-S-D-865](#) [ZSS-117-06-S-D-1039](#) [ZSS-125-01-L-D-505](#) [ZSS-136-05-G-D-940](#) [ZSS-107-04-H-D-750](#) [ZSS-107-04-L-D-820-LL](#) [ZSS-107-05-L-D-890](#) [ZSS-108-03-G-D-646](#) [ZSS-110-02-G-D-623](#) [ZSS-110-02-G-D-624](#) [ZSS-110-02-L-D-566](#) [ZSS-110-03-G-D-700](#) [ZSS-110-06-H-D-1010](#) [ZSS-110-09-T-D-1265](#) [ZSS-113-03-L-D-682](#) [ZSS-115-03-T-D-664](#) [ZSS-120-09-L-D-1320](#) [ZSS-125-07-S-D-1140](#) [ZSS-130-09-S-D-1140](#) [ZSS-132-01-S-D-455](#) [ZSS-114-02-S-D-540](#) [ZSS-115-08-G-D-1148](#) [ZSS-118-01-L-D-540](#) [ZSS-132-04-G-D-735](#) [ZSS-105-03-L-D-710](#) [ZSS-105-09-L-D-1340-LL](#) [ZSS-107-09-G-D-1270](#) [ZSS-108-01-G-D-540-LL](#) [ZSS-108-08-L-D-1240](#) [ZSS-110-04-L-D-790](#) [ZSS-110-06-G-D-1008](#) [ZSS-112-03-L-D-670](#) [ZSS-114-05-G-D-760](#) [ZSS-132-04-S-D-662](#) [ZSS-136-02-G-D-640](#) [ZSS-136-09-L-D-1320](#) [ZSS-132-09-T-D-1325-LL](#)