


SD1765-1



NOTES:

1. FOR USE WITH RG-8, 8A, 11, 11A & 213/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE 3-7-2.
3. FOR CABLE TRIMMING USE KTJ-124 & KTD-179.
4. FOR CRIMPING USE DIE KTH-1078.
5. MATERIALS:
 - INSULATOR: HIGH DENSITY POLYETHYLENE, MIL-P-22748
 - GASKETS: SIL. RUB., ZZ-R-765
 - K-GRIP SLEEVE: COM. BRONZE TUBE, ALLOY 220
 - CONTACT: BER. COP., ASTM-B-196
 - SPRING: STAINLESS STEEL, TYPE 302
 - ALL OTHER PARTS: BRASS, ASTM-B16
6. FINISHES:
 - CENTER CONTACT: HARD GOLD PLATE PER MIL-G-45204
 - SPRING: PASSIVATE PER QQ-P-35
 - ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
7. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: NON-CONSTANT
 - VOLTAGE RATING: 20 KVDC
 - INSULATION RESISTANCE: 10^6 MEGOHMS
 - CURRENT CARRYING CAPACITY: 25 AMPS @ 30°C TEMP RISE

REVISIONS

ISSUE	CHANGES	
	DATE	DESCRIPTION
4	10/30/92	CN 34190 C REDRAWN JCA
5	11/24/99	CN 37941 E HVN
6	11/22/06	CN 39710 C DRK
H	12/03/2009	REVISED PER ER ER20507 GGR

CUSTOMER
SALES DRAWING

SCALE 2:1

APPROX SURFACE AREA

USED ON

REF:

PLUG, 20 KV

DRAWN	JCA	DATE	10/30/92
DESIGN	LI	DATE	11/02/92
APPR.		DATE	

KINGS
by WINCHESTER
Winchester Electronics
62 Barnes Industrial
Road North
Wallingford, CT 06492

SD1765-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bomar Interconnect:](#)

[1765-1](#)