

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

MATERIALS:

- SST, CORROSION-RESISTANT, NON MAGNETIC 303, PER ASTM A484 AND
- A582, BERYLLIUM COPPER UNS C17300 PER ASTM B196, TD04, QQ-C-530
- OXIDE-NORYL (TM). MIL-P-46129.


FINISH:

- CENTER CONDUCTORS AND SOLDER COMPONENTS SHALL BE GOLD PLATED PER MIL-G-45204 TYPE II, CLASS 1 OVER NICKEL PLATE PER QQ-N-290. BODY AND BODY COMPONENTS SHALL BE PASSIVATED PER AMS2700.



PERFORMANCE:

- FREQUENCY: DC-40GHz
- VSWR: 1.25 MAX.
- INSERTION LOSS: .32 dB
- OPERATING TEMP: -55°C TO 125°C
- IMPEDANCE: 50Ohms Nom.

REV	DESCRIPTION	DATE	APPD
-	REL	04/03	LMW
A	ECO-13227	11/24/20	LA



CUSTOMER OUTLINE DRAWING

MATERIAL	DO NOT SCALE DRAWING	DRAWN LMW	DATE 04/03	 Winchester Interconnect _{LLC} 68 Water St Norwalk, CT 06854		
	UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS: $\pm 1/64$.XX: $\pm .01$.XXX: $\pm .005$ ANGLES: $\pm 2^\circ$	ENG APPR.	DATE			
		MFG APPR.	DATE			
		OTHER APPR.	DATE			
COMMENTS:	THIRD ANGLE PROJECTION 	TITLE: 2.9 MM JACK TO 2.9 MM JACK		SIZE B	DWG. NO. 25-925-0000-90	REV A
surface area: sq inch		weight: lbs	PER ASME Y14.5M-1994			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[25-925-0000-90](#)