



Features

- Carbon element
- Plain or knurled shaft option
- Metal bushing
- Metal shaft
- Rear solder lugs
- Audio or linear taper options
- Variety of resistance values



- Detent at "no-load" position
- RoHS compliant*

PDB241-GNL Series - "No-Load" Guitar Potentiometer

Electrical Characteristics

Taper.....Audio, linear
Standard Resistance.....10K to 1M ohms
Standard Resistance Tolerance.....±20 %


Environmental Characteristics

Operating Temperature
.....-10 °C to +70 °C
Power Rating.....0.25 watt
Maximum Operating Voltage.....250 V
Rotational Noise.....150 mV max.

Mechanical Characteristics

Mechanical Angle.....300° ±5°
Rotational Torque.....10 to 45 g-cm
Stop Strength.....8 kg-cm min.
Rotational Life.....15,000 cycles min.
Detent Position.....300°
Detent Torque.....100-300 gf-cm
Soldering Condition
Manual Soldering
.....300 °C within 3 seconds
Wave Soldering
.....260 °C within 3 seconds
Hardware.....Two flat washers
and two mounting nuts supplied
per potentiometer


Derating Curve




Standard Resistance Table

Resistance (Ohms)	Resistance Code
10,000	103
25,000	253
50,000	503
100,000	104
250,000	254
300,000	304
500,000	504
1,000,000	105

Product Dimensions



Circuit



How To Order



PDB24 1 - GNL 01 - 504 A2

Model _____
 Number of Units _____
 1 = Single
 Guitar Pot Designator _____
 Configuration _____
 01 = Knurled Shaft (18-Tooth) / Solder Lugs
 02 = Plain Shaft / Solder Lugs
 03 = Knurled Shaft (18-Tooth, Long) / Solder Lugs
 04 = Plain Shaft (Long) / Solder Lugs
 11 = Knurled Shaft (24-Tooth) / Solder Lugs
 13 = Knurled Shaft (24-Tooth, Long) / Solder Lugs
 Resistance Code (See Table) _____
 Resistance Taper (See Taper Charts) _____

PDB241-GNL Series - “No-Load” Guitar Potentiometer

BOURNS®

Taper Chart



Inquire for availability of other tapers.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[PDB241-GNL11-254B0](#) [PDB241-GNL11-504B0](#) [PDB241-GNL13-504B0](#) [PDB241-GNL13-254B0](#) [PDB241-GNL11-254A2](#) [PDB241-GNL13-504A2](#) [PDB241-GNL11-504A2](#)