




Features

- IEEE 802.3u (100Base-T) compliant
- MECHATROLINK-III compliant
- Hi-Pot: 2250 VDC or 1500 VAC
- Additional metal shield for surge immunity and superior EMC performance
- Compliant to IEC 61000-4-5 surge immunity test level 3 (2000 V)
- RoHS compliant*

SM91076L - 10/100 Base-T Transformer

Electrical Specifications @ 25 °C

OCL (-40 ~ +125 °C)	350 μ H min @ 100 kHz, 0.1 V, 8 mA DC bias
Leakage Inductance	0.5 μ H max. @ 100 kHz, 0.1 V
DCR	
Transformer Side	1.0 Ω max.
CM Choke Side	1.4 Ω max.
Cww (TCT to CMT, RCT to CMT)	20 pF max.
Turns Ratio	1:1 $\pm$ 2 %
Insertion Loss	
1~100 MHz	-1.4 dB max.
Return Loss (Z out = 100 Ω)	
1~40 MHz	-16 dB min.
40~100 MHz	-10+20*log (f/80 MHz) dB min.
Cross Talk (between each channel)	
1~60 MHz	-40 dB min.
60~100 MHz	-35 dB min.
Common Mode Rejection Ratio	
1~60 MHz	-37 dB min.
60~100 MHz	-30 dB min.
Differential to Common Mode Rejection Ratio	
30 MHz	-35 dB min.
60 MHz	-35 dB min.
Hi-Pot (1 mA, 60 s)	2250 VDC or 1500 VAC
Operating Temperature	-40 °C to +125 °C
Storage Temperature	-40 °C to +125 °C
Moisture Sensitivity Level	1
ESD Classification (HBM)	N/A

Packaging Specifications

Tape & Reel..... 500 pcs./reel

How To Order

SM91076 L - E


Model _____
Termination _____
L = Tin (RoHS Compliant)
Packaging _____
E = Tape and Reel

Additional Information


Click these links for more information:




Product Dimensions



Recommended Layout



Electric Schematic



WARNING Cancer and Reproductive Harm
www.P65Warnings.ca.gov

*RoHS Directive 2015/863, Mar 31, 2015 and Annex.

**MMA is a group of product developers and users promoting the use of the open field network MECHATROLINK. Specifications are subject to change without notice.


Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

SM91076L 10/100 Base-T Transformer

BOURNS®

Solder Profile



Reflow Condition		Pb-free Assembly
Average Ramp-up Rate		3 °C / second max.
Preheat	Temperature Min. (T_{smin})	150 °C
	Temperature Max. (T_{smax})	200 °C
	Time (T_{smin} to T_{smax})	60 ~ 180 seconds
Liquidus Temperature (T_L)		217 °C
Time above Liquidus Temperature (t_L)		60 ~ 150 seconds
Peak Temperature (T_p)		245 - 250 °C
Time within 5 °C of Actual Peak Temperature (T_p)		20 ~ 40 seconds
Ramp-down Rate from Peak Temperature		6 °C / second max.
Time from 25 °C to Peak Temperature (T_p)		8 minutes max.
Do not Exceed		260 °C

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[SM91076L-E](#)