
# 



This connector is an interface connector, 48 and 36 circuits sealed and lever type.

### Board-to-wire/Sealed connector

### Features

### Improvement of Operability

The lever is adopted to decrease the connector mating force. The fixing part to PC board is snap fit configuration in consideration of the workability when assembling.

### Sealed

Mat seal is adopted for improving the workability of wire seal part.

### Durability

Heat resistant specification corresponding to 120°C.


#### Reduced waste structure

Low cost and low resources are realized by abolishing use of the wire rod pin and the alignment board.

#### Variations

This connector is available in two kinds of keying codes. If the harness cover of an option is used, the harness can be taken out from the side.


Circuits: Lineup of 48 and 36 circuits.



### **Specifications**

- •Current rating: Power/ 7 A DC
  - Signal/ 5 A DC
- Voltage rating: 50 V DC
- Temperature range: -40°C to +120°C (including temperature rise in applying electrical current)
- •Contact resistance: Initial value/  $8 \text{ m}\Omega$  max.
  - After environmental tests/ 16 m $\Omega$  max.
- Insulation resistance: 100 MΩ min.
- •Withstanding voltage: 1,000 VAC/minute •Applicable wire: AVSS 0.3 mm<sup>2</sup> to 0.85 mm<sup>2</sup>
  - AESSX-f 0.3 mm<sup>2</sup> to 0.75 mm<sup>2</sup>
- \* Compliant with ELV/RoHS.
- \* Contact JST for details.

### **ZRO** CONNECTOR




	Applicable		
Model No.	Conductor (mm <sup>2</sup> )	Insulation O.D. (mm)	Q'ty/reel
SZRO-A021T-M0.64	0.3 to 0.5	1.4 to 1.7	10,000
SZRO-A031T-M0.64	0.75 to 0.85	1.8 to 1.9	10,000

Material and Finish


Copper alloy, tin-plated (reflow treatment)

### Female connector





### •48 circuits




Circuits	Model No.	Key Code	Applicable wire range (mm²)	Q'ty/box	Housing Color	Wire seal Color
	36ZRO-B-1A	Α	0.5 to 0.85	512	Black	Brown
36	36ZRO-B-2A	Α	0.3 to 0.85 (Note)	512	Black	Red
	36ZRO-B-2B	В	0.3 to 0.85 (Note)	512	Gray	Red
	48ZRO-B-1A	Α	0.5 to 0.85	384	Black	Brown
48	48ZRO-B-1B	В	0.5 to 0.85	384	Gray	Brown
	48ZRO-B-2A	Α	0.3 to 0.85 (Note)	384	Black	Red
	48ZRO-B-2B	В	0.3 to 0.85 (Note)	384	Gray	Red
	Material and Finish					

Housing: Glass-filled PBT Seal: Silicone Lever: POM

Note: There is a limit to an arrangement and number of wires when 0.75 mm<sup>2</sup> and 0.85 mm<sup>2</sup> wires applied. Refer to the drawing or contact JST for details.

## **ZRO** CONNECTOR

### Male connector




Туре	Circuits	Model No.	Key Code	Q'ty/box	Housing Color
36		S36B-ZROK-2A-R A		240	Black
Normal	30	S36B-ZROH-2B-R	В	240	Gray
Normai	48	S48B-ZROK-2A-R	Α	192	Black
		S48B-ZROH-2B-R	В	102	Gray
Case lock	36	S36B-ZROK-3A-R	Α	240	Black
		S36B-ZROH-3B-R	В	240	Gray
	48	S48B-ZROK-3A-R	Α	192	Black
		S48B-ZROH-3B-R	В	102	Gray
Material and Finish					

Housing: Glass-filled PBT Pin: Brass, tin-plated (reflow treatment)


Fin. Blass, theplated (fellow freatmen

### Harness cover




Circuits	Model No.	Q'ty/box	Housing Color		
36	ZROHC-36H-K-1	900	Black		
48	ZROHC-48H-K-1	600	Black		
Material and Finish					
PBT					

### **ZRO** CONNECTOR



Q'ty/box				
7,000				
Material and Finish				
PBT, Gray				

### PC board layout, Assembly layout



Crimping machine, Applicator				
Strip terminal	Crimping machine	Crimp applicator MKS-L		
		Dies	Crimp applicator with dies	
SZRO-A021T-M0.64	AP-K2N	MK/SWPH-A021-064	APLMK SWPH-A021-064	
SZRO-A031T-M0.64		MK/SZRO-A031-064	APLMK SZRO-A031-064	

Note: When crimping operation is conducted using an applicator and die set other than the above, JST cannot guarantee the performance of the terminal.