

With a high degree of mechanical and electrical stability, Bulgin's M12 X Coding connectors provide a cost effective and flexible connectivity solution for onsite installations, helping to decrease downtime in process control, manufacturing automation and industrial instrumentation applications.

Key features:

- Reliable industry standard (EN 61076-2-109) screw locking mechanism
- Field installable, cable and panel mount options
- Maximum Data Signaling Rate to 10Gbit/s
- -25 °C to 85 °C Temperature Range
- Plastic and metal options variants
- Cat6a cables
- Ethernet, Profinet Application
- 800V Rated Impulse Voltage
- IP67 degree of protection
- 0.5A Rated Current
- M12 X Coding

M12 Series coding options:
(Full Contact Diagrams Page 174)



X-Coding




M12 X Code Rear Panel Mounting Male



PXMBNI12RPM08XPCM16

- 8 Contacts
- PCB termination
- Mates with flex body connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12RPM08XPCM16	08	X	PCB Terminal	M16 Mounting / Gland Nut Thread

M12 X Code Rear Panel Mounting Female



PXMBNI12RPF08XPCM16

- 8 Contacts
- PCB termination
- Mates with Inline body connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12RPF08XPCM16	08	X	PCB Terminal	M16 Mounting / Gland Nut Thread

M12 X Code Rear Panel Mounting Female - RJ45



PXMBNI12RAF08XRJM16

- 8 Contacts
- Solder termination
- Metal flex body
- Mates with Inline body connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12RAF08XRJM16	08	X	RJ45	M16 Mounting / Gland Nut Thread

M12 X Code Rear Panel Mounting Female - RJ45



PXMBNI12RPM08XRJM16

- 8 Contacts
- Solder termination
- Metal flex body
- Mates with Inline body connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12RPM08XRJM16	08	X	RJ45	M16 Mounting / Gland Nut Threa

Nickel Plated M12 X Code Inline Body Male



PXMBNI12FIM08XSCPG9

- ⬡ 8 Contacts
- ⬡ Solder termination
- ⬡ Metal Inline body
- ⬡ Mates with flex body and panel mount connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12FIM08XSCPG9	08	X	Solder Terminal	PG9 Mounting / Gland Nut Thread

Nickel Plating M12 X Code Flex Body Female



PXMBNI12FBF08XSCPG9

- ⬡ 8 Contacts
- ⬡ Solder termination
- ⬡ Metal Flex Body
- ⬡ Mates with Inline Body and panel mount connectors




Part Number	Contacts	Code	Termination	Mounting Nut
PXMBNI12FBF08XSCPG9	08	X	Solder Terminal	PG9 Mounting / Gland Nut Threa

Inline to Inline Overmould Cable



PXPTPU12FIM08XFI010PU

- ⬡ 8 Contacts
- ⬡ 1, 2, 3, 5 & 10m cable options
- ⬡ TPU flex body overmold
- ⬡ PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FIM08XFI010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FIM08XFI020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FIM08XFI030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FIM08XFI050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FIM08XFI100PU	08	X	Overmold Cable	10m	PU

Flex Body to Flex Body Overmould Cable



PXPTPU12FBF08XFB010PU

- ⬡ 8 Contacts
- ⬡ 1, 2, 3, 5 & 10m cable options
- ⬡ TPU flex body overmold
- ⬡ PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FBF08XFB010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FBF08XFB020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FBF08XFB030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FBF08XFB050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FBF08XFB100PU	08	X	Overmold Cable	10m	PU

Inline to Flex Body Overmould Cable



PXPTPU12FIM08XFB010PU

- 8 Contacts
- 1, 2, 3, 5 & 10m cable options
- TPU flex body overmold
- PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FIM08XFB010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FIM08XFB020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FIM08XFB030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FIM08XFB050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FIM08XFB100PU	08	X	Overmold Cable	10m	PU

Inline to RJ45 Overmould Cable



PXPTPU12FIM08XRJ010PU

- 8 Contacts
- 1, 2, 3, 5 & 10m cable options
- TPU flex body overmold
- PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FIM08XRJ010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FIM08XRJ020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FIM08XRJ030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FIM08XRJ050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FIM08XRJ100PU	08	X	Overmold Cable	10m	PU

Flex body to RJ45 Overmould Cable



PXPTPU12FBF08XRJ010PU

- 8 Contacts
- 1, 2, 3, 5 & 10m cable options
- TPU flex body overmold
- PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FBF08XRJ010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FBF08XRJ020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FBF08XRJ030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FBF08XRJ050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FBF08XRJ100PU	08	X	Overmold Cable	10m	PU

Inline Overmould Cable



PXPTPU12FIM08XCL010PU

- 8 Contacts
- 1, 2, 3, 5 & 10m cable options
- TPU flex body overmold
- PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FIM08XCL010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FIM08XCL020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FIM08XCL030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FIM08XCL050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FIM08XCL100PU	08	X	Overmold Cable	10m	PU

Inline Overmould Cable



PXPTPU12FBF08XCL010PU

- 8 Contacts
- 1, 2, 3, 5 & 10m cable options
- TPU flex body overmold
- PU jacket cable




Part Number	Contacts	Code	Termination	Lead Length	Cable Material
PXPTPU12FBF08XCL010PU	08	X	Overmold Cable	1m	PU
PXPTPU12FBF08XCL020PU	08	X	Overmold Cable	2m	PU
PXPTPU12FBF08XCL030PU	08	X	Overmold Cable	3m	PU
PXPTPU12FBF08XCL050PU	08	X	Overmold Cable	5m	PU
PXPTPU12FBF08XCL100PU	08	X	Overmold Cable	10m	PU

M12 SMT Connectors



PXPLCP12SM

- 4, 5, 8 & 12 Contacts
- Male and Female options
- PCB Termination




Part Number	Contacts	Code	Termination
PXPLCP12SMF08XPC	8	X	PCB Terminal

PA66 M12 Sealing Cap



PXPPAM12

- Sealing caps to maintain IP67 rating
- Male & Female versions




Part Number	Series	Type	Material
PXPPAM12CAM	M12	Male	PA66
PXPPAM12CAF	M12	Female	PA66

Brass - Nickel Plating M12 Sealing Cap



PXMBNI12

- Sealing caps to maintain IP67 rating
- Male & Female versions



Part Number	Series	Type	Material
PXMBNI12CAM	M12	Male	Brass - Nickel Plating
PXMBNI12CAF	M12	Female	Brass - Nickel Plating

Buccaneer M12 X Coding Series

Specifications



Electrical

No. Contacts:	8
Current Rating:	0.5A
Voltage Rating (ac/dc) :	48V
Contact Resistance:	<5mΩ
Insulation Resistance:	>100MΩ
Operating Temp Range:	-25°C to 85°C

Mechanical:

Locking Mechanism:	Screw coupling
Sealing:	IP67
Contact Accomodation:	
8 Contacts	26AWG x 4P + AEB
Cable:	6.2mm Dia
Contacts:	Terminations:
8 Contacts	PCB / Solder / Cable
Mechanical Operation:	500 mating cycles
Largest diameter over coupling ring:	20.0mm

Panel Mount:

Body Material:	Nickel Plated Brass
Coupling Nut Material:	Nickel Plated Brass
Colour:	Grey
Plug Contacts Material:	Brass, Gold plating
Socket Contacts Material:	Phosphor Bronze, Gold plating
O Rings & Gaskets Materials:	Viton
RoHS:	Compliant

Cable Connectors:

TPU / LCP
Nickel Plated Brass
Black
Brass, Gold plating
Phosphor Bronze, Gold plating
Viton
Compliant

Flex & Inline Connectors:

Nickel Plated Brass
Nickel Plated Brass
Grey
Brass, Gold plating
Phosphor Bronze, Gold plating
Viton
Compliant


MX	XXX	XX	XX	X	XX	X	XX
Series	Material	Series Size	Body Style	Orientation	Contacts	Code	Termination
PXM	BNI = Brass Nickel TPU = overmold for PUR LCP = Liquid Crystal Polymer	12	FB = Flex Body	M = Male	08	X	PC = PCB
PXP			FI = Inline Body	F = Female			CL = Cable
			RP = Rear Panel Mounting				SC = Solder
			RA = Right Angle				RJ = RJ45
							FB = FLEX BODY
							FI = Inline BODY

XXX	XXX	XXX
Mounting / Gland Nut Thread	Lead Length	Cable Material
PG9	010 = 1m	PUR
M16	020 = 2m	
	030 = 3m	
	050 = 5m	
	100 = 10m	


Contact Diagrams:

PXMBNI12RPM08XPCM16
PXMBNI12FIM08XSCPG9

PXMBNI12RPF08XPCM16
PXMBNI12FBF08XSCPG9



PXMBNI12RAF08XRJM16
PXMBNI12RPM08XRJM16



PXPTPU12FIM08XFI010PU





PXPTPU12FBF08XFB010PU





PXPTPU12FIM08XFB010PU



PXPTPU12FIM08XRJ010PU



PXPTPU12FBF08XRJ010PU



PXPTPU12FIM08XCL010PU



P2
TINNED
WIRES

PXPTPU12FBF08XCL010PU



P2
TINNED
WIRES

P1	PAIR	WIRE COLOUR	P2
1		WHITE / ORANGE	1
2			2
3		WHITE / GREEN	3
4			4
5		WHITE / BLUE	5
6			6
7		WHITE / BROWN	7
8			8

P1	PAIR	WIRE COLOUR	P2
1		WHITE / ORANGE	1
2			2
3		WHITE / GREEN	3
4			4
5		WHITE / BLUE	5
6			6
7		WHITE / BROWN	7
8			8
SHELL		BRAID	SHELL

P1	PAIR	WIRE COLOUR	P2
1		WHITE / ORANGE	1
2			2
3		WHITE / GREEN	3
4			4
5		WHITE / BLUE	5
6			6
7		WHITE / BROWN	7
8			8
SHELL		BRAID	SHELL

P1	PAIR	WIRE COLOUR	P2	
1		WHITE / ORANGE	OPEN	
2				
3		WHITE / GREEN		
4				
5		WHITE / BLUE		
6				
7		WHITE / BROWN		
8				
SHELL		BRAID		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bulgin:

<u>PXPTPU12FIM08XFI010PU</u>	<u>PXPTPU12FIM08XCL020PU</u>	<u>PXPTPU12FIM08XCL050PU</u>	
<u>PXPTPU12FIM08XCL100PU</u>	<u>PXPTPU12FBF08XCL050PU</u>	<u>PXPTPU12FBF08XFB020PU</u>	
<u>PXPTPU12FBF08XFB100PU</u>	<u>PXPTPU12FIM08XFB030PU</u>	<u>PXPTPU12FIM08XFB050PU</u>	
<u>PXPTPU12FBF08XCL020PU</u>	<u>PXPTPU12FBF08XFB050PU</u>	<u>PXPTPU12FIM08XCL030PU</u>	<u>PXPTPU12FIM08XFI020PU</u>
<u>PXPTPU12FBF08XCL030PU</u>	<u>PXPTPU12FBF08XFB030PU</u>	<u>PXPTPU12FIM08XFI030PU</u>	
<u>PXPTPU12FBF08XFB010PU</u>	<u>PXPTPU12FIM08XFB020PU</u>	<u>PXPTPU12FIM08XFI050PU</u>	<u>PXPTPU12FIM08XFI100PU</u>
<u>PXPTPU12FBF08XCL010PU</u>	<u>PXPTPU12FIM08XCL010PU</u>	<u>PXPTPU12FIM08XFB100PU</u>	
<u>PXPTPU12FBF08XCL100PU</u>	<u>PXPTPU12FIM08XFB010PU</u>		