



preci-dip


PCB CONNECTORS

SERIES 370

370-PP-1NN-00-001101

Single Row
2.54 mm, Turret head

PCB header strips for wiring application with solder tail / connecting pin.



TECHNICAL SPECS.:

Insulator	Black glass filled polyester PCT-GF30-FR
Flammability	UL 94V-O
Contact	Brass CuZn36Pb3 (C36000)
Connecting pin Ø	0.5 mm
Mechanical life	Min. 100 cycles
Rated current	3 A
Contact resistance	Max. 10 m
Dielectric strength	Min. 1000 V RMS

ORDERING INFORMATION:

PP Plating code	Termination	Connecting pin
10	Gold 0.25 µm	Gold 0.25 µm
80	Tin	Tin

NN number of poles. Replace NN with the requested number of poles, e.g. 460-10-2NN-00-001101 for a double row version with 16 pins becomes 460-10-216-00-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole $\varnothing$: $0.7 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole $\varnothing$: $1 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Preci-dip:](#)

[370-10-164-00-001101](#) [370-10-138-00-001101](#) [370-10-149-00-001101](#) [370-10-148-00-001101](#) [370-10-147-00-001101](#) [370-10-146-00-001101](#) [370-80-143-00-001101](#) [370-80-142-00-001101](#) [370-80-141-00-001101](#) [370-80-140-00-001101](#) [370-80-139-00-001101](#) [370-80-151-00-001101](#) [370-80-162-00-001101](#) [370-80-148-00-001101](#) [370-80-147-00-001101](#) [370-80-146-00-001101](#) [370-80-145-00-001101](#) [370-80-144-00-001101](#) [370-80-155-00-001101](#) [370-80-154-00-001101](#) [370-80-153-00-001101](#) [370-80-152-00-001101](#) [370-80-136-00-001101](#) [370-80-150-00-001101](#) [370-80-149-00-001101](#) [370-80-160-00-001101](#) [370-80-159-00-001101](#) [370-80-158-00-001101](#) [370-80-157-00-001101](#) [370-80-156-00-001101](#) [370-80-118-00-001101](#) [370-80-117-00-001101](#) [370-80-116-00-001101](#) [370-80-115-00-001101](#) [370-80-114-00-001101](#) [370-80-126-00-001101](#) [370-80-138-00-001101](#) [370-80-123-00-001101](#) [370-80-122-00-001101](#) [370-80-121-00-001101](#) [370-80-120-00-001101](#) [370-80-119-00-001101](#) [370-80-130-00-001101](#) [370-80-129-00-001101](#) [370-80-128-00-001101](#) [370-80-127-00-001101](#) [370-80-137-00-001101](#) [370-80-125-00-001101](#) [370-80-163-00-001101](#) [370-80-135-00-001101](#) [370-80-134-00-001101](#) [370-80-133-00-001101](#) [370-80-132-00-001101](#) [370-80-131-00-001101](#) [370-10-103-00-001101](#) [370-10-115-00-001101](#) [370-80-111-00-001101](#) [370-80-164-00-001101](#) [370-80-161-00-001101](#) [370-80-124-00-001101](#) [370-10-109-00-001101](#) [370-10-108-00-001101](#) [370-10-107-00-001101](#) [370-10-106-00-001101](#) [370-10-105-00-001101](#) [370-10-104-00-001101](#) [370-10-116-00-001101](#) [370-10-114-00-001101](#) [370-10-126-00-001101](#) [370-10-112-00-001101](#) [370-10-111-00-001101](#) [370-10-110-00-001101](#) [370-10-122-00-001101](#) [370-10-121-00-001101](#) [370-10-120-00-001101](#) [370-10-119-00-001101](#) [370-10-118-00-001101](#) [370-10-117-00-001101](#) [370-10-127-00-001101](#) [370-10-102-00-001101](#) [370-10-113-00-001101](#) [370-80-113-00-001101](#) [370-10-124-00-001101](#) [370-10-123-00-001101](#) [370-10-157-00-001101](#) [370-10-156-00-001101](#) [370-10-155-00-001101](#) [370-10-154-00-001101](#) [370-10-153-00-001101](#) [370-10-125-00-001101](#) [370-10-163-00-001101](#) [370-10-151-00-001101](#) [370-10-161-00-001101](#) [370-10-160-00-001101](#) [370-10-159-00-001101](#) [370-10-158-00-001101](#) [370-80-106-00-001101](#) [370-80-105-00-001101](#) [370-80-104-00-001101](#) [370-80-103-00-001101](#)