



preci-dip

PCB CONNECTORS


SERIES 350

350-PP-1NN-00-106101

Single row

2.54 mm, Surface mount perpendicular gull-wing, Pin Ø 0.47 mm

Pin connectors, SMD.



TECHNICAL SPECS.:

Insulator	Black glass filled polyester PCT-GF30-FR
Flammability	UL 94V-O
Contact	Brass CuZn36Pb3 (C36000)
Connecting pin Ø	0.47 mm
Mechanical life	Min. 500 cycles
Rated current	3 A
Dielectric strength	Min. 1000 V RMS
Coplanarity SMD termination	Max. 0.1 mm (measured on 25 mm long connectors)

ORDERING INFORMATION:

PP Plating code	Termination	Connecting pin
10	Gold 0.25 µm	Gold 0.25 µm
80	Tin	Tin
V3*	Tin	Gold 0.75 µm

*only for 350...00-106101 seriesNN number of poles. Replace NN with the requested number of poles, e.g. 350-10-1NN-00-106101 for a single row version with 8 pins becomes 350-10-108-00-106101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole $\varnothing$: $0.7 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole $\varnothing$: $1 + 0.09/-0.06$ mm | Drilled hole $\varnothing$: 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

PACKAGING:

Standard connector packaging is card box.

SMD mount connectors available on request with Tape & Reel packaging acc. to EIA Standard 481.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Preci-dip:](#)

[350-10-154-00-106101](#) [350-80-103-00-106101](#) [350-10-163-00-106101](#) [350-10-162-00-106101](#) [350-80-159-00-106101](#) [350-80-158-00-106101](#) [350-80-157-00-106101](#) [350-80-156-00-106101](#) [350-V3-106-00-106101](#) [350-V3-103-00-106101](#) [350-80-163-00-106101](#) [350-80-162-00-106101](#) [350-80-161-00-106101](#) [350-80-160-00-106101](#) [350-V3-108-00-106101](#) [350-V3-107-00-106101](#) [350-80-153-00-106101](#) [350-V3-105-00-106101](#) [350-V3-117-00-106101](#) [350-V3-115-00-106101](#) [350-V3-114-00-106101](#) [350-V3-113-00-106101](#) [350-V3-112-00-106101](#) [350-V3-111-00-106101](#) [350-V3-110-00-106101](#) [350-80-133-00-106101](#) [350-80-132-00-106101](#) [350-80-131-00-106101](#) [350-80-143-00-106101](#) [350-V3-104-00-106101](#) [350-80-140-00-106101](#) [350-80-139-00-106101](#) [350-80-138-00-106101](#) [350-80-137-00-106101](#) [350-80-136-00-106101](#) [350-80-135-00-106101](#) [350-80-146-00-106101](#) [350-80-145-00-106101](#) [350-80-144-00-106101](#) [350-80-154-00-106101](#) [350-80-142-00-106101](#) [350-80-155-00-106101](#) [350-80-152-00-106101](#) [350-80-151-00-106101](#) [350-80-150-00-106101](#) [350-80-149-00-106101](#) [350-80-148-00-106101](#) [350-80-147-00-106101](#) [350-V3-145-00-106101](#) [350-V3-144-00-106101](#) [350-V3-116-00-106101](#) [350-V3-155-00-106101](#) [350-80-141-00-106101](#) [350-V3-118-00-106101](#) [350-V3-151-00-106101](#) [350-V3-150-00-106101](#) [350-V3-149-00-106101](#) [350-V3-148-00-106101](#) [350-V3-147-00-106101](#) [350-V3-146-00-106101](#) [350-V3-157-00-106101](#) [350-V3-156-00-106101](#) [350-V3-141-00-106101](#) [350-V3-154-00-106101](#) [350-V3-142-00-106101](#) [350-V3-152-00-106101](#) [350-V3-163-00-106101](#) [350-V3-162-00-106101](#) [350-V3-161-00-106101](#) [350-V3-160-00-106101](#) [350-V3-159-00-106101](#) [350-V3-158-00-106101](#) [350-V3-121-00-106101](#) [350-V3-120-00-106101](#) [350-V3-119-00-106101](#) [350-V3-131-00-106101](#) [350-V3-153-00-106101](#) [350-V3-164-00-106101](#) [350-V3-127-00-106101](#) [350-V3-126-00-106101](#) [350-V3-125-00-106101](#) [350-V3-124-00-106101](#) [350-V3-123-00-106101](#) [350-V3-122-00-106101](#) [350-V3-134-00-106101](#) [350-V3-133-00-106101](#) [350-V3-132-00-106101](#) [350-V3-130-00-106101](#) [350-V3-143-00-106101](#) [350-V3-128-00-106101](#) [350-V3-140-00-106101](#) [350-V3-139-00-106101](#) [350-V3-138-00-106101](#) [350-V3-137-00-106101](#) [350-V3-136-00-106101](#) [350-V3-135-00-106101](#) [350-10-120-00-106101](#) [350-10-119-00-106101](#) [350-10-131-00-106101](#) [350-80-129-00-106101](#)