

**CLI C 1-6 GE/SW 28 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                        |
|------------|------------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 2.5 - 5 mm, 6 x 4.2 mm, yellow |
| Order No.  | <a href="#">0252711549</a>                                             |
| Type       | CLI C 1-6 GE/SW 28 MP                                                  |
| GTIN (EAN) | 4008190171520                                                          |
| Qty.       | 100 pc(s).                                                             |

## CLI C 1-6 GE/SW 28 MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 5 mm   | Depth (inches)  | 0.197 inch |
| Height     | 6 mm   | Height (inches) | 0.236 inch |
| Width      | 4.2 mm | Width (inches)  | 0.165 inch |
| Net weight | 0.1 g  |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                   |                                                |                                              |               |
|-----------------------------------|------------------------------------------------|----------------------------------------------|---------------|
| Colour                            | yellow                                         | Colour of printing                           | black         |
| Halogen                           | Yes                                            | Insulation cross-section, max.               | 5             |
| Material                          | PVC, soft, without Cadmium                     | Material colour according to resistance code | 4             |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range                  | -30...80 °C   |
| Operating temperature range, max. | 80 °C                                          | Operating temperature range, min.            | -30 °C        |
| Orientation of print              | horizontal                                     | Printed characters                           | Numbers       |
| Printing                          | 28                                             | Printing method                              | hot-embossing |
| Recommended industries            | Process, Machinery                             | Type of printing                             | Standard      |
| UL 94 flammability rating         | V-0                                            | Version                                      | MultiPack     |
| Width                             | 4.2 mm                                         |                                              |               |

## Conductor and cable markers

|                               |                     |                                  |                         |
|-------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 2.5 - 5 mm          | Conductor O.D., max.             | 5 mm                    |
| Conductor O.D., min.          | 2.5 mm              | Conductor cross-section, max.    | 4 mm <sup>2</sup>       |
| Conductor cross-section, min. | 1.5 mm <sup>2</sup> | Cross-section for connected wire | 1.5 - 4 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI C 1-6 GE/SW 28 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0252711549](#)