

TS 35X7.5 2M/AL/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Aluminum has the second best electrical conductivity after copper. One advantage is low weight, anMiscellaneous is outstanding corrosion protection.

General ordering data

Version	Rail, TS 35, TS 35 x 7.5, without slot, Aluminium, untreated
Order No.	0330800000
Type	TS 35X7.5 2M/AL/BK
GTIN (EAN)	4008190100650
Qty.	2 m

TS 35X7.5 2M/AL/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	108.2 g		

Mounting rail

Installation advice	Direct mounting	
Length of the terminal rail	min.	0 mm
	max.	2,000 mm
	nominal	2,000 mm
Material	Aluminium	
Permitted thermal current for PEN function, max.	125 A	
Pre-punched mounting rail	No	
Short circuit strength corresponds to E-Cu wire	35 mm²	
Short-time withstand current according to IEC 60947-7-2	4.2 kA/1s	
Slit gap		
Slit length		
Slit width		
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	1 mm	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0330800000](#)