

**IE-C5DD4UG0030MSSA20-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12-RJ45

**General ordering data**

|            |                                                                                                                                 |
|------------|---------------------------------------------------------------------------------------------------------------------------------|
| Version    | Dragline cable, PROFINET, M12 D-code – IP 67 straight socket, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 3 m |
| Order No.  | <a href="#">1211080030</a>                                                                                                      |
| Type       | IE-C5DD4UG0030MSSA20-E                                                                                                          |
| GTIN (EAN) | 4050118072709                                                                                                                   |
| Qty.       | 1 pc(s).                                                                                                                        |

Creation date September 16, 2022 2:12:12 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## IE-C5DD4UG0030MSSA20-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Length     | 3 m   | Length (inches) | 118.11 inch |
| Net weight | 218 g |                 |             |

## Temperatures

|                          |                |                       |                |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature      | -50 °C...70 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -20 °C...60 °C |                       |                |

## Environmental Product Compliance

|                |      |                                              |
|----------------|------|----------------------------------------------|
| REACH SVHC     | SCIP | 67cf1078-<br>beca-4687-860b-<br>dc475a6ec24a |
| Lead 7439-92-1 |      |                                              |

## Cable specific standards

|                               |                                                   |                              |                          |
|-------------------------------|---------------------------------------------------|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |                              |                          |

## General standards

|                         |         |
|-------------------------|---------|
| Certificate no. (cULus) | E316369 |
|-------------------------|---------|

## Standards

|                               |                                                   |                              |                          |
|-------------------------------|---------------------------------------------------|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |                              |                          |

## Cable structure

|                              |                                                         |                                       |                                                   |
|------------------------------|---------------------------------------------------------|---------------------------------------|---------------------------------------------------|
| Arrangement of wire cores    | Star-quad                                               | Colour sequence or wires - wire pairs | white, yellow, blue, orange                       |
| Complete shielding           | Aluminium foil, Shielding braid made from copper wiring | Cross-section                         | 4*AWG 22/7 - 0.36 mm <sup>2</sup>                 |
| Diameter of inner sheathing  | 3.9 mm                                                  | Filler                                | As central element                                |
| Insulation                   | PE                                                      | Insulation cross-section              | 1.5 mm                                            |
| Material sheath              | PUR                                                     | Number of wires                       | 4                                                 |
| Overlap of shielding braid   | 85 %                                                    | Sheath diameter, max.                 | 6.7 mm                                            |
| Sheath diameter, min.        | 6.3 mm                                                  | Sheathing colour                      | green (RAL 6018), SF/UTP                          |
| Sheathing material thickness | 0.9 mm                                                  | Shielding                             | SF/UTP                                            |
| Shielding braid thickness    | 0.13 mm                                                 | Standard designations                 | 2YH(ST)C11Y<br>2x2x0,75/1,5-100 LI VZN<br>GN FRNC |
| Strands                      | 7                                                       | Wire core insulation thickness        | 0.38 mm                                           |
| Wire material                | Stranded tin-plated copper wire                         |                                       |                                                   |

## Electrical properties of cable

|                          |                                             |
|--------------------------|---------------------------------------------|
| Capacity at 1 kHz        | 52 nF/km                                    |
| Category                 | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) |
| Characteristic impedance | 100 ± 15 Ω at 1-100 MHz                     |

Creation date September 16, 2022 2:12:12 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## IE-C5DD4UG0030MSSA20-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                |                                      |
|--------------------------------|--------------------------------------|
| Deviation                      | 40 ns/100m                           |
| Loop resistance                | 120 Ω/km                             |
| Operating voltage (UL rating)  | Operating voltage 600 V              |
| Operating voltage (UL rating)  | 600 V undefined                      |
| Operating voltage, UL          | 600 V                                |
| Resistance differential        | 3 %                                  |
| Signal propagation time        | 5.3 ns/m                             |
| Speed                          | 180 m/min                            |
| Test voltage: wire-wire-shield | 2000 V <sub>eff</sub> , 50 Hz, 1 min |
| Transfer impedance             | 20 mΩ/m at 10 MHz                    |

## Mechanical and material properties of cable

|                                 |                                        |                                |                                |
|---------------------------------|----------------------------------------|--------------------------------|--------------------------------|
| Abrasion resistance             | very good                              | Acceleration                   | 4 m/s <sup>2</sup>             |
| Bending cycles                  | 3 Mio                                  | Fire propagation               | No                             |
| Halogen                         | halogen-free, according to IEC 60754-2 | Min. bending radius, once only | 5 x cable diameter             |
| Min. bending radius, repetitive | 7.5 x cable diameter                   | Pulling force                  | ≤ 150 N                        |
| Resistance to oils              | in accordance with IEC 60811-2-1       | Resistance to spread of flame  | in accordance with IEC 60332-1 |
| Silicone-free                   | Yes                                    | Speed                          | 180 m/min                      |
| UV-resistant                    | Yes                                    |                                |                                |

## Plug

|           |                                                              |            |                                                             |
|-----------|--------------------------------------------------------------|------------|-------------------------------------------------------------|
| Plug left | M12, IP67, female contact, straight, plug, Plastic, shielded | Plug right | RJ45, IP20, male contact, straight, plug, Plastic, shielded |
|-----------|--------------------------------------------------------------|------------|-------------------------------------------------------------|

## Plug, left

|                |                                    |
|----------------|------------------------------------|
| Connector left | M12 D-code – IP 67 straight socket |
|----------------|------------------------------------|

## Plug, right

|                 |            |
|-----------------|------------|
| Connector right | RJ45 IP 20 |
|-----------------|------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ECLASS 9.0  | 27-06-03-08 |
| ECLASS 9.1  | 27-06-03-08 | ECLASS 10.0 | 27-06-03-08 |
| ECLASS 11.0 | 27-06-03-08 | ECLASS 12.0 | 27-06-03-08 |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E316369    |

Creation date September 16, 2022 2:12:12 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

**IE-C5DD4UG0030MSSA20-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |                                                                             |
|--------------------|-----------------------------------------------------------------------------|
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>          |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                    |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |


## IE-C5DD4UG0030MSSA20-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensioned drawing



## Dimensioned drawing



## Wiring diagram

| RJ45 |        | M12 |
|------|--------|-----|
| 1    | gelb   | 1   |
| 3    | weiß   | 2   |
| 2    | orange | 3   |
| 6    | blau   | 4   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1211080030](#)