

IE-SW-VL08-8GT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

- Wide ranges of variations with 5 to 16 ports
- Variations for Gigabit Ethernet
- Two redundant power inputs 12/24/48 V DC
- Models with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Gigabit Ethernet, Number of ports: 8 * RJ45 10/100/1000BaseT(X), IP30, -10 °C...60 °C
Order No.	1241270000
Type	IE-SW-VL08-8GT
GTIN (EAN)	4050118029284
Qty.	1 pc(s).

Creation date January 22, 2022 4:50:32 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-SW-VL08-8GT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	135 mm	Height (inches)	5.315 inch
Width	52.85 mm	Width (inches)	2.081 inch
Net weight	850 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-10 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	According to IEC 60068-2-32	Safety standard	UL508, EN 60950-1
Ship use	DNV-GL	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

IE-SW-VL08-8GT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Interfaces

Alarm contact	Function DIP switch	Port surveillance, Broadcast storm protection enable/disable, Enable/ disable jumbo frame support, Activate/ deactivate IEEE 802.3az energy-efficient Ethernet
	1 relay output with a current capacity of 1 A at 24 V DC	
LED indicator	Power LED: PWR1, PWR2, FAULT, 10/100/1000M	Number of ports
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half- duplex mode, Auto MDI/ MDI-X port	8 * RJ45 10/100/1000BaseT(X)

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	2,424,649 h

Power supply

Connection type	1 removable 6-pin terminal block	
Current consumption	0.32 A at 24 V	
Reverse polarity protection	Available	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	9.6 V
	Voltage, max.	60 V

Switch characteristics

Bandwidth backplane	16 Gbps	Jumbo frame support	up to 9.6 KB
MAC table size	8 K	Packet buffer size	4,000 Kbit

Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Gigabit Ethernet	Switch	unmanaged
Type of mounting	DIN rail, Panel (with optional mounting kit)		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X), IEEE 802.3x for flow control, IEEE 802.3az Energy- Efficient Ethernet		

IE-SW-VL08-8GT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


Technical data

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ECLASS 9.0	19-17-01-06
ECLASS 9.1	19-17-01-06	ECLASS 10.0	19-17-04-02
ECLASS 11.0	19-17-04-02		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads

Approval/Certificate/Document of Conformity	CC-Link IE Field Certificate DNV-GL certificate ATEX certificate KC certificate EU Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Product Change Notification IE-SW-VL08-GT-series
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format
Brochures	

IE-SW-VL08-8GT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly


- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components.

IE-WALLMOUNT-KIT-30MM for use with:

- Industrial Ethernet Switches of the product range **IE-SW-BL05**

IE-WALLMOUNT-KIT-46MM for use with:

- Industrial Ethernet Switches of the product ranges **IE-SW- BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18**
- Industrial Ethernet media converters of the product range **IE-MC-VL**
- Industrial Ethernet switches of the product range **IE-WL-AP**

General ordering data

Type	IE-WALLMOUNT-KIT-46MM
Order No.	1504440000
GTIN (EAN)	4050118312317
Qty.	1 pc(s).

IE-SW-VL08-8GT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ethernet (Cat.6)**

- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, 802.3 at Type 1, 802.3 at
GTIN (EAN)	4050118153002	Type 2, 802.3 bt Type 3, $U_p(L/N-PE) \leq 550 \text{ V}$
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1241270000](#)