

CABTITE EP A 24/42 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Cabtite - Cable Entry Plates**

Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.

With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).

The tool less IP54 snap version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material, suitable for the temperature range from -40°C to +90°C.

Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

Version	Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 44 mm, Width: 142 mm, Depth: 12 mm, -40 °C...90 °C, IP54
Order No.	2743600000
Type	CABTITE EP A 24/42 GY
GTIN (EAN)	4064675 123316
Qty.	10 pc(s).

CABTITE EP A 24/42 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	12 mm	Depth (inches)	0.472 inch
Height	44 mm	Height (inches)	1.732 inch
Width	142 mm	Width (inches)	5.591 inch
Wall thickness, min.	1.5 mm	Wall thickness, max.	2.5 mm
Net weight	49 g		

Temperatures

Operating temperature -40 °C...90 °C

General information

Material	TPE	Protection degree	IP54
Silicone	No	UL 94 flammability rating	V-0

Number of connectable cables

Type of mounting	Snap-on		
Number of connectable cables	42		
Cable entries	Number	12	
	Cable diameter, min.	1 mm	
	Cable diameter, max.	7.2 mm	
	Cable type	Round cable	
	Number	17	
	Cable diameter, min.	1 mm	
	Cable diameter, max.	6.4 mm	
	Cable type	Round cable	
	Number	12	
	Cable diameter, min.	1 mm	
	Cable diameter, max.	5 mm	
	Cable type	Round cable	
	Number	1	
	Cable diameter, min.	1 mm	
	Cable diameter, max.	4.7 mm	
	Cable type	Round cable	

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.0	27-18-28-15
ECLASS 9.1	27-18-92-65	ECLASS 10.0	27-18-28-15
ECLASS 11.0	27-18-28-15	ECLASS 12.0	27-18-28-15

Approvals

Approvals



ROHS

Conform

CABTITE EP A 24/42 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[EU Declaration of Conformity - Cabtite EP - DoC DE PS2483](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[INSTR CABTITE EP DE/EN](#)

Catalogues


[Catalogues in PDF-format](#)

CABTITE EP A 24/42 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2743600000](#)