

CRIMPFIX ECO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	2833890000
Type	CRIMPFIX ECO
GTIN (EAN)	4064675422570
Qty.	1 pc(s).

CRIMPFIX ECO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	323 mm	Depth (inches)	12.717 inch
Height	188 mm	Height (inches)	7.402 inch
Width	230 mm	Width (inches)	9.055 inch
Net weight	12,496 g		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Consumables	Linked wire-end ferrules	Crimping	Trapezoidal
Crimping length	8 mm	Crimping range, max.	2.5 mm ²
Crimping range, min.	0.5 mm ²	Drive	Electro-mechanical
Electrical connection	100-240 V / 50/60 Hz / 100 VA	Length of wire-end ferrule	14 mm
Pulse time	approx. 1.5 s	Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ECLASS 9.0	17-13-01-01
ECLASS 9.1	17-13-01-01	ECLASS 10.0	17-13-01-01
ECLASS 11.0	17-13-01-01	ECLASS 12.0	17-13-01-01

Approvals

ROHS Conform

DownloadsUser Documentation [OPIN CRIMPFIX ECO WEB](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2833890000](#)