

**RS SD15B UNC LPK2****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

Passive interfaces for signal transmission on a SubD connector equipped with a clamping-yoke connection in accordance with IEC 807-2 / DIN 41652. The main features include:

- Group with 9-, 15-, 37- and 50-pole male and female connectors.
- One-to-one electrical connection between controller and field connections.
- Extremely compact modules in RS 45 section for installation on standard TS35 mounting rail.
- Pin for the earth connection.

**General ordering data**

|            |                                                                                                    |
|------------|----------------------------------------------------------------------------------------------------|
| Version    | Interface, RSSD, D-sub connectors, acc. to IEC 60807 / DIN 41652, 15-pole female, Screw connection |
| Order No.  | <a href="#">8209730000</a>                                                                         |
| Type       | RS SD15B UNC LPK2                                                                                  |
| GTIN (EAN) | 4008190296087                                                                                      |
| Qty.       | 1 pc(s).                                                                                           |

## RS SD15B UNC LPK2

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 66 mm | Depth (inches)  | 2.598 inch |
| Height     | 45 mm | Height (inches) | 1.772 inch |
| Width      | 61 mm | Width (inches)  | 2.402 inch |
| Net weight | 104 g |                 |            |

## Temperatures

|                     |             |                       |           |
|---------------------|-------------|-----------------------|-----------|
| Storage temperature | -40...70 °C | Operating temperature | 0...55 °C |
|---------------------|-------------|-----------------------|-----------|

## Environmental Product Compliance

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 7b5ffb72-271d-4c73-8b09-bd0aaee3697a |
|------------|----------------|------|--------------------------------------|

## Connection Data

|                                |                |                             |                                                 |
|--------------------------------|----------------|-----------------------------|-------------------------------------------------|
| Connection (field side)        | LPK 2H 5.08mm  | Connection on control side  | D-sub connectors, acc. to IEC 60807 / DIN 41652 |
| Design of locking system       | UNC 4/40       | Earthing                    | Yes                                             |
| Number of poles (control side) | 15-pole female | Protective earth connection | Flat-blade contact                              |

## Rating data

|               |       |                              |       |
|---------------|-------|------------------------------|-------|
| Rated voltage | 100 V | Rated current per connection | 1.5 A |
|---------------|-------|------------------------------|-------|

## Insulation coordination (EN50178)

|                               |              |                          |       |
|-------------------------------|--------------|--------------------------|-------|
| According to                  | DIN EN 50178 | Rated insulation voltage | 100 V |
| Surge voltage category        | II           | Pollution severity level | 2     |
| Pulse voltage test (1,2/50µs) | 0.8 kV       |                          |       |

## Connection field

|                                  |                     |                              |                      |
|----------------------------------|---------------------|------------------------------|----------------------|
| Clamping range, max.             | 1.5 mm <sup>2</sup> | Clamping range, min.         | 0.15 mm <sup>2</sup> |
| Flexible with sleeve, max.       | 2.5 mm <sup>2</sup> | Flexible with sleeve, min.   | 0.5 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K       | 4 mm <sup>2</sup>   | Flexible, min. H05(07) V-K   | 0.5 mm <sup>2</sup>  |
| Max. wire cross-section, AWG     | AWG 12              | Min. wire cross-section, AWG | AWG 26               |
| Sleeve with plastic collar, max. | 2.5 mm <sup>2</sup> | Solid, max. H05(07) V-U      | 6 mm <sup>2</sup>    |
| Solid, min. H05(07) V-U          | 0.5 mm <sup>2</sup> | Stripping length             | 6 mm                 |
| Tightening torque, max.          | 0.6 Nm              | Tightening torque, min.      | 0.5 Nm               |
| Type of connection               | Screw connection    |                              |                      |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002780    | ETIM 7.0    | EC002780    |
| ETIM 8.0    | EC002780    | ECLASS 9.0  | 27-14-11-52 |
| ECLASS 9.1  | 27-14-11-52 | ECLASS 10.0 | 27-14-11-52 |
| ECLASS 11.0 | 27-14-11-52 | ECLASS 12.0 | 27-14-11-52 |

## RS SD15B UNC LPK2

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of  
Conformity

[Declaration of Conformity](#)

Engineering Data

[WSCAD](#)

Catalogues

[Catalogues in PDF-format](#)

## RS SD15B UNC LPK2

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold


Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



N: Number of poles

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8209730000](#)