

**WDK 2.5PE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

A protective feed through terminal block is an electrical conductor for the purpose of safety and is used in many applications. To establish the electrical and mechanical connection between copper conductors and the mounting support plate, PE terminal blocks are used. They have one or more contact points for connection with and/or bifurcation of protective earth conductors.

**General ordering data**

|            |                                                                                                                       |
|------------|-----------------------------------------------------------------------------------------------------------------------|
| Version    | PE terminal, Double-tier terminal. Screw connection, 2.5 mm <sup>2</sup> , 300 A (2.5 mm <sup>2</sup> ), Green/yellow |
| Order No.  | <a href="#">1036300000</a>                                                                                            |
| Type       | WDK 2.5PE                                                                                                             |
| GTIN (EAN) | 4008190297565                                                                                                         |
| Qty.       | 50 pc(s).                                                                                                             |

## WDK 2.5PE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 62.5 mm    | Depth (inches) | 2.461 inch |
| Depth including DIN rail | 63.5 mm    | Height         | 69.5 mm    |
| Height (inches)          | 2.736 inch | Width          | 5.1 mm     |
| Width (inches)           | 0.201 inch | Net weight     | 17.62 g    |

## Temperatures

|                                  |                |                                  |                                                                                                   |
|----------------------------------|----------------|----------------------------------|---------------------------------------------------------------------------------------------------|
| Storage temperature              |                | Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
|                                  | -25 °C...55 °C |                                  |                                                                                                   |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C                                                                                            |

## Material data

|                           |       |        |              |
|---------------------------|-------|--------|--------------|
| Material                  | Wemid | Colour | Green/yellow |
| UL 94 flammability rating | V-0   |        |              |

## Rating data IECEx/ATEX

|                                |                                                                                                   |                                 |                   |
|--------------------------------|---------------------------------------------------------------------------------------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1346U                                                                                  | Certificate No. (IECEx)         | IECExULD15.0003U  |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup>                                                                                 | Wire cross section max. (IECEx) | 4 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              |                   |
| Ex 2014/34/EU label            | II 2 G D                                                                                          |                                 | Ex eb II C Gb     |

## System specifications

|                                     |                                                                 |                               |     |
|-------------------------------------|-----------------------------------------------------------------|-------------------------------|-----|
| Version                             | Screw connection, With PE connection, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1                                                               | Number of levels              | 2   |
| Number of clamping points per level | 2                                                               | Number of potentials per tier | 1   |
| Levels cross-connected internally   | Yes                                                             | PE connection                 | Yes |
| Rail                                | TS 35                                                           | N-function                    | No  |
| PE function                         | Yes                                                             | PEN function                  | No  |

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | Yes   | Number of similar terminals | 1       |
| Open sides               | right | Type of mounting            | Snap-on |

## CSA rating data

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1057876 | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

## WDK 2.5PE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|                                                                                         |                     |                                                                                         |                      |
|-----------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------|----------------------|
| Clamping range, max.                                                                    | 4 mm <sup>2</sup>   | Clamping range, min.                                                                    | 0.05 mm <sup>2</sup> |
| Clamping screw                                                                          | M 2.5               | Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>    |
| Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> | Connection direction                                                                    | top                  |
| Gauge to IEC 60947-1                                                                    | A3                  | Number of connections                                                                   | 4                    |
| Stripping length                                                                        | 10 mm               | Tightening torque, max.                                                                 | 0.6 Nm               |
| Tightening torque, min.                                                                 | 0.4 Nm              | Type of connection                                                                      | Screw connection     |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>  |
| Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>   | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>  |

## Dimensions

|              |       |
|--------------|-------|
| TS 35 offset | 32 mm |
|--------------|-------|

## General

|      |       |           |               |
|------|-------|-----------|---------------|
| Rail | TS 35 | Standards | IEC 60947-7-2 |
|------|-------|-----------|---------------|

## PE rating data

|                          |                              |              |    |
|--------------------------|------------------------------|--------------|----|
| Rated short-time current | 300 A (2.5 mm <sup>2</sup> ) | PEN function | No |
|--------------------------|------------------------------|--------------|----|

## Rating data

|                                                      |                     |                                              |         |
|------------------------------------------------------|---------------------|----------------------------------------------|---------|
| Rated cross-section                                  | 2.5 mm <sup>2</sup> | Rated voltage to adjoining terminal          | 400 V   |
| Standards                                            | IEC 60947-7-2       | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Rated impulse withstand voltage to adjacent terminal | 6 kV                | Power loss in accordance with IEC 60947-7-x  | 0.77 W  |
| Pollution severity                                   | 3                   |                                              |         |

## UL rating data

|                                            |        |                                            |        |
|--------------------------------------------|--------|--------------------------------------------|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 12 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus)   | 12 AWG |
| Conductor size Field wiring min. (cURus)   | 22 AWG |                                            |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |

## WDK 2.5PE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                           |            |
|---------------------------|------------|
| ROHS                      | Conform    |
| UL File Number Search     | UL Website |
| Certificate No. (cURus)   | E60693     |
| Certificate No. (cURusEX) | E184763    |

## Downloads

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">UKCA Ex Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">ATEX Certificate</a><br><a href="#">CB Test Certificate</a><br><a href="#">CB Certificate</a><br><a href="#">EAC certificate</a><br><a href="#">EAC EX Certificate</a><br><a href="#">CCC Ex Certificate</a><br><a href="#">UKCA Ex Certificate</a><br><a href="#">CE Declaration of Conformity</a><br><a href="#">CE Declaration of Conformity all terminals</a><br><a href="#">UKCA Declaration of Conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">NTI WDK 2.5 ZOV</a><br><a href="#">WDK 2.5 V</a><br><a href="#">NTI WDK-WPE 2.5EX</a>                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Brochures                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |

### WDK 2.5PE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

---

---

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1036300000](#)