

**WDU 4N BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                                                                                |
|------------|--------------------------------------------------------------------------------|
| Version    | Feed-through terminal, Screw connection, 4 mm <sup>2</sup> , 500 V, 32 A, blue |
| Order No.  | <a href="#">1042680000</a>                                                     |
| Type       | WDU 4N BL                                                                      |
| GTIN (EAN) | 4032248273225                                                                  |
| Qty.       | 100 pc(s).                                                                     |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 37.7 mm    | Depth (inches) | 1.484 inch |
| Depth including DIN rail | 38.5 mm    | Height         | 44 mm      |
| Height (inches)          | 1.732 inch | Width          | 6.1 mm     |
| Width (inches)           | 0.24 inch  | Net weight     | 6.35 g     |

## Temperatures

|                                  |                |                                  |                                                                                                   |
|----------------------------------|----------------|----------------------------------|---------------------------------------------------------------------------------------------------|
| Storage temperature              |                | Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
|                                  | -25 °C...55 °C |                                  |                                                                                                   |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C                                                                                            |

## Material data

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Material                  | Wemid | Colour | blue |
| UL 94 flammability rating | V-0   |        |      |

## Rating data IECEx/ATEX

|                                |                                                                                                   |                                 |                   |
|--------------------------------|---------------------------------------------------------------------------------------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO14ATEX1338U                                                                                  | Certificate No. (IECEX)         | IECEXULD14.0005U  |
| Max. voltage (ATEX)            | 352 V                                                                                             | Current (ATEX)                  | 31 A              |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup>                                                                                 | Max. voltage (IECEX)            | 352 V             |
| Current (IECEX)                | 31 A                                                                                              | Wire cross section max. (IECEX) | 4 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              |                   |
| Ex 2014/34/EU label            | II 2 G D                                                                                          |                                 | Ex eb II C Gb     |

## System specifications

|                                     |                                                                          |                               |     |
|-------------------------------------|--------------------------------------------------------------------------|-------------------------------|-----|
| Version                             | Screw connection, for plug-in cross-connector, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1                                                                        | Number of levels              | 1   |
| Number of clamping points per level | 2                                                                        | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No                                                                       | PE connection                 | No  |
| Rail                                | TS 35                                                                    | N-function                    | Yes |
| PE function                         | No                                                                       | PEN function                  | No  |

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | No    | Number of similar terminals | 1       |
| Open sides               | right | Type of mounting            | Snap-on |

## CSA rating data

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1057876 | Current size B (CSA)          | 10 A   |
| Current size D (CSA)          | 10 A           | Voltage size B (CSA)          | 300 V  |
| Voltage size D (CSA)          | 300 V          | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|                                                                                         |                      |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|---------------------|
| Blade size                                                                              | 0.6 x 3.5 mm         | Clamping range, max.                                                                    | 6 mm <sup>2</sup>   |
| Clamping range, min.                                                                    | 0.13 mm <sup>2</sup> | Clamping screw                                                                          | M 3                 |
| Connection cross-section, stranded, max.                                                | 6 mm <sup>2</sup>    | Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> |
| Connection direction                                                                    | on side              | Gauge to IEC 60947-1                                                                    | A4                  |
| Number of connections                                                                   | 2                    | Stripping length                                                                        | 11 mm               |
| Tightening torque, max.                                                                 | 1 Nm                 | Tightening torque, min.                                                                 | 0.5 Nm              |
| Torque level with DMS electric screwdriver                                              | 2                    | Twin wire-end ferrules, max.                                                            | 1.5 mm <sup>2</sup> |
| Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  | Type of connection                                                                      | Screw connection    |
| Wire connection cross section AWG, max.                                                 | AWG 10               | Wire connection cross section AWG, min.                                                 | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>    | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>    | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.                                         | 6 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup> |

## General

|                                         |        |                                         |               |
|-----------------------------------------|--------|-----------------------------------------|---------------|
| Rail                                    | TS 35  | Standards                               | IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 10 | Wire connection cross section AWG, min. | AWG 26        |

## Rating data

|                                 |                   |                                              |        |
|---------------------------------|-------------------|----------------------------------------------|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 500 V  |
| Rated current                   | 32 A              | Current at maximum wires                     | 39 A   |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 6 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Pollution severity              | 3                 |                                              |        |

## UL rating data

|                                            |        |                                            |        |
|--------------------------------------------|--------|--------------------------------------------|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus)   | 10 AWG |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Current size B (cURus)                     | 10 A   |
| Current size D (cURus)                     | 10 A   | Voltage size B (cURus)                     | 300 V  |
| Voltage size D (cURus)                     | 300 V  |                                            |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 |             |             |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E60693  |

## Downloads


|                                             |                                                                                                                                                                                                                                                                                                                                                 |
|---------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">EAC certificate</a><br><a href="#">EAC EX Certificate</a><br><a href="#">CCC Ex Certificate</a><br><a href="#">CE Declaration of Conformity</a><br><a href="#">ATEX Certificate</a><br><a href="#">CE Declaration of Conformity all terminals</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                 |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                                                                                                                                                                                                                        |
| User Documentation                          | <a href="#">NTI WDU/WPE 4N</a><br><a href="#">Usage of terminals in EXi atmospheres</a><br><a href="#">StorageConditionsTerminalBlocks</a>                                                                                                                                                                                                      |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                        |
| Brochures                                   |                                                                                                                                                                                                                                                                                                                                                 |

### WDU 4N BL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5/4 mm<sup>2</sup>


End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

| Type       | WAP WDU2.5N/4N BL          | Version             |
|------------|----------------------------|---------------------|
| Order No.  | <a href="#">1060080000</a> | W-Series, End plate |
| GTIN (EAN) | 4008190097172              |                     |
| Qty.       | 50 pc(s).                  |                     |

| Type       | WAP WDU2.5N/4N             | Version             |
|------------|----------------------------|---------------------|
| Order No.  | <a href="#">1060000000</a> | W-Series, End plate |
| GTIN (EAN) | 4008190149154              |                     |
| Qty.       | 50 pc(s).                  |                     |

4 mm<sup>2</sup>


The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

## General ordering data

| Type       | ZQV 4N/3 BL                |
|------------|----------------------------|
| Order No.  | <a href="#">1528080000</a> |
| GTIN (EAN) | 4050118333008              |
| Qty.       | 60 pc(s).                  |

| Type       | ZQV 4N/9 RD                |
|------------|----------------------------|
| Order No.  | <a href="#">2460750000</a> |
| GTIN (EAN) | 4050118476170              |
| Qty.       | 20 pc(s).                  |

| Type       | ZQV 4N/7 RD                |
|------------|----------------------------|
| Order No.  | <a href="#">2460770000</a> |
| GTIN (EAN) | 4050118476194              |
| Qty.       | 20 pc(s).                  |

| Type       | ZQV 4N/9                   |
|------------|----------------------------|
| Order No.  | <a href="#">1528070000</a> |
| GTIN (EAN) | 4050118332797              |
| Qty.       | 20 pc(s).                  |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type ZQV 4N/7  
 Order No. [1528020000](#)  
 GTIN (EAN) 4050118332780  
 Qty. 20 pc(s).

Type ZQV 4N/5 BL  
 Order No. [1528140000](#)  
 GTIN (EAN) 4050118333015  
 Qty. 60 pc(s).

Type ZQV 4N/4 BL  
 Order No. [1528120000](#)  
 GTIN (EAN) 4050118332872  
 Qty. 60 pc(s).

Type ZQV 4N/8  
 Order No. [1528030000](#)  
 GTIN (EAN) 4050118332841  
 Qty. 20 pc(s).

Type ZQV 4N/10 BL  
 Order No. [1528230000](#)  
 GTIN (EAN) 4050118333138  
 Qty. 20 pc(s).

Type ZQV 4N/7 BL  
 Order No. [1528180000](#)  
 GTIN (EAN) 4050118333114  
 Qty. 20 pc(s).

Type ZQV 4N/6 RD  
 Order No. [2460780000](#)  
 GTIN (EAN) 4050118476200  
 Qty. 20 pc(s).

Type ZQV 4N/30  
 Order No. [2561580000](#)  
 GTIN (EAN) 4050118570113  
 Qty. 5 pc(s).

Type ZQV 4N/2 BL  
 Order No. [1528040000](#)  
 GTIN (EAN) 4050118332773  
 Qty. 60 pc(s).

Type ZQV 4N/50  
 Order No. [1528130000](#)  
 GTIN (EAN) 4050118332902  
 Qty. 5 pc(s).

Type ZQV 4N/3  
 Order No. [1527940000](#)  
 GTIN (EAN) 4050118332865  
 Qty. 60 pc(s).

Type ZQV 4N/5 RD  
 Order No. [2460790000](#)  
 GTIN (EAN) 4050118476217  
 Qty. 60 pc(s).

Type ZQV 4N/30 BL  
 Order No. [2561610000](#)  
 GTIN (EAN) 4050118569971  
 Qty. 5 pc(s).

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type ZQV 4N/2 RD  
 Order No. [2460450000](#)  
 GTIN (EAN) 4050118476149  
 Qty. 60 pc(s).

Type ZQV 4N/50 RD  
 Order No. [2460730000](#)  
 GTIN (EAN) 4050118476156  
 Qty. 5 pc(s).

Type ZQV 4N/9 BL  
 Order No. [1528220000](#)  
 GTIN (EAN) 4050118333107  
 Qty. 20 pc(s).

Type ZQV 4N/5  
 Order No. [1527980000](#)  
 GTIN (EAN) 4050118332759  
 Qty. 60 pc(s).

Type ZQV 4N/50 BL  
 Order No. [1528240000](#)  
 GTIN (EAN) 4050118333121  
 Qty. 5 pc(s).

Type ZQV 4N/8 RD  
 Order No. [2460760000](#)  
 GTIN (EAN) 4050118476187  
 Qty. 20 pc(s).

Type ZQV 4N/4  
 Order No. [1527970000](#)  
 GTIN (EAN) 4050118332889  
 Qty. 60 pc(s).

Type ZQV 4N/32  
 Order No. [2561670000](#)  
 GTIN (EAN) 4050118570175  
 Qty. 5 pc(s).

Type ZQV 4N/4 RD  
 Order No. [2460800000](#)  
 GTIN (EAN) 4050118476224  
 Qty. 60 pc(s).

Type ZQV 4N/10 RD  
 Order No. [2460740000](#)  
 GTIN (EAN) 4050118476163  
 Qty. 20 pc(s).

Type ZQV 4N/6 BL  
 Order No. [1528170000](#)  
 GTIN (EAN) 4050118332926  
 Qty. 20 pc(s).

Type ZQV 4N/2  
 Order No. [1527930000](#)  
 GTIN (EAN) 4050118332766  
 Qty. 60 pc(s).

Type ZQV 4N/8 BL  
 Order No. [1528190000](#)  
 GTIN (EAN) 4050118332858  
 Qty. 20 pc(s).

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |
|------------|----------------------------|
| Type       | ZQV 4N/6                   |
| Order No.  | <a href="#">1527990000</a> |
| GTIN (EAN) | 4050118332919              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 4N/3 RD                |
| Order No.  | <a href="#">2460810000</a> |
| GTIN (EAN) | 4050118476231              |
| Qty.       | 60 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 4N/10                  |
| Order No.  | <a href="#">1528090000</a> |
| GTIN (EAN) | 4050118332896              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 4N/30 RD               |
| Order No.  | <a href="#">2561600000</a> |
| GTIN (EAN) | 4050118569964              |
| Qty.       | 5 pc(s).                   |

## SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw. The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | SCHT 7                     | Version                                                   |
| Order No.  | <a href="#">0517960000</a> | SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00 |
| GTIN (EAN) | 4008190001742              | Weidmueller, white                                        |
| Qty.       | 20 pc(s).                  |                                                           |

**WDU 4N BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****DEK 5/6****WS/ DEK**

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

|            |                            |                                                        |
|------------|----------------------------|--------------------------------------------------------|
| Type       | DEK 5/6 MM WS              | Version                                                |
| Order No.  | <a href="#">2007120000</a> | Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392104              |                                                        |
| Qty.       | 600 pc(s).                 |                                                        |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## WS 12/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |                                                    |
|------------|----------------------------|----------------------------------------------------|
| Type       | WS 12/6 MM WS              | Version                                            |
| Order No.  | <a href="#">2007200000</a> | WS, Terminal marker, 12 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391886              |                                                    |
| Qty.       | 600 pc(s).                 |                                                    |

## W-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

## General ordering data

|            |                            |
|------------|----------------------------|
| Type       | WAD 4 GE BED               |
| Order No.  | <a href="#">1072000000</a> |
| GTIN (EAN) | 4008190446109              |
| Qty.       | 50 pc(s).                  |
| Type       | WAD 4 WS                   |
| Order No.  | <a href="#">1072100000</a> |
| GTIN (EAN) | 4008190446116              |
| Qty.       | 50 pc(s).                  |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## W-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                        |
|------------|----------------------------|------------------------|
| Type       | WTA 1/ZA WDU1.5            | Version                |
| Order No.  | <a href="#">1632300000</a> | W-Series, Test adapter |
| GTIN (EAN) | 4008190257354              |                        |
| Qty.       | 25 pc(s).                  |                        |
| Type       | WTA 1 WDU1.5               | Version                |
| Order No.  | <a href="#">1632290000</a> | W-Series, Test adapter |
| GTIN (EAN) | 4008190257361              |                        |
| Qty.       | 25 pc(s).                  |                        |

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WS 12/6 MC NE WS           | Version                                                            |
| Order No.  | <a href="#">1609900000</a> | WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, |
| GTIN (EAN) | 4008190203467              | Allen-Bradley, white                                               |
| Qty.       | 600 pc(s).                 |                                                                    |

## WDU 4N BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## ZGB pivotable group tag holder



The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.

The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

|            |                            |                                                                     |
|------------|----------------------------|---------------------------------------------------------------------|
| Type       | ZGB 15                     | Version                                                             |
| Order No.  | <a href="#">1636530000</a> | Terminal markers, Terminal marker, 15 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190297053              | Weidmueller, white                                                  |
| Qty.       | 20 pc(s).                  |                                                                     |
| Type       | ZGB 30                     | Version                                                             |
| Order No.  | <a href="#">1611930000</a> | Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190002251              | Weidmueller, white                                                  |
| Qty.       | 20 pc(s).                  |                                                                     |

## SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |                          |
|------------|----------------------------|--------------------------|
| Type       | EW 35 DB                   | Version                  |
| Order No.  | <a href="#">1269050000</a> | Accessories, End bracket |
| GTIN (EAN) | 4050118065008              |                          |
| Qty.       | 50 pc(s).                  |                          |

**WDU 4N BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/6 MC NE WS           | Version                                                   |
| Order No.  | <a href="#">1609820000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190203436              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1042680000](#)