

**CLI C 2-4 RT/WS + CD****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                  |
|------------|------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, red |
| Order No.  | <a href="#">1568261737</a>                                       |
| Type       | CLI C 2-4 RT/WS + CD                                             |
| GTIN (EAN) | 4008190109165                                                    |
| Qty.       | 250 pc(s).                                                       |

## CLI C 2-4 RT/WS + CD

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 8 mm    | Depth (inches)  | 0.315 inch |
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 7 mm    | Width (inches)  | 0.276 inch |
| Net weight | 0.212 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                   |                                      |                                              |               |
|-----------------------------------|--------------------------------------|----------------------------------------------|---------------|
| Colour                            | red                                  | Colour of printing                           | white         |
| Halogen                           | Yes                                  | Insulation cross-section, max.               | 10            |
| Material                          | PVC, soft, without Cadmium           | Material colour according to resistance code | 2             |
| Number of markers per combination | 1 Reel = Conductor and cable markers | Operating temperature range                  | -30...80 °C   |
| Operating temperature range, max. | 80 °C                                | Operating temperature range, min.            | -30 °C        |
| Orientation of print              | horizontal                           | Printed characters                           | Symbols       |
| Printing                          | +                                    | Printing method                              | hot-embossing |
| Recommended industries            | Process, Machinery                   | Type of printing                             | Standard      |
| UL 94 flammability rating         | V-0                                  | Version                                      | CD            |
| Width                             | 7 mm                                 |                                              |               |

## Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 4 - 10 mm           | Conductor O.D., max.             | 10 mm                    |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max.    | 16 mm <sup>2</sup>       |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1568261737](#)