

KSW 2,5 8/5,08 1-8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

General ordering data

Version	KSW, Terminal marker, 2.5 x 40.6 mm, Pitch in mm (P): 5.08 Weidmueller, white
Order No.	1630100001
Type	KSW 2,5 8/5,08 1-8
GTIN (EAN)	4008190228958
Qty.	10 pc(s).
Alternative product	1629900000

Creation date January 26, 2022 10:29:50 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

KSW 2,5 8/5,08 1-8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Height	2.5 mm	Height (inches)	0.098 inch
Width	40.6 mm	Width (inches)	1.598 inch
Net weight	0.6 g		

Temperatures

Operating temperature range	150 °C
-----------------------------	--------

General data

Adhesive	Acrylate	Application/manufacture	Weidmueller
Colour	white	Colour of printing	black
Material	Polyester, PVC-free	Material colour according to resistance code	9
Number of markers per combination	1 Label reel = Terminal marker	Number per sheet	20
Operating temperature range	150 °C	Operating temperature range, max.	150 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	1 - 8	Printing method	Thermal transfer
Version	Self-adhesive	Width	40.6 mm

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ECLASS 9.0	27-14-11-37
ECLASS 9.1	27-14-11-37	ECLASS 10.0	27-14-11-37
ECLASS 11.0	27-28-11-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1630100001](#)