

LM MT300 40/6 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 6 x 40 mm, white
Order No.	1760461044
Type	LM MT300 40/6 WS
GTIN (EAN)	4032248032167
Qty.	10 pc(s).

LM MT300 40/6 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	6 mm	Height (inches)	0.236 inch
Width	40 mm	Width (inches)	1.575 inch
Net weight	11.4 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester, PVC-free	Material colour according to resistance code	9
Number of markers per combination	1 Label sheet = 176 Device markers	Number per sheet	176
Operating temperature range	-40...150 °C	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Printing method	Laser print
UL 94 flammability rating	HB	Version	Self-adhesive
Width	40 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

LM MT300 40/6 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1760461044](#)