


CP M DM40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Use our diode and redundancy modules to connect two power supplies and compensate for a device failing. In addition, our capacity module offers power reserves, guaranteeing purposeful and quick triggering of a circuit breaker, for example.

General ordering data

Version	Diode module
Order No.	1222220000
Type	CP M DM40
GTIN (EAN)	4050118005455
Qty.	1 pc(s).
Available until	2019-06-30
Alternative product	2486110000

CP M DM40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	130 mm	Height (inches)	5.118 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	867 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5...95 %, no condensation		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

DC input voltage range	18...30 V DC	Input current	2 x 20 A or 1 x 40 A
Rated input voltage	24 V DC	Wire connection method	Screw connection

Output

Nominal output current for U_{nom}	40 A @ 60 °C	Output current, max.	48 A
Output voltage, note	Voltage input - 0.7 V	Rated output voltage	24 V DC $\pm$ 1 %
Switching thresholds	21.6 V DC, relay is on for Power Good, 20.4 V DC, relay is off for Power Fail	Voltage monitoring	Yes, In both inputs
Wire connection method	Screw connection		

General data

Degree of efficiency	> 97% @ 24 V Input voltage	Humidity	5...95 %, no condensation
Mounting position, installation notice	Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.	Operating temperature	-25 °C...70 °C

EMC / shock / vibration

Interference immunity test acc. to	EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)	Noise emission in accordance with EN55032	
Shock resistance IEC 60068-2-27	15 g In all directions	Vibration resistance IEC 60068-2-6	Class B 1 g according to EN 50178

Insulation coordination

Insulation voltage	0.5 kV Input / output - Box	Pollution severity	2
Protection class	III, with no ground connection, for SELV		

CP M DM40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Electrical safety (applied standards)

Electrical machine equipment

Acc. to EN60204

For use with electronic equipment

Acc. to EN50178 /
VDE0160

Connection data (input)

Conductor cross-section, AWG/kcmil ,
max.

6

Conductor cross-section, AWG/kcmil ,
min.

22

Conductor cross-section, flexible , min.

2.5 mm²

Conductor cross-section, rigid , max.

16 mm²

Conductor cross-section, rigid , min.

0.5 mm²Wire connection cross section, flexible
(input), max.10 mm²

Connection data (output)

Conductor cross-section, AWG/kcmil ,
max.

6

Conductor cross-section, AWG/kcmil ,
min.

22

Conductor cross-section, flexible , max.

10 mm²

Conductor cross-section, flexible , min.

2.5 mm²

Conductor cross-section, rigid , max.

16 mm²

Conductor cross-section, rigid , min.

0.5 mm²

Number of terminals

4 (3 +, 4 +, 3 -, 4 -)

Signalling

Floating contact

Yes

Approvals

Certificate No. (GERMLLOYD)

94767-10

Certificate no. (cULus)

E258476

Institute (GERMLLOYD)

GERMLLOYD

Institute (cULus)

CULUS

Classifications

ETIM 6.0

EC002540

ETIM 7.0

EC002540

ETIM 8.0

EC002540

ECLASS 9.0

27-04-07-01

ECLASS 9.1

27-04-07-01

ECLASS 10.0

27-04-07-01

ECLASS 11.0

27-04-07-90

Approvals

Approvals



ROHS

Conform

UL File Number Search

E258476

Downloads

Approval/Certificate/Document of
Conformity[DE_PA5200_160512_001.pdf](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD](#)

User Documentation

[Operating instructions](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1222220000](#)