

IE-SFP-1FEMLC-T**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Version	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85 °C
Order No.	1241450000
Type	IE-SFP-1FEMLC-T
GTIN (EAN)	4050118029192
Qty.	1 pc(s).

IE-SFP-1FEMLC-T**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	40 g
------------	------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024	Safety standard	UL 60950-1
Ship use	DNV-GL		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps														
Digital diagnostic monitor function (DDM)	Supported														
Transceiver type	Multimode														
Connector type	LC-Duplex														
Transmission distance, typ.	4 km														
Wavelength	<table border="1"> <tr> <td>typ.</td> <td>1,310 nm</td> </tr> <tr> <td>Wavelength</td> <td>TX</td> </tr> <tr> <td>min.</td> <td>1,280 nm</td> </tr> <tr> <td>max.</td> <td>1,340 nm</td> </tr> <tr> <td>Wavelength</td> <td>RX</td> </tr> <tr> <td>min.</td> <td>1,100 nm</td> </tr> <tr> <td>max.</td> <td>1,650 nm</td> </tr> </table>	typ.	1,310 nm	Wavelength	TX	min.	1,280 nm	max.	1,340 nm	Wavelength	RX	min.	1,100 nm	max.	1,650 nm
typ.	1,310 nm														
Wavelength	TX														
min.	1,280 nm														
max.	1,340 nm														
Wavelength	RX														
min.	1,100 nm														
max.	1,650 nm														
Receive power	<table border="1"> <tr> <td>min.</td> <td>-32 dBm</td> </tr> <tr> <td>max.</td> <td>-3 dBm</td> </tr> </table>	min.	-32 dBm	max.	-3 dBm										
min.	-32 dBm														
max.	-3 dBm														
Transmission power	<table border="1"> <tr> <td>min.</td> <td>-18 dBm</td> </tr> <tr> <td>max.</td> <td>-8 dBm</td> </tr> </table>	min.	-18 dBm	max.	-8 dBm										
min.	-18 dBm														
max.	-8 dBm														
Link-budget	14 dB														

Guarantee

Time interval	3 years
---------------	---------

Power supply

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

IE-SFP-1FEMLC-T**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ECLASS 9.0	27-44-03-92	ECLASS 9.1	27-44-02-92
ECLASS 10.0	27-44-03-92	ECLASS 11.0	27-44-03-92
ECLASS 12.0	27-44-03-92		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Downloads

Approval/Certificate/Document of Conformity	DNV certificate EU Declaration of Conformity
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1241450000](#)