

CC-M 85/54 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	MetalliCard, Device markers, 54 x 85 mm, silver
Order No.	1327600000
Type	CC-M 85/54 AL
GTIN (EAN)	4050118132502
Qty.	40 pc(s).

CC-M 85/54 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	54 mm	Height (inches)	2.126 inch
Width	85 mm	Width (inches)	3.346 inch
Net weight	6.1 g		

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

General data

Colour	silver	Material	Chrome coated aluminium (AL)
Number of markers per combination	1 MetalliCard = Device markers	Operating temperature range	-55...130 °C
Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C
Recommended industries	Energy, Process	Size of labelling field	83.8 x 52.4 mm
Width	85 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

CC-M 85/54 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



CC-M 85/54 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Complementary products****General ordering data**

Type	DKB CC 85/54	Version
Order No.	1175850000	MetalliCard, Adhesive strip, 54 x 85 mm, Transparent
GTIN (EAN)	4032248972364	
Qty.	100 pc(s).	
Type	INLAY CC-M 85/54	
Order No.	1341030000	
GTIN (EAN)	4050118145427	
Qty.	1 pc(s).	
Type	INLAY CC-M UNIVERSAL	
Order No.	1341120000	
GTIN (EAN)	4050118145458	
Qty.	1 pc(s).	
Type	PRIMER CC-M	
Order No.	2068020000	
GTIN (EAN)	4050118416534	
Qty.	100 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1327600000](#)