

THM WO VIN 24.5/62 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 5.1 - 13.7 mm, 24.5 x 62 mm, white
Order No.	1391410000
Type	THM WO VIN 24.5/62 WS
GTIN (EAN)	4050118191530
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

Creation date January 23, 2022 9:38:10 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

THM WO VIN 24.5/62 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	24.5 mm	Height (inches)	0.965 inch
Width	62 mm	Width (inches)	2.441 inch
Net weight	683 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Vinyl film	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	2,000	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Size of labelling field	25 x 24.5 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	62 mm		

Conductor and cable markers

Conductor O.D.	5.1 - 13.7 mm	Conductor O.D., max.	13.7 mm
Conductor O.D., min.	5.1 mm	Conductor cross-section, max.	95 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 95 mm ²
Halogen	Yes	Text field height	19.05 mm
Text field width	24.5 mm		

Classifications


ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format



THM WO VIN 24.5/62 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1391410000](#)