


**RSM-8 24V- 2CO S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Relay bases (RSM) with common positive and negative to be connected to PLC or other type of controllers. The interfaces are made up of groups of 4, 8 or 16 RCL relays (12.7 mm) or RSS (6.1 mm). The connection to the controller can be set up using pluggable connectors or using direct cabling with IEC 60603-13 connectors. Wide range of options:

- 1 or 2 CO contacts with 16/8/6 A relays
- Voltages from 5 to 230 V
- Screw, tension clamp or PUSH IN connection
- Compatible with Weidmüller's solid-state relays

The range of relays provides galvanic isolation between input/output as well as between the adjacent contacts on the relays. This enables the various voltages in the controllers and those required by the various field elements to be safely adapted.

**General ordering data**

|            |                                  |
|------------|----------------------------------|
| Version    | Interface, RSM, Screw connection |
| Order No.  | <a href="#">1448940000</a>       |
| Type       | RSM-8 24V- 2CO S                 |
| GTIN (EAN) | 4050118253474                    |
| Qty.       | 1 pc(s).                         |

## RSM-8 24V- 2CO S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |           |                 |            |
|------------|-----------|-----------------|------------|
| Depth      | 71 mm     | Depth (inches)  | 2.795 inch |
| Height     | 109 mm    | Height (inches) | 4.291 inch |
| Width      | 149 mm    | Width (inches)  | 5.866 inch |
| Net weight | 440.408 g |                 |            |

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
|---------------------|-------------|-----------------------|-------------|

## Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Rated data UL

|                                 |          |                                  |               |
|---------------------------------|----------|----------------------------------|---------------|
| Operating temperature UL, max.  | 50 °C    | Operating temperature UL, min.   | 0 °C          |
| Rated current $I_N$             | 16.7 mA  | Rated voltage DC $U_N$ (supply)  | 24 V DC + 10% |
| Rated current (supply)          | 4.6 A    | Rated voltage DC $U_N$ (input)   | 24 V DC + 10% |
| Rated voltage AC $U_N$ (output) | 250 V AC | Rated current $I_{max}$ (output) | 4.6 A         |

## General data

|                              |       |                                  |        |
|------------------------------|-------|----------------------------------|--------|
| LED status display per relay | green | LED status of the supply voltage | yellow |
|------------------------------|-------|----------------------------------|--------|

## Connection data

|                         |              |                            |                                                                                     |
|-------------------------|--------------|----------------------------|-------------------------------------------------------------------------------------|
| Connection (field side) | LL2N 5.08 mm | Connection on control side | LP 5.08 + plug-in connector in acc. with IEC60603-13 / DIN41651, 10-pin, LL 5.08 mm |
|-------------------------|--------------|----------------------------|-------------------------------------------------------------------------------------|

## Rating data

|                         |                                       |
|-------------------------|---------------------------------------|
| Mechanical service life | 30 x 10 <sup>6</sup> switching cycles |
|-------------------------|---------------------------------------|

## Ratings data input

|               |               |               |         |
|---------------|---------------|---------------|---------|
| Input voltage | 24 V DC ± 10% | Input current | 16.7 mA |
|---------------|---------------|---------------|---------|

## Ratings data output

|                            |            |                         |                        |
|----------------------------|------------|-------------------------|------------------------|
| Relay type                 | RCL        | Type of output          | Potential-free contact |
| Contact material           | AgNi 90/10 | Rated voltage           | ≤ 250 V AC             |
| Max. AC continuous current | 5 A        | Minimum contact current | 0.1 A                  |
| Minimum contact voltage    | 5 V        |                         |                        |

## Insulation coordination (EN50178)

|                          |          |                               |      |
|--------------------------|----------|-------------------------------|------|
| Pollution severity level | 2        | Pulse voltage test (1,2/50µs) | 6 kV |
| Insulation test voltage  | 1.2 kVAC |                               |      |

## RSM-8 24V- 2CO S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Insulation coordinates (EN50178)

|                                   |           |                                    |          |
|-----------------------------------|-----------|------------------------------------|----------|
| Rated input insulation voltage    | < 50 V AC | Rated output insulation voltage    | 250 V AC |
| Overvoltage category input/output | III       | Overvoltage category output/output | III      |
| Pollution severity level          | 2         | Pulse voltage test (1,2/50µs)      | 6 kV     |
| Insulation test voltage           | 1.2 kVAC  | Clearance input/output             | ≥ 5.5 mm |

## Connection field

|                                  |                     |                              |                      |
|----------------------------------|---------------------|------------------------------|----------------------|
| Clamping range, max.             | 6 mm <sup>2</sup>   | Clamping range, min.         | 0.13 mm <sup>2</sup> |
| Flexible with sleeve, max.       | 2.5 mm <sup>2</sup> | Flexible with sleeve, min.   | 0.5 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K       | 4 mm <sup>2</sup>   | Flexible, min. H05(07) V-K   | 0.5 mm <sup>2</sup>  |
| Max. wire cross-section, AWG     | AWG 12              | Min. wire cross-section, AWG | AWG 26               |
| Sleeve with plastic collar, max. | 2.5 mm <sup>2</sup> | Solid, max. H05(07) V-U      | 6 mm <sup>2</sup>    |
| Solid, min. H05(07) V-U          | 0.5 mm <sup>2</sup> | Stripping length             | 6 mm                 |
| Tightening torque, max.          | 0.6 Nm              | Tightening torque, min.      | 0.5 Nm               |
| Type of connection               | Screw connection    |                              |                      |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002780    | ETIM 7.0    | EC002780    |
| ETIM 8.0    | EC002780    | ECLASS 9.0  | 27-14-11-52 |
| ECLASS 9.1  | 27-24-22-16 | ECLASS 10.0 | 27-14-11-52 |
| ECLASS 11.0 | 27-14-11-52 |             |             |

## Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E141197 |

## Downloads


|                                             |                                                                   |
|---------------------------------------------|-------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of Conformity</a>                         |
| Product Change Notification                 | <a href="#">20210816 Technical change to RSM relay interfaces</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                          |
| Brochures                                   |                                                                   |

## RSM-8 24V- 2CO S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1448940000](#)