

VG M25 EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, and besides EAC, they are ATEX and IECEx certified.

General ordering data

Version	VG Exe 4J (Ex plastic cable gland 4J Exe), Cable glands, M 25, 10 mm, OD min. 13 - OD max. 18 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1461150000
Type	VG M25 EXE SW
GTIN (EAN)	4050118267273
Qty.	20 pc(s).

Creation date January 25, 2022 1:21:40 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

VG M25 EXE SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	22.85 g
------------	---------

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

Certificate numbers cable gland

Approval conditions	ATEX, IECEX, EAC	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (EAC)	RU C-TR 05.B04161	Certificate no. cable gland (IECEX)	IECEX IMQ 13.0003X
Identification	Ex e IIC Gb, Ex tb IIIC Db IP66/68		

General information

AF size 1	33 mm	AF size 2	33 mm
Cable glands	metric	Explosion protection type	Improved safety Ex e
External thread	M 25	Impact resistance	4 J ATEX version
Installation guidelines	See assembly instructions	Length of thread	10 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Outer cable diameter, max.	18 mm
Outer cable diameter, min.	13 mm	Pitch of thread	1.5 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Seal insert		Standards	IEC 60079-0, IEC 60079-7, IEC 60079-31, EN 60079-0, EN 60079-7, EN 60079-31
	CR		
UL 94 flammability rating	HB		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-34	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



Approvals	CE; EAC; ATEX; IECEX
ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

VG M25 EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M25 MS	Version
Order No.	1737010000	SKMU MS (brass locknut), Locknut, M 25, 3.5 mm, Brass, nickel-
GTIN (EAN)	4008190956486	plated
Qty.	100 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1461150000](#)