

FP MONO LED DC HQ8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Energy-efficient basic lighting with a long service life**

- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	1488530000
Type	FP MONO LED DC HQ8
GTIN (EAN)	4050118298574

FP MONO LED DC HQ8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	68 mm	Height (inches)	2.677 inch
Width	104 mm	Width (inches)	4.094 inch
Length	271 mm	Length (inches)	10.669 inch
Net weight	662 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
Humidity	92 % @ 25 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3, 6,6'-di-tert-butyl-2,2'- methylenedi-p-cresol 119-47-1	SCIP	cfe9d4bf-2d88-4e4b- aa73-fe200a7615a0
------------	---	------	--

General data

Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Connector cross-section, max.	2.5 mm ²	Connector cross-section, min.	0.5 mm ²
Efficiency class (according to EU Directive No. 874/2012)	A	Halogen	No
Height	≤ 3000 m	Insulation voltage	< 500 V (housing/PE)
LED operating life	> 50.000 h	Light colour (CCT)	Cool White, 6000K
Light current	393 lm	Mounting position, installation notice	Arbitrary
Peak acceleration, type L	70 m/s ²	Pollution severity	2
Protection class	II	Protection degree	IP54
Shape of the LED module	Other	Shock resistance EN 60721-3-3	Class 3M3 portable
Short-circuit protection	Yes, internal	Silicone	No
Surge voltage category	II	Type of connection	Plug-in connector with fixed number of poles, HQ 8
UL 94 flammability rating	V-0	Vibration resistance EN 60721-3-3	Class 3M3 sinusoidal, stationary

Rated data acc. to IEC 60598-1

DC input voltage range	24...120 V DC	Input voltage	21.6 V ... 144 V DC / protected against reverse polarity
Power rating	5 W		

Classifications

ETIM 6.0	EC001959	ETIM 7.0	EC001959
ETIM 8.0	EC001959	ECLASS 9.0	27-11-06-40
ECLASS 9.1	27-11-06-40	ECLASS 10.0	27-11-06-40
ECLASS 11.0	27-11-06-40	ECLASS 12.0	27-11-06-40

FP MONO LED DC HQ8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E345151

Downloads

Catalogues	Catalogues in PDF-format
------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1488530000](#)