

**KP-M20/-120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|            |                                              |
|------------|----------------------------------------------|
| Version    | cable lug, terminal end, 120 mm <sup>2</sup> |
| Order No.  | <a href="#">1498280000</a>                   |
| Type       | KP-M20/-120                                  |
| GTIN (EAN) | 4050118307702                                |
| Qty.       | 50 pc(s).                                    |

**KP-M20/-120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |           |
|------------|-----------|
| Net weight | 116.592 g |
|------------|-----------|

**Technical data**

|         |                               |
|---------|-------------------------------|
| Version | DIN series 46235,<br>standard |
|---------|-------------------------------|

**Connectors**

|                                |                     |                                |               |
|--------------------------------|---------------------|--------------------------------|---------------|
| Conductor cross-section        | 120 mm <sup>2</sup> | Connection length (l)          | 72 mm         |
| Flange width (b)               | 36 mm               | Hole                           | M 20          |
| Identification number Cu       | 20 K                | Inside diameter of flange (d2) | 21 mm         |
| Inside diameter of shaft (d1)  | 15.5 mm             | Insulation                     | not available |
| Outside diameter of shaft (d3) | 21 mm               | Shaft length (a)               | 35 mm         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001050    | ETIM 7.0    | EC001050    |
| ETIM 8.0    | EC001050    | ECLASS 9.0  | 27-40-02-03 |
| ECLASS 9.1  | 27-40-02-03 | ECLASS 10.0 | 27-40-02-03 |
| ECLASS 11.0 | 27-40-02-03 | ECLASS 12.0 | 27-40-02-03 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |                                          |

## KP-M20/-120

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1498280000](#)