

WAS5 DC/ALARM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Limit value monitoring, Input : 0-20 mA, 0-10 V, Output : 2 x relays
Order No.	8543820000
Type	WAS5 DC/ALARM
GTIN (EAN)	4032248181230
Qty.	1 pc(s).

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	112.4 mm	Depth (inches)	4.425 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	92.4 mm	Length (inches)	3.638 inch
Weight	137 g	Net weight	110.1 g

Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	0 °C...55 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Probability of failure

MTTF	369 Jahre
------	-----------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Input current	0(4)...20 mA	Input resistance, current	≤ 110 Ω
Input resistance, voltage	≥ 100 kΩ	Input voltage	0...10 V
Number of inputs	1		

Output

Contact material	AgNi 90/10	Status indicator	LED green ON: OK, LED red ON: alarm (per channel)
Switching thresholds	1...90 % (independently for channel 1 and channel 2)		

Output (digital)

Alarm function	configurable, High or low alarm, Hysteresis 5% / 10%	Contact material	AgNi 90/10
Continuous current	3 A	Hysteresis	1...10 % (independent for channel 1 and channel 2)
Max. switching voltage, AC	250 V	Type	2 CO contacts, Open or closed-circuit principle

General data

Accuracy	Repeat accuracy: max. ± 0.3% of measuring range end value (10 V/ 20 mA)	Configuration	DIP switch, Potentiometer
Current-carrying capacity of cross- connect.	≤ 2 A	Galvanic isolation	3-way isolator
Input/Output	0...10 V, 0(4)...20 mA / 2 CO contact	Power consumption	Typ.: 1 W both relays picked up
Rail	TS 35	Temperature coefficient	≤ 500 ppm/K
Type of connection	Screw connection	Voltage supply	24 V DC ± 25 %

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

Clearance & creepage distances	≥ 3 mm	EMC standards	EN 61000-4-2, -3, -4, -5, -6
Galvanic isolation	3-way isolator	Impulse withstand voltage	4 kV
Insulation voltage	2 kV _{eff} / 5 s	Pollution severity	2
Rated voltage	300 V	Surge voltage category	III

Connection data

Type of connection	Screw connection	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-20	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20		

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Limit-value monitoring component for DC-current/ voltage standard signals with relay output and 3-way electrical isolation.

Limit-value monitoring component in 22.5 mm width for recording 0(4)...20 mA / 0...10 V standard signals. Two relay contacts (COs), each with a switching capacity of 750 VA, are available on the output side for monitoring an upper and lower limit. The switching behaviour (high/low trip, fail-safe) can be selected using DIP switches. Switching thresholds and hystereses can be adjusted with the front-side potentiometer. The component has 4 kV of 3-way isolation and is supplied externally with 24 VDC.

Add-on housing for TS35 rail mounting
Dimensions: L/W/H
 92.4/ 22.5/ 112.4 mm
Screw connection /
Nominal cross-section
 2.5 mm²
Protection degree: IP
 20
Input
 0(4)...20 mA / 0...10 V
Output
 2 x relay / CO

Open-circuit/closed-circuit principle
Switching current 3 A
Switching voltage 6...250 V AC / 6...60 V DC
Switching thresholds 1...90 % via potentiometer (independently for channels 1 and 2)
Hysteresis 1% ... 10 % via potentiometer (independently for channels 1 and 2)
Temperature coefficient < 500 ppm/K
Step response time < 60 ms

Auxiliary power 24 VDC ± 25 %
Ambient temperature

Short specification

Limit-value monitoring component for DC-current/voltage standard signals with relay output and 3-way electrical isolation.

Limit-value monitoring component in 22.5 mm width for recording 0(4)...20 mA / 0...10 V standard signals. Two

WAS5 DC/ALARM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Important note**

Product information

This product will soon be replaced by a new product.

Please do not use with new systems. Please contact our technical support.

Approvals

Approvals



ROHS

Conform

UL File Number Search

E141197

DownloadsApproval/Certificate/Document of
Conformity[Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures


WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Connection diagram



Example 1



Example 2



Switch position/setting options

function	SW 1			
	1	2	3	4
Channel A High Trip	■			
Channel A Low Trip	□			
Channel B High Trip		■		
Channel B Low Trip		□		
FAILSAFE, Channel 1 & 2			□	□
NON FAILSAFE, Chan. 1 & 2			■	■

■ = on
□ = off

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank




WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 10/5 MC NE WS	Version
Order No.	1635000000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190261948	Allen-Bradley, white
Qty.	720 pc(s).	

2.5 mm²


The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Type	ZQV 2.5N/2 BL	Version
Order No.	1717990000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190349295	
Qty.	60 pc(s).	
Type	ZQV 2.5N/2 RT	Version
Order No.	1717900000	Accessories, Z-series, Cross-connector, 24 A
GTIN (EAN)	4008190349288	
Qty.	60 pc(s).	
Type	ZQV 2.5N/2 GE	Version
Order No.	1693800000	Z-series, Cross-connector, 24 A
GTIN (EAN)	4008190883621	
Qty.	60 pc(s).	

WAS5 DC/ALARM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	ZQV 2.5N/2 SW	Version
Order No.	1718080000	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190349301	
Qty.	60 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8543820000](#)